

0	
11	



Loc. F2D8

NOTES:

- 1) MAXIMUM TEMPERATURE CLASS:
CLASS 3 (125°C)
- 2) TEST METHOD PER:
SAE/USCAR-2 REV-4
SAE/USCAR-20 REV-2
- 3) CONNECTOR MAY BE USED WITH THE FOLLOWING RANGE
OF WIRE SIZES/TYPES:
-SIZE: 22 GAGE- 16 GAGE- 1.50mm MIN O.D. TO 2.41mm MAX O.D.
-THERMAL CONDUCTIVITY: 4-5 MS-8283
-CONTACT FCI ENGINEERING REGARDING USE OF OTHER WIRE
TYPES AND/OR SIZES
- 4) CONNECTOR MAY BE USED WITH THE FOLLOWING TERMINALS:
-FCI APEX150 WITH WIRE SIZES DEFINED IN NOTE 3.
-SEE FCI DRAWING 454011 FOR SPECIFIC PART NUMBERS
AND CRIMPING REQUIREMENTS.
-CONTACT FCI ENGINEERING REGARDING USE OF COMPATIBLE
NON FCI TERMINALS
- 5) ANNUAL QUALITY REQUIREMENTS:
-PERMISSION TO PERFORM CONTINUOUS COMPLIANCE
PER FCI SPECIFICATION #AQA-001 INSTEAD OF ANNUAL LAYOUT
AND ANNUAL PV REQUIREMENTS OF QS-9000 SECTION 2 AND
SAE/USCAR-2 REV-4.
- 6) INTERFACE REQUIREMENTS:
-MATES WITH FCI CONNECTORS AS SPECIFIED IN CHART AND
WITH DEVICES THAT CONFORM TO USCAR ISO-5-016-2-201
- 7)  QUALITY ASSURANCE REQUIREMENTS SPC DATA, REQUIRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Delphi Connection Systems:

[54241630](#) [54241630N](#) [54241631](#) [54241632](#) [54241632-B](#) [54241631-B](#) [54241630-B](#) [54241633-B](#) [54241630N-B](#)
[54241631N-B](#) [54241632N-B](#) [54241633N-B](#)