





TOP FEEDING REEL WINDING DIRECTION




PART No.	ENG No.	FORM	FINISH
08-65-0105	8088-(555)	CHAIN	555
08-65-0106	8088-(555)L	LOOSE	

LEGEND

8088-(***)*
PLATING CODE
BLANK = CHAIN FORM, TOP FEEDING REEL
L = LOOSE FORM



A-A



B-B

NOTES:

- MATERIAL: PHOS. BRONZE
- FINISH:
555 = 0.00038/.000015 MIN. SELECT GOLD IN CONTACT AREA OVER (0.00076)/.000030 MIN. NICKEL OVERALL
- PRODUCT SPECIFICATION: PS-99020-0088.
- FOR 22-30 AWG WIRE: (1.57)/.062 DIA MAX INSULATION
- THIS PART CONFORMS TO CLASS B REQUIREMENTS OF MOLEX COSMETIC SPECIFICATION PS-45499-002.

CUT-OFF TOLERANCE	EC NO: UCP2013-5579	DRWN:MKIPPER 2013/06/27	CHKD:JBELL 2013/06/27	APPR:FSMITH 2013/07/16	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	TITLE	DOCUMENT NO.	SHEET NO.
						$\nabla Z=0$	4 PLACES ± --- ± ---	MM/IN	10:1	METRIC		KK (2.54)/.100		
						$\nabla F=0$	3 PLACES ± --- ± .010					ANTI-FISH HOOKING		
						$\nabla E=0$	2 PLACES ± 0.25 ± .020					TERMINAL 22-30 AWG		
							1 PLACE ± 0.51 ± ---					molex		
							0 PLACE ± ±					SD-8088-****		
							ANGULAR ±1/2°							
							DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							
								SEE CHART						