

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


A

REV PER 0G3A-0002-04

05MAR04

JR

TM

AMP  
WIRE RANGE22-16 AWG  
SOLID OR STRANDED

1 STAMP AMP 22-18\*, LOCATED APPROX AS SHOWN. STAMPING MAY BE ON TOP OR BOTTOM.

2 WIRE INSULATION DIA: 2.67-3.56

3 TONGUE MATERIAL THK: 0.84 MAX

4 FROM THE EDGE OF METAL WIRE BBL TO CENTER OF STUD HOLE.

5 105°C [221°F] MAX OPERATING TEMP.

6 VOLTAGE RATING, 300V MAX

7 MATERIAL: BODY- COPPER ASTM B-152  
SLEEVE: NYLON, RED

8 FINISH: BODY- TIN PLATE PER ASTM B545

LOOSE PIECE

150300-0

PACKAGE TYPE

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN JR RUTH 05MAR2004

CHK T MICHIELUTTI 05MAR04

APVD T MICHIELUTTI 05MAR04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT


CUSTOMER DRAWING

tyco  
ElectronicsTyco Electronics Corporation  
Harrisburg, Pa 17105-3608NAME  
TERMINAL, RING TONGUE, P.I.D.G.,  
WIRE SIZE 22-16 AWG

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-150300

SCALE 5:1 SHEET 1 OF 1 REV A

DIMENSIONS:  
mmTOLERANCES UNLESS  
OTHERWISE SPECIFIED:0 PLC ± -  
1 PLC ± -  
2 PLC ± .02  
3 PLC ± -  
4 PLC ± -  
ANGLES ± -

MATERIAL

7

FINISH

8