

Glass Passivated Bridge Rectifiers




Features:



- UL Recognized file # E-326243.
- The Plastic material used carries underwriters laboratory flammability recognition 94V-0.
- Integrally moulded heatsink provide very low thermal resistance for maximum heat dissipation.
- Surge overload ratings from 300 amperes to 400 amperes.
- Typical I_R less than $0.2\mu A$.
- High temperature soldering guaranteed:
260°C / 10 seconds / 0.375 inches, (9.5mm) lead lengths (for wire type).
- Isolated voltage from case to lead over 2500 volts.

GBPC



Mechanical Data

Case : Moulded plastic body.
Terminals : Pure tin plated, lead free leads solderable per MIL-STD-202, Method 208.
Mounting torque : 20 inches-lbs. maximum.



Glass Passivated Bridge Rectifiers





Maximum Rating and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%

Type Number	Symbol	-005	Units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	V
Maximum RMS Voltage	V_{RMS}	35	
Maximum DC Blocking Voltage	V_{DC}	50	
Rectified Current GBPC25	$I_F (AV)$	25	A
Single Sine-wave Superimposed GBPC25	I_{FSM}	300	
Forward Voltage Drop Per GBPC25 12.5A	V_F	1.1	V
Maximum DC Reverse Current at Rated DC Blocking Voltage Per Element (Note 1)	I_R	5	μA
Typical Thermal Resistance	$R_{\theta JC}$	1.5	$^{\circ}C/W$
Operating and Storage Temperature Range	T_J, T_{STG}	-50 to +150	$^{\circ}C$

- Notes:** 1. Pulse test with PW = 300 μ sec, 1% duty cycle.
2. Suffix "W" - wire lead structure/"M" - terminal location face to face.

Ratings and Characteristic Curves (GBPC25005)




Glass Passivated Bridge Rectifiers




Ratings and Characteristic Curves (GBPC25005)


Maximum Non-Repetitive Forward Surge Current
Per Bridge Element



Typical Reverse Characteristics Per
Bridge Element



Typical Junction Capacitance



Part Number Table

Description	Part Number
Bridge Rectifier, 25A, 50V	GBPC25005

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.

