



- The exclusive two-piece design offers the lowest threading force in the industry
- Small head height permits more efficient use of space in compact areas
- Average 14% lighter than one-piece ties
- Excellent for critical applications such as aircraft design
- Releaseable for bundle modifications prior to tensioning and cutoff

Part Number:	SST1M-C0
Product Family:	<i>Sta-Strap</i> ® Cable Ties - Releasable - Weather Resistant Nylon 6.6
Product Line:	Two Piece Nylon Cable Ties
RoHS Compliancy Status:	Compliant
Part Description:	Cable Tie, Releasable, 4.0", Miniature cross section
Product Type:	Cable Ties
Material:	Weather Resistant Nylon 6.6
Color:	Black
CSA Certified:	Yes
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	Yes
Length (In.):	4.0

Length (mm):	102
Width (In.):	.095
Width (mm):	2.4
CE Compliant:	Yes
Cross Section:	Miniature
Head Height (In.):	.150
Head Height (mm):	3.8
Head Width (In.):	.175
Head Width (mm):	4.5
Locking Style:	Releasable
Material Flammability Rating:	UL94V-2
Max. Bundle Diameter (In.):	.78
Max. Bundle Diameter (mm):	20
Max. Continuous Use Temperature:	185°F (85°C)
Min. Loop Tensile Strength (Lbs.):	18
Min. Loop Tensile Strength (N):	80
Std. Pkg. UOM:	PK
Thickness (In.):	.035
Thickness (mm):	.9

Tool: GTS, GTSL, GS2B, PTS, PPTS, STS2

UOM: PC

Std. Pkg. Qty.: 100

Min. Order Qty.: 100