




## Solid-Electrolyte TANTALEX® Capacitors, Military MIL-PRF-39003/01 Qualified, Style CSR13



### PERFORMANCE CHARACTERISTICS

**Operating Temperature:** - 55 °C to + 125 °C  
(above 85 °C, voltage derating is required)

**Capacitance Range:** 0.033 µF to 330 µF

**Capacitance Tolerance:** ± 5 %, ± 10 %, ± 20 %

**Voltage Rating:** 6 V<sub>DC</sub> to 100 V<sub>DC</sub>

### DESCRIPTION

Solid-Electrolyte TANTALEX® capacitors to military specification MIL-PRF-39003 - Exponential and Weibull Distribution: Hermetically sealed, metal cased, axial leaded tubular capacitors manufactured as military style CSR13. These capacitors are furnished to the requirements of the military specification, including marking, testing and inspection.

In accordance with the specification, all capacitors are marked with the military part number (M39003/xx-xxxx) rather than the older style designation (CSRxxxxxxx) and should be ordered as such. All capacitors covered by MIL-PRF-39003 are now ordered with the military part number as illustrated in the Part Numbering System chart. Capacitors must not be ordered using the style number identification.

### FEATURES

- Hermetically sealed
- Metal cased
- Axial lead
- Weibull failure rates G, B, C, D
- Exponential failure rates M, P, R, S
- Tape and reel available per EIA-296 standard

### STYLE, MILITARY SPECIFICATION SHEET

Style CSR13, M39003/01 MIL-PRF-39003/01

MIL-PRF-39003 establishes failure rates (expressed in percent per 1000 h) based on exponential and Weibull distribution. Care must be exercised in ordering to insure the part number correctly identifies the desired failure rate level.

In addition, each order for military style CSR13, CSR21, CSR23 capacitors requiring government inspection must state whether inspection is to be at the destination or at the Vishay Sprague plant. Orders requiring source inspection cannot be shipped until this has been accomplished.

Style CS13 capacitors previously shown in MIL-C-26655 are directly replaced by style CSR13 and style CSR23 capacitors are extended capacitance range versions of military style CSR13.


For information on the performance characteristics of these capacitors, please refer to the latest issue of the military specification.

### ORDERING INFORMATION

| M39003                                                        | /01                                                                   | -2254                                               | A                                                                                                                                                                                                                                                                                                                                                                                                   | /TR                                                                                                                                                                          |
|---------------------------------------------------------------|-----------------------------------------------------------------------|-----------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| BASIC<br>DOCUMENT NUMBER                                      | SLASH SHEET                                                           | DASH NUMBER                                         | SURGE CURRENT<br>OPTION LETTER                                                                                                                                                                                                                                                                                                                                                                      | PACKAGING OPTION <sup>(1)</sup>                                                                                                                                              |
| Indicates the Basic Specification; in this case MIL-PRF-39003 | Indicates the Specification Sheet of the Basic Military Specification | Taken from Ratings table of the Specification Sheet | Blank = Standard (no surge current)<br>A = + 25 °C, after Weibull<br>B = - 55 °C and + 85 °C, after Weibull<br>C = - 55 °C and + 85 °C, before Weibull<br>D = + 25 °C, after Weibull, high temperature solder<br>E = - 55 °C and + 85 °C, after Weibull, high temperature solder<br>F = - 55 °C and + 85 °C, before Weibull, high temperature solder<br>H = High temperature solder only (no surge) | Blank = Bulk<br>/TR = Tape and reel<br>/HR = Tape and reel, half reel<br>/PR = Tape and reel, partial reel<br>/RR = Tape and reel, option R<br>/WR = Tape and reel, option W |

#### Note

<sup>(1)</sup> See detailed packaging information following the Standard Ratings table.

**DIMENSIONS** in inches [millimeters]


| CASE CODE | L<br>± 0.031 [0.79] | D<br>+ 0.016 [0.41]<br>- 0.015 [0.38] | M<br>± 0.002 [0.05] | J<br>(MAX.)   |
|-----------|---------------------|---------------------------------------|---------------------|---------------|
| A         | 0.286 [7.26]        | 0.135 [3.43]                          | 0.020 [0.51]        | 0.422 [10.72] |
| B         | 0.474 [12.04]       | 0.185 [4.70]                          | 0.020 [0.51]        | 0.610 [15.49] |
| C         | 0.686 [17.42]       | 0.289 [7.34]                          | 0.025 [0.64]        | 0.822 [20.88] |
| D         | 0.786 [19.96]       | 0.351 [8.92]                          | 0.025 [0.64]        | 0.922 [23.42] |

**Notes**

- The case insulation shall extend 0.015" [0.38 mm] minimum beyond each end. However, when a shrink-fitted insulation is used, it shall lap over the ends of the capacitor body.
- A minimum lead length of 1.0" [2.54 mm] for use with tape and reel automatic insertion equipment is available upon request.

**RATINGS AND CASE CODES**

| μF    | 6 V | 10 V | 15 V | 20 V | 35 V | 50 V | 75 V | 100 V |
|-------|-----|------|------|------|------|------|------|-------|
| 0.033 |     |      |      |      |      | A    |      | A     |
| 0.039 |     |      |      |      |      | A    |      | A     |
| 0.047 |     |      |      |      |      | A    |      | A     |
| 0.056 |     |      |      |      |      | A    |      | A     |
| 0.068 |     |      |      |      |      | A    |      | A     |
| 0.082 |     |      |      |      |      | A    |      | A     |
| 0.10  |     |      |      |      |      | A    | A    | A     |
| 0.12  |     |      |      |      |      | A    | A    | A     |
| 0.15  |     |      |      |      |      | A    | A    | A     |
| 0.18  |     |      |      |      |      | A    | A    | A     |
| 0.22  |     |      |      |      |      | A    | A    | A     |
| 0.27  |     |      |      |      |      | A    | A    | A     |
| 0.33  |     |      |      |      |      | A    | A    | A     |
| 0.39  |     |      |      |      |      | A    | A    | A     |
| 0.47  |     |      |      |      |      | A    | A    | A     |
| 0.56  |     |      |      |      |      | A    | A    | A     |
| 0.68  |     |      |      |      |      | A    | A    | B     |
| 0.82  |     |      |      |      |      | A    | B    | B     |
| 1.0   |     |      |      |      |      | A    | B    | B     |
| 1.2   |     |      |      | A    |      | B    | B    | B     |
| 1.5   |     |      |      | A    |      | B    | B    | B     |
| 1.8   |     |      |      | A    |      | B    | B    | B     |
| 2.2   |     |      |      | A    |      | B    | B    | B     |
| 2.7   |     |      | A    |      |      | B    | B    | B     |
| 3.3   |     |      | A    |      |      | B    | B    | C     |
| 3.9   |     | A    |      |      |      | B    | B    | C     |
| 4.7   |     | A    |      |      |      | B    | C    | C     |
| 5.6   | A   |      |      |      | B    | C    | C    | C     |
| 6.8   | A   |      |      |      | B    | C    | C    | C     |

**RATINGS AND CASE CODES**

| $\mu\text{F}$ | 6 V | 10 V | 15 V | 20 V | 35 V | 50 V | 75 V | 100 V |
|---------------|-----|------|------|------|------|------|------|-------|
| 8.2           |     |      |      | B    |      | C    | C    |       |
| 10            |     |      |      | B    |      | C    | C    |       |
| 12            |     |      |      | B    |      | C    | D    |       |
| 15            |     |      |      | B    |      | C    | D    |       |
| 18            |     |      | B    |      |      | C    |      |       |
| 22            |     |      | B    |      | C    | D    |      |       |
| 27            |     | B    |      | C    | D    |      |      |       |
| 33            |     | B    |      | C    | D    |      |      |       |
| 39            |     | B    |      | C    | D    |      |      |       |
| 47            | B   |      |      | C    | D    |      |      |       |
| 56            | B   |      | C    | D    |      |      |      |       |
| 68            |     |      | C    | D    |      |      |      |       |
| 82            |     | C    |      | D    |      |      |      |       |
| 100           |     | C    |      | D    |      |      |      |       |
| 120           |     | C    | D    |      |      |      |      |       |
| 150           | C   |      | D    |      |      |      |      |       |
| 180           | C   | D    |      |      |      |      |      |       |
| 220           |     | D    |      |      |      |      |      |       |
| 270           | D   |      |      |      |      |      |      |       |
| 330           | D   |      |      |      |      |      |      |       |

**STANDARD RATINGS**

| CAPACITANCE<br>( $\mu\text{F}$ )                                         | CASE<br>CODE | CAP.<br>TOL.<br>( $\pm$ %) | PART NO. M39003/01-<br>FAILURE RATE LEVEL (%/1000 h) |          |           |            |          |          |           |            | MAX. DCL ( $\mu\text{A}$ ) AT |         |          | MAX. DF (%) AT     |                     |
|--------------------------------------------------------------------------|--------------|----------------------------|------------------------------------------------------|----------|-----------|------------|----------|----------|-----------|------------|-------------------------------|---------|----------|--------------------|---------------------|
|                                                                          |              |                            | M<br>1.0                                             | P<br>0.1 | R<br>0.01 | S<br>0.001 | G<br>1.0 | B<br>0.1 | C<br>0.01 | D<br>0.001 | + 25 °C                       | + 85 °C | + 125 °C | - 55 °C<br>+ 25 °C | + 85 °C<br>+ 125 °C |
|                                                                          |              |                            |                                                      |          |           |            |          |          |           |            |                               |         |          |                    |                     |
| 6 V <sub>DC</sub> AT + 85 °C, SURGE = 8 V; 4 V <sub>DC</sub> AT + 125 °C |              |                            |                                                      |          |           |            |          |          |           |            |                               |         |          |                    |                     |
| 5.6                                                                      | A            | 5                          | 5001                                                 | 5201     | 5401      | 5601       | 4001     | 6001     | 7001      | 8001       | 0.3                           | 6       | 7.5      | 4                  | 4                   |
| 5.6                                                                      | A            | 10                         | 2241                                                 | 2481     | 2721      | 2961       | 4002     | 6002     | 7002      | 8002       | 0.3                           | 6       | 7.5      | 4                  | 4                   |
| 6.8                                                                      | A            | 5                          | 5002                                                 | 5202     | 5402      | 5602       | 4003     | 6003     | 7003      | 8003       | 0.3                           | 6       | 7.5      | 6                  | 6                   |
| 6.8                                                                      | A            | 10                         | 2242                                                 | 2482     | 2722      | 2962       | 4004     | 6004     | 7004      | 8004       | 0.3                           | 6       | 7.5      | 6                  | 6                   |
| 6.8                                                                      | A            | 20                         | 2243                                                 | 2483     | 2723      | 2963       | 4005     | 6005     | 7005      | 8005       | 0.3                           | 6       | 7.5      | 6                  | 6                   |
| 47                                                                       | B            | 5                          | 5003                                                 | 5203     | 5403      | 5603       | 4006     | 6006     | 7006      | 8006       | 1.5                           | 24      | 30       | 6                  | 6                   |
| 47                                                                       | B            | 10                         | 2244                                                 | 2484     | 2724      | 2964       | 4007     | 6007     | 7007      | 8007       | 1.5                           | 24      | 30       | 6                  | 6                   |
| 47                                                                       | B            | 20                         | 2245                                                 | 2485     | 2725      | 2965       | 4008     | 6008     | 7008      | 8008       | 1.5                           | 24      | 30       | 6                  | 6                   |
| 56                                                                       | B            | 5                          | 5004                                                 | 5204     | 5404      | 5604       | 4009     | 6009     | 7009      | 8009       | 1.5                           | 24      | 30       | 6                  | 6                   |
| 56                                                                       | B            | 10                         | 2246                                                 | 2486     | 2726      | 2966       | 4010     | 6010     | 7010      | 8010       | 1.5                           | 24      | 30       | 6                  | 6                   |
| 150                                                                      | C            | 5                          | 5005                                                 | 5205     | 5405      | 5605       | 4011     | 6011     | 7011      | 8011       | 4.5                           | 90      | 113      | 8                  | 8                   |
| 150                                                                      | C            | 10                         | 2247                                                 | 2487     | 2727      | 2967       | 4012     | 6012     | 7012      | 8012       | 4.5                           | 90      | 113      | 8                  | 8                   |
| 150                                                                      | C            | 20                         | 2248                                                 | 2488     | 2728      | 2968       | 4013     | 6013     | 7013      | 8013       | 4.5                           | 90      | 113      | 8                  | 8                   |
| 180                                                                      | C            | 5                          | 5006                                                 | 5206     | 5406      | 5606       | 4014     | 6014     | 7014      | 8014       | 5.5                           | 110     | 138      | 8                  | 8                   |
| 180                                                                      | C            | 10                         | 2249                                                 | 2489     | 2729      | 2969       | 4015     | 6015     | 7015      | 8015       | 5.5                           | 110     | 138      | 8                  | 8                   |
| 270                                                                      | D            | 5                          | 5007                                                 | 5207     | 5407      | 5607       | 4016     | 6016     | 7016      | 8016       | 6.5                           | 130     | 163      | 8                  | 8                   |
| 270                                                                      | D            | 10                         | 2250                                                 | 2490     | 2730      | 2970       | 4017     | 6017     | 7017      | 8017       | 6.5                           | 130     | 163      | 8                  | 8                   |
| 330                                                                      | D            | 5                          | 5008                                                 | 5208     | 5408      | 5608       | 4018     | 6018     | 7018      | 8018       | 7.5                           | 150     | 188      | 8                  | 8                   |
| 330                                                                      | D            | 10                         | 2251                                                 | 2491     | 2731      | 2971       | 4019     | 6019     | 7019      | 8019       | 7.5                           | 150     | 188      | 8                  | 8                   |
| 330                                                                      | D            | 20                         | 2252                                                 | 2492     | 2732      | 2972       | 4020     | 6020     | 7020      | 8020       | 7.5                           | 150     | 188      | 8                  | 8                   |



## STANDARD RATINGS

| CAPACITANCE<br>( $\mu$ F)                                                   | CASE<br>CODE | CAP.<br>TOL.<br>( $\pm$ %) | PART NO. M39003/01-<br>FAILURE RATE LEVEL (%/1000 h) |      |      |       |      |      |      |       | MAX. DCL ( $\mu$ A) AT |         |          | MAX. DF (%) AT     |                     |
|-----------------------------------------------------------------------------|--------------|----------------------------|------------------------------------------------------|------|------|-------|------|------|------|-------|------------------------|---------|----------|--------------------|---------------------|
|                                                                             |              |                            | M                                                    | P    | R    | S     | G    | B    | C    | D     | + 25 °C                | + 85 °C | + 125 °C | - 55 °C<br>+ 25 °C | + 85 °C<br>+ 125 °C |
|                                                                             |              |                            | 1.0                                                  | 0.1  | 0.01 | 0.001 | 1.0  | 0.1  | 0.01 | 0.001 |                        |         |          |                    |                     |
| 10 V <sub>DC</sub> AT + 85 °C, SURGE = 13 V; 7 V <sub>DC</sub> AT + 125 °C  |              |                            |                                                      |      |      |       |      |      |      |       |                        |         |          |                    |                     |
| 3.9                                                                         | A            | 5                          | 5009                                                 | 5209 | 5409 | 5609  | 4021 | 6021 | 7021 | 8021  | 0.3                    | 6       | 7.5      | 4                  | 4                   |
| 3.9                                                                         | A            | 10                         | 2253                                                 | 2493 | 2733 | 2973  | 4022 | 6022 | 7022 | 8022  | 0.3                    | 6       | 7.5      | 4                  | 4                   |
| 4.7                                                                         | A            | 5                          | 5010                                                 | 5210 | 5410 | 5610  | 4023 | 6023 | 7023 | 8023  | 0.4                    | 7       | 8.8      | 4                  | 4                   |
| 4.7                                                                         | A            | 10                         | 2254                                                 | 2494 | 2734 | 2974  | 4024 | 6024 | 7024 | 8024  | 0.4                    | 7       | 8.8      | 4                  | 4                   |
| 4.7                                                                         | A            | 20                         | 2255                                                 | 2495 | 2735 | 2975  | 4025 | 6025 | 7025 | 8025  | 0.4                    | 7       | 8.8      | 4                  | 4                   |
| 27                                                                          | B            | 5                          | 5011                                                 | 5211 | 5411 | 5611  | 4026 | 6026 | 7026 | 8026  | 2                      | 40      | 50       | 6                  | 6                   |
| 27                                                                          | B            | 10                         | 2256                                                 | 2496 | 2736 | 2976  | 4027 | 6027 | 7027 | 8027  | 2                      | 40      | 50       | 6                  | 6                   |
| 33                                                                          | B            | 5                          | 5012                                                 | 5212 | 5412 | 5612  | 4028 | 6028 | 7028 | 8028  | 2.5                    | 50      | 63       | 6                  | 6                   |
| 33                                                                          | B            | 10                         | 2257                                                 | 2497 | 2737 | 2977  | 4029 | 6029 | 7029 | 8029  | 2.5                    | 50      | 63       | 6                  | 6                   |
| 33                                                                          | B            | 20                         | 2258                                                 | 2498 | 2738 | 2978  | 4030 | 6030 | 7030 | 8030  | 2.5                    | 50      | 63       | 6                  | 6                   |
| 39                                                                          | B            | 5                          | 5013                                                 | 5213 | 5413 | 5613  | 4031 | 6031 | 7031 | 8031  | 2.5                    | 50      | 63       | 6                  | 6                   |
| 39                                                                          | B            | 10                         | 2259                                                 | 2499 | 2739 | 2979  | 4032 | 6032 | 7032 | 8032  | 2.5                    | 50      | 63       | 6                  | 6                   |
| 82                                                                          | C            | 5                          | 5014                                                 | 5214 | 5414 | 5614  | 4033 | 6033 | 7033 | 8033  | 4                      | 80      | 100      | 6                  | 6                   |
| 82                                                                          | C            | 10                         | 2260                                                 | 2500 | 2740 | 2980  | 4034 | 6034 | 7034 | 8034  | 4                      | 80      | 100      | 6                  | 6                   |
| 100                                                                         | C            | 5                          | 5015                                                 | 5215 | 5415 | 5615  | 4035 | 6035 | 7035 | 8035  | 5                      | 100     | 125      | 8                  | 8                   |
| 100                                                                         | C            | 10                         | 2261                                                 | 2501 | 2741 | 2981  | 4036 | 6036 | 7036 | 8036  | 5                      | 100     | 125      | 8                  | 8                   |
| 100                                                                         | C            | 20                         | 2262                                                 | 2502 | 2742 | 2982  | 4037 | 6037 | 7037 | 8037  | 5                      | 100     | 125      | 8                  | 8                   |
| 120                                                                         | C            | 5                          | 5016                                                 | 5216 | 5416 | 5616  | 4038 | 6038 | 7038 | 8038  | 6                      | 120     | 150      | 8                  | 8                   |
| 120                                                                         | C            | 10                         | 2263                                                 | 2503 | 2743 | 2983  | 4039 | 6039 | 7039 | 8039  | 6                      | 120     | 150      | 8                  | 8                   |
| 180                                                                         | D            | 5                          | 5017                                                 | 5217 | 5417 | 5617  | 4040 | 6040 | 7040 | 8040  | 9                      | 180     | 226      | 8                  | 8                   |
| 180                                                                         | D            | 10                         | 2264                                                 | 2504 | 2744 | 2984  | 4041 | 6041 | 7041 | 8041  | 9                      | 180     | 226      | 8                  | 8                   |
| 220                                                                         | D            | 5                          | 5018                                                 | 5218 | 5418 | 5618  | 4042 | 6042 | 7042 | 8042  | 10                     | 200     | 250      | 8                  | 8                   |
| 220                                                                         | D            | 10                         | 2265                                                 | 2505 | 2745 | 2985  | 4043 | 6043 | 7043 | 8043  | 10                     | 200     | 250      | 8                  | 8                   |
| 220                                                                         | D            | 20                         | 2266                                                 | 2506 | 2746 | 2986  | 4044 | 6044 | 7044 | 8044  | 10                     | 200     | 250      | 8                  | 8                   |
| 15 V <sub>DC</sub> AT + 85 °C, SURGE = 20 V; 10 V <sub>DC</sub> AT + 125 °C |              |                            |                                                      |      |      |       |      |      |      |       |                        |         |          |                    |                     |
| 2.7                                                                         | A            | 5                          | 5019                                                 | 5219 | 5419 | 5619  | 4045 | 6045 | 7045 | 8045  | 0.3                    | 6       | 7.5      | 4                  | 4                   |
| 2.7                                                                         | A            | 10                         | 2267                                                 | 2507 | 2747 | 2987  | 4046 | 6046 | 7046 | 8046  | 0.3                    | 6       | 7.5      | 4                  | 4                   |
| 3.3                                                                         | A            | 5                          | 5020                                                 | 5220 | 5420 | 5620  | 4047 | 6047 | 7047 | 8047  | 0.4                    | 8       | 10       | 4                  | 4                   |
| 3.3                                                                         | A            | 10                         | 2268                                                 | 2508 | 2748 | 2988  | 4048 | 6048 | 7048 | 8048  | 0.4                    | 8       | 10       | 4                  | 4                   |
| 3.3                                                                         | A            | 20                         | 2269                                                 | 2509 | 2749 | 2989  | 4049 | 6049 | 7049 | 8049  | 0.4                    | 8       | 10       | 4                  | 4                   |
| 18                                                                          | B            | 5                          | 5021                                                 | 5221 | 5421 | 5621  | 4050 | 6050 | 7050 | 8050  | 2                      | 35      | 44       | 6                  | 6                   |
| 18                                                                          | B            | 10                         | 2270                                                 | 2510 | 2750 | 2990  | 4051 | 6051 | 7051 | 8051  | 2                      | 35      | 44       | 6                  | 6                   |
| 22                                                                          | B            | 5                          | 5022                                                 | 5222 | 5422 | 5622  | 4052 | 6052 | 7052 | 8052  | 2                      | 40      | 50       | 6                  | 6                   |
| 22                                                                          | B            | 10                         | 2271                                                 | 2511 | 2751 | 2991  | 4053 | 6053 | 7053 | 8053  | 2                      | 40      | 50       | 6                  | 6                   |
| 22                                                                          | B            | 20                         | 2272                                                 | 2512 | 2752 | 2992  | 4054 | 6054 | 7054 | 8054  | 2                      | 40      | 50       | 6                  | 6                   |
| 56                                                                          | C            | 5                          | 5023                                                 | 5223 | 5423 | 5623  | 4055 | 6055 | 7055 | 8055  | 4                      | 80      | 100      | 6                  | 6                   |
| 56                                                                          | C            | 10                         | 2273                                                 | 2513 | 2753 | 2993  | 4056 | 6056 | 7056 | 8056  | 4                      | 80      | 100      | 6                  | 6                   |
| 68                                                                          | C            | 5                          | 5024                                                 | 5224 | 5424 | 5624  | 4057 | 6057 | 7057 | 8057  | 5                      | 100     | 125      | 6                  | 6                   |
| 68                                                                          | C            | 10                         | 2274                                                 | 2514 | 2754 | 2994  | 4058 | 6058 | 7058 | 8058  | 5                      | 100     | 125      | 6                  | 6                   |
| 68                                                                          | C            | 20                         | 2275                                                 | 2515 | 2755 | 2995  | 4059 | 6059 | 7059 | 8059  | 5                      | 100     | 125      | 6                  | 6                   |
| 120                                                                         | D            | 5                          | 5025                                                 | 5225 | 5425 | 5625  | 4060 | 6060 | 7060 | 8060  | 9                      | 180     | 226      | 8                  | 8                   |
| 120                                                                         | D            | 10                         | 2276                                                 | 2516 | 2756 | 2996  | 4061 | 6061 | 7061 | 8061  | 9                      | 180     | 226      | 8                  | 8                   |
| 150                                                                         | D            | 5                          | 5026                                                 | 5226 | 5426 | 5626  | 4062 | 6062 | 7062 | 8062  | 10                     | 200     | 250      | 8                  | 8                   |
| 150                                                                         | D            | 10                         | 2277                                                 | 2517 | 2757 | 2997  | 4063 | 6063 | 7063 | 8063  | 10                     | 200     | 250      | 8                  | 8                   |
| 150                                                                         | D            | 20                         | 2278                                                 | 2518 | 2758 | 2998  | 4064 | 6064 | 7064 | 8064  | 10                     | 200     | 250      | 8                  | 8                   |







## STANDARD RATINGS

| CAPACITANCE<br>(μF)                                                         | CASE<br>CODE | CAP.<br>TOL.<br>(± %) | PART NO. M39003/01-<br>FAILURE RATE LEVEL (%/1000 h) |      |      |       |      |      |      |       | MAX. DCL (μA) AT |         |          | MAX. DF (%) AT     |                     |
|-----------------------------------------------------------------------------|--------------|-----------------------|------------------------------------------------------|------|------|-------|------|------|------|-------|------------------|---------|----------|--------------------|---------------------|
|                                                                             |              |                       | M                                                    | P    | R    | S     | G    | B    | C    | D     | + 25 °C          | + 85 °C | + 125 °C | - 55 °C<br>+ 25 °C | + 85 °C<br>+ 125 °C |
|                                                                             |              |                       | 1.0                                                  | 0.1  | 0.01 | 0.001 | 1.0  | 0.1  | 0.01 | 0.001 |                  |         |          |                    |                     |
| 50 V <sub>DC</sub> AT + 85 °C, SURGE = 65 V; 33 V <sub>DC</sub> AT + 125 °C |              |                       |                                                      |      |      |       |      |      |      |       |                  |         |          |                    |                     |
| 2.7                                                                         | B            | 10                    | 2364                                                 | 2604 | 2844 | 3084  | 4207 | 6207 | 7207 | 8207  | 1                | 20      | 25       | 4                  | 4                   |
| 3.3                                                                         | B            | 5                     | 5084                                                 | 5284 | 5484 | 5684  | 4208 | 6208 | 7208 | 8208  | 1.2              | 25      | 32       | 4                  | 4                   |
| 3.3                                                                         | B            | 10                    | 2365                                                 | 2605 | 2845 | 3085  | 4209 | 6209 | 7209 | 8209  | 1.2              | 25      | 32       | 4                  | 4                   |
| 3.3                                                                         | B            | 20                    | 2366                                                 | 2606 | 2846 | 3086  | 4210 | 6210 | 7210 | 8210  | 1.2              | 25      | 32       | 4                  | 4                   |
| 3.9                                                                         | B            | 5                     | 5085                                                 | 5285 | 5485 | 5685  | 4211 | 6211 | 7211 | 8211  | 1.5              | 30      | 38       | 4                  | 4                   |
| 3.9                                                                         | B            | 10                    | 2367                                                 | 2607 | 2847 | 3087  | 4212 | 6212 | 7212 | 8212  | 1.5              | 30      | 38       | 4                  | 4                   |
| 4.7                                                                         | B            | 5                     | 5086                                                 | 5286 | 5486 | 5686  | 4213 | 6213 | 7213 | 8213  | 1.7              | 35      | 44       | 4                  | 4                   |
| 4.7                                                                         | B            | 10                    | 2368                                                 | 2608 | 2848 | 3088  | 4214 | 6214 | 7214 | 8214  | 1.7              | 35      | 44       | 4                  | 4                   |
| 4.7                                                                         | B            | 20                    | 2369                                                 | 2609 | 2849 | 3089  | 4215 | 6215 | 7215 | 8215  | 1.7              | 35      | 44       | 4                  | 4                   |
| 5.6                                                                         | C            | 5                     | 5087                                                 | 5287 | 5487 | 5687  | 4216 | 6216 | 7216 | 8216  | 2.2              | 45      | 56       | 4                  | 4                   |
| 5.6                                                                         | C            | 10                    | 2370                                                 | 2610 | 2850 | 3090  | 4217 | 6217 | 7217 | 8217  | 2.2              | 45      | 56       | 4                  | 4                   |
| 6.8                                                                         | C            | 5                     | 5088                                                 | 5288 | 5488 | 5688  | 4218 | 6218 | 7218 | 8218  | 2.2              | 45      | 56       | 6                  | 6                   |
| 6.8                                                                         | C            | 10                    | 2371                                                 | 2611 | 2851 | 3091  | 4219 | 6219 | 7219 | 8219  | 2.2              | 45      | 56       | 6                  | 6                   |
| 6.8                                                                         | C            | 20                    | 2372                                                 | 2612 | 2852 | 3092  | 4220 | 6220 | 7220 | 8220  | 2.2              | 45      | 56       | 6                  | 6                   |
| 8.2                                                                         | C            | 5                     | 5089                                                 | 5289 | 5489 | 5689  | 4221 | 6221 | 7221 | 8221  | 2.5              | 50      | 63       | 6                  | 6                   |
| 8.2                                                                         | C            | 10                    | 2373                                                 | 2613 | 2853 | 3093  | 4222 | 6222 | 7222 | 8222  | 2.5              | 50      | 63       | 6                  | 6                   |
| 10                                                                          | C            | 5                     | 5090                                                 | 5290 | 5490 | 5690  | 4223 | 6223 | 7223 | 8223  | 2.5              | 50      | 63       | 6                  | 6                   |
| 10                                                                          | C            | 10                    | 2374                                                 | 2614 | 2854 | 3094  | 4224 | 6224 | 7224 | 8224  | 2.5              | 50      | 63       | 6                  | 6                   |
| 10                                                                          | C            | 20                    | 2375                                                 | 2615 | 2855 | 3095  | 4225 | 6225 | 7225 | 8225  | 2.5              | 50      | 63       | 6                  | 6                   |
| 12                                                                          | C            | 5                     | 5091                                                 | 5291 | 5491 | 5691  | 4226 | 6226 | 7226 | 8226  | 3                | 60      | 75       | 6                  | 6                   |
| 12                                                                          | C            | 10                    | 2376                                                 | 2616 | 2856 | 3096  | 4227 | 6227 | 7227 | 8227  | 3                | 60      | 75       | 6                  | 6                   |
| 15                                                                          | C            | 5                     | 5092                                                 | 5292 | 5492 | 5692  | 4228 | 6228 | 7228 | 8228  | 4                | 80      | 100      | 6                  | 6                   |
| 15                                                                          | C            | 10                    | 2377                                                 | 2617 | 2857 | 3097  | 4229 | 6229 | 7229 | 8229  | 4                | 80      | 100      | 6                  | 6                   |
| 15                                                                          | C            | 20                    | 2378                                                 | 2618 | 2858 | 3098  | 4230 | 6230 | 7230 | 8230  | 4                | 80      | 100      | 6                  | 6                   |
| 18                                                                          | C            | 5                     | 5093                                                 | 5293 | 5493 | 5693  | 4231 | 6231 | 7231 | 8231  | 4.5              | 90      | 113      | 6                  | 6                   |
| 18                                                                          | C            | 10                    | 2379                                                 | 2619 | 2859 | 3099  | 4232 | 6232 | 7232 | 8232  | 4.5              | 90      | 113      | 6                  | 6                   |
| 22                                                                          | D            | 5                     | 5094                                                 | 5294 | 5494 | 5694  | 4233 | 6233 | 7233 | 8233  | 5.5              | 110     | 138      | 6                  | 6                   |
| 22                                                                          | D            | 10                    | 2380                                                 | 2620 | 2860 | 3100  | 4234 | 6234 | 7234 | 8234  | 5.5              | 110     | 138      | 6                  | 6                   |
| 22                                                                          | D            | 20                    | 2381                                                 | 2621 | 2861 | 3101  | 4235 | 6235 | 7235 | 8235  | 5.5              | 110     | 138      | 6                  | 6                   |
| 75 V <sub>DC</sub> AT + 85 °C, SURGE = 98 V; 50 V <sub>DC</sub> AT + 125 °C |              |                       |                                                      |      |      |       |      |      |      |       |                  |         |          |                    |                     |
| 0.10                                                                        | A            | 5                     | 5095                                                 | 5295 | 5495 | 5695  | 4236 | 6236 | 7236 | 8236  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.10                                                                        | A            | 10                    | 2382                                                 | 2622 | 2862 | 3102  | 4237 | 6237 | 7237 | 8237  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.10                                                                        | A            | 20                    | 2383                                                 | 2623 | 2863 | 3103  | 4238 | 6238 | 7238 | 8238  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.12                                                                        | A            | 5                     | 5096                                                 | 5296 | 5496 | 5696  | 4239 | 6239 | 7239 | 8239  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.12                                                                        | A            | 10                    | 2384                                                 | 2624 | 2864 | 3104  | 4240 | 6240 | 7240 | 8240  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.15                                                                        | A            | 5                     | 5097                                                 | 5297 | 5497 | 5697  | 4241 | 6241 | 7241 | 8241  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.15                                                                        | A            | 10                    | 2385                                                 | 2625 | 2865 | 3105  | 4242 | 6242 | 7242 | 8242  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.15                                                                        | A            | 20                    | 2386                                                 | 2626 | 2866 | 3106  | 4243 | 6243 | 7243 | 8243  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.18                                                                        | A            | 5                     | 5098                                                 | 5298 | 5498 | 5698  | 4244 | 6244 | 7244 | 8244  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.18                                                                        | A            | 10                    | 2387                                                 | 2627 | 2867 | 3107  | 4245 | 6245 | 7245 | 8245  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.22                                                                        | A            | 5                     | 5099                                                 | 5299 | 5499 | 5699  | 4246 | 6246 | 7246 | 8246  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.22                                                                        | A            | 10                    | 2388                                                 | 2628 | 2868 | 3108  | 4247 | 6247 | 7247 | 8247  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.22                                                                        | A            | 20                    | 2389                                                 | 2629 | 2869 | 3109  | 4248 | 6248 | 7248 | 8248  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.27                                                                        | A            | 5                     | 5100                                                 | 5300 | 5500 | 5700  | 4249 | 6249 | 7249 | 8249  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.27                                                                        | A            | 10                    | 2390                                                 | 2630 | 2870 | 3110  | 4250 | 6250 | 7250 | 8250  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.33                                                                        | A            | 5                     | 5101                                                 | 5301 | 5501 | 5701  | 4251 | 6251 | 7251 | 8251  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.33                                                                        | A            | 10                    | 2391                                                 | 2631 | 2871 | 3111  | 4252 | 6252 | 7252 | 8252  | 0.3              | 5       | 6.3      | 2                  | 4                   |





## STANDARD RATINGS

| CAPACITANCE<br>(μF)                                                         | CASE<br>CODE | CAP.<br>TOL.<br>(± %) | PART NO. M39003/01-<br>FAILURE RATE LEVEL (%/1000 h) |      |      |       |      |      |      |       | MAX. DCL (μA) AT |         |          | MAX. DF (%) AT     |                     |
|-----------------------------------------------------------------------------|--------------|-----------------------|------------------------------------------------------|------|------|-------|------|------|------|-------|------------------|---------|----------|--------------------|---------------------|
|                                                                             |              |                       | M                                                    | P    | R    | S     | G    | B    | C    | D     | + 25 °C          | + 85 °C | + 125 °C | - 55 °C<br>+ 25 °C | + 85 °C<br>+ 125 °C |
|                                                                             |              |                       | 1.0                                                  | 0.1  | 0.01 | 0.001 | 1.0  | 0.1  | 0.01 | 0.001 |                  |         |          |                    |                     |
| 75 V <sub>DC</sub> AT + 85 °C, SURGE = 98 V; 50 V <sub>DC</sub> AT + 125 °C |              |                       |                                                      |      |      |       |      |      |      |       |                  |         |          |                    |                     |
| 0.33                                                                        | A            | 20                    | 2392                                                 | 2632 | 2872 | 3112  | 4253 | 6253 | 7253 | 8253  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.39                                                                        | A            | 5                     | 5102                                                 | 5302 | 5502 | 5702  | 4254 | 6254 | 7254 | 8254  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.39                                                                        | A            | 10                    | 2393                                                 | 2633 | 2873 | 3113  | 4255 | 6255 | 7255 | 8255  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.47                                                                        | A            | 5                     | 5103                                                 | 5303 | 5503 | 5703  | 4256 | 6256 | 7256 | 8256  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.47                                                                        | A            | 10                    | 2394                                                 | 2634 | 2874 | 3114  | 4257 | 6257 | 7257 | 8257  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.47                                                                        | A            | 20                    | 2395                                                 | 2635 | 2875 | 3115  | 4258 | 6258 | 7258 | 8258  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.56                                                                        | A            | 5                     | 5104                                                 | 5304 | 5504 | 5704  | 4259 | 6259 | 7259 | 8259  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.56                                                                        | A            | 10                    | 2396                                                 | 2636 | 2876 | 3116  | 4260 | 6260 | 7260 | 8260  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.68                                                                        | A            | 5                     | 5105                                                 | 5305 | 5505 | 5705  | 4261 | 6261 | 7261 | 8261  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.68                                                                        | A            | 10                    | 2397                                                 | 2637 | 2877 | 3117  | 4262 | 6262 | 7262 | 8262  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.68                                                                        | A            | 20                    | 2398                                                 | 2638 | 2878 | 3118  | 4263 | 6263 | 7263 | 8263  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.82                                                                        | B            | 5                     | 5106                                                 | 5306 | 5506 | 5706  | 4264 | 6264 | 7264 | 8264  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 0.82                                                                        | B            | 10                    | 2399                                                 | 2639 | 2879 | 3119  | 4265 | 6265 | 7265 | 8265  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 1.0                                                                         | B            | 5                     | 5107                                                 | 5307 | 5507 | 5707  | 4266 | 6266 | 7266 | 8266  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 1.0                                                                         | B            | 10                    | 2400                                                 | 2640 | 2880 | 3120  | 4267 | 6267 | 7267 | 8267  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 1.0                                                                         | B            | 20                    | 2401                                                 | 2641 | 2881 | 3121  | 4268 | 6268 | 7268 | 8268  | 0.3              | 5       | 6.3      | 2                  | 4                   |
| 1.2                                                                         | B            | 5                     | 5108                                                 | 5308 | 5508 | 5708  | 4269 | 6269 | 7269 | 8269  | 0.3              | 5       | 6.3      | 4                  | 4                   |
| 1.2                                                                         | B            | 10                    | 2402                                                 | 2642 | 2882 | 3122  | 4270 | 6270 | 7270 | 8270  | 0.3              | 5       | 6.3      | 4                  | 4                   |
| 1.5                                                                         | B            | 5                     | 5109                                                 | 5309 | 5509 | 5709  | 4271 | 6271 | 7271 | 8271  | 0.6              | 10      | 13       | 4                  | 4                   |
| 1.5                                                                         | B            | 10                    | 2403                                                 | 2643 | 2883 | 3123  | 4272 | 6272 | 7272 | 8272  | 0.6              | 10      | 13       | 4                  | 4                   |
| 1.5                                                                         | B            | 20                    | 2404                                                 | 2644 | 2884 | 3124  | 4273 | 6273 | 7273 | 8273  | 0.6              | 10      | 13       | 4                  | 4                   |
| 1.8                                                                         | B            | 5                     | 5110                                                 | 5310 | 5510 | 5710  | 4274 | 6274 | 7274 | 8274  | 0.7              | 10      | 13       | 4                  | 4                   |
| 1.8                                                                         | B            | 10                    | 2405                                                 | 2645 | 2885 | 3125  | 4275 | 6275 | 7275 | 8275  | 0.7              | 10      | 13       | 4                  | 4                   |
| 2.2                                                                         | B            | 5                     | 5111                                                 | 5311 | 5511 | 5711  | 4276 | 6276 | 7276 | 8276  | 0.8              | 15      | 19       | 4                  | 4                   |
| 2.2                                                                         | B            | 10                    | 2406                                                 | 2646 | 2886 | 3126  | 4277 | 6277 | 7277 | 8277  | 0.8              | 15      | 19       | 4                  | 4                   |
| 2.2                                                                         | B            | 20                    | 2407                                                 | 2647 | 2887 | 3127  | 4278 | 6278 | 7278 | 8278  | 0.8              | 15      | 19       | 4                  | 4                   |
| 2.7                                                                         | B            | 5                     | 5112                                                 | 5312 | 5512 | 5712  | 4279 | 6279 | 7279 | 8279  | 1                | 15      | 19       | 4                  | 4                   |
| 2.7                                                                         | B            | 10                    | 2408                                                 | 2648 | 2888 | 3128  | 4280 | 6280 | 7280 | 8280  | 1                | 15      | 19       | 4                  | 4                   |
| 3.3                                                                         | B            | 5                     | 5113                                                 | 5313 | 5513 | 5713  | 4281 | 6281 | 7281 | 8281  | 1.2              | 20      | 25       | 4                  | 4                   |
| 3.3                                                                         | B            | 10                    | 2409                                                 | 2649 | 2889 | 3129  | 4282 | 6282 | 7282 | 8282  | 1.2              | 20      | 25       | 4                  | 4                   |
| 3.3                                                                         | B            | 20                    | 2410                                                 | 2650 | 2890 | 3130  | 4283 | 6283 | 7283 | 8283  | 1.2              | 20      | 25       | 4                  | 4                   |
| 3.9                                                                         | B            | 5                     | 5114                                                 | 5314 | 5514 | 5714  | 4284 | 6284 | 7284 | 8284  | 1.5              | 20      | 25       | 4                  | 4                   |
| 3.9                                                                         | B            | 10                    | 2411                                                 | 2651 | 2891 | 3131  | 4285 | 6285 | 7285 | 8285  | 1.5              | 20      | 25       | 4                  | 4                   |
| 4.7                                                                         | C            | 5                     | 5115                                                 | 5315 | 5515 | 5715  | 4286 | 6286 | 7286 | 8286  | 3                | 60      | 75       | 4                  | 4                   |
| 4.7                                                                         | C            | 10                    | 2412                                                 | 2652 | 2892 | 3132  | 4287 | 6287 | 7287 | 8287  | 3                | 60      | 75       | 4                  | 4                   |
| 4.7                                                                         | C            | 20                    | 2413                                                 | 2653 | 2893 | 3133  | 4288 | 6288 | 7288 | 8288  | 3                | 60      | 75       | 4                  | 4                   |
| 5.6                                                                         | C            | 5                     | 5116                                                 | 5316 | 5516 | 5716  | 4289 | 6289 | 7289 | 8289  | 3                | 60      | 75       | 4                  | 4                   |
| 5.6                                                                         | C            | 10                    | 2414                                                 | 2654 | 2894 | 3134  | 4290 | 6290 | 7290 | 8290  | 3                | 60      | 75       | 4                  | 4                   |
| 6.8                                                                         | C            | 5                     | 5117                                                 | 5317 | 5517 | 5717  | 4291 | 6291 | 7291 | 8291  | 5                | 100     | 125      | 6                  | 6                   |
| 6.8                                                                         | C            | 10                    | 2415                                                 | 2655 | 2895 | 3135  | 4292 | 6292 | 7292 | 8292  | 5                | 100     | 125      | 6                  | 6                   |
| 6.8                                                                         | C            | 20                    | 2416                                                 | 2656 | 2896 | 3136  | 4293 | 6293 | 7293 | 8293  | 5                | 100     | 125      | 6                  | 6                   |
| 8.2                                                                         | C            | 5                     | 5118                                                 | 5318 | 5518 | 5718  | 4294 | 6294 | 7294 | 8294  | 5                | 100     | 125      | 6                  | 6                   |
| 8.2                                                                         | C            | 10                    | 2417                                                 | 2657 | 2897 | 3137  | 4295 | 6295 | 7295 | 8295  | 5                | 100     | 125      | 6                  | 6                   |
| 10                                                                          | C            | 5                     | 5119                                                 | 5319 | 5519 | 5719  | 4296 | 6296 | 7296 | 8296  | 5                | 100     | 125      | 6                  | 6                   |
| 10                                                                          | C            | 10                    | 2418                                                 | 2658 | 2898 | 3138  | 4297 | 6297 | 7297 | 8297  | 5                | 100     | 125      | 6                  | 6                   |
| 10                                                                          | C            | 20                    | 2419                                                 | 2659 | 2899 | 3139  | 4298 | 6298 | 7298 | 8298  | 5                | 100     | 125      | 6                  | 6                   |
| 12                                                                          | D            | 5                     | 5120                                                 | 5320 | 5520 | 5720  | 4299 | 6299 | 7299 | 8299  | 5                | 100     | 125      | 6                  | 6                   |
| 12                                                                          | D            | 10                    | 2420                                                 | 2660 | 2900 | 3140  | 4300 | 6300 | 7300 | 8300  | 5                | 100     | 125      | 6                  | 6                   |
| 15                                                                          | D            | 5                     | 5121                                                 | 5321 | 5521 | 5721  | 4301 | 6301 | 7301 | 8301  | 7                | 140     | 175      | 6                  | 6                   |
| 15                                                                          | D            | 10                    | 2421                                                 | 2661 | 2901 | 3141  | 4302 | 6302 | 7302 | 8302  | 7                | 140     | 175      | 6                  | 6                   |
| 15                                                                          | D            | 20                    | 2422                                                 | 2662 | 2902 | 3142  | 4303 | 6303 | 7303 | 8303  | 7                | 140     | 175      | 6                  | 6                   |





## STANDARD RATINGS

| CAPACITANCE<br>( $\mu$ F)                                                     | CASE<br>CODE | CAP.<br>TOL.<br>( $\pm$ %) | PART NO. M39003/01-<br>FAILURE RATE LEVEL (%/1000 h) |      |      |       |      |      |      |       | MAX. DCL ( $\mu$ A) AT |         |          | MAX. DF (%) AT     |                     |
|-------------------------------------------------------------------------------|--------------|----------------------------|------------------------------------------------------|------|------|-------|------|------|------|-------|------------------------|---------|----------|--------------------|---------------------|
|                                                                               |              |                            | M                                                    | P    | R    | S     | G    | B    | C    | D     | + 25 °C                | + 85 °C | + 125 °C | - 55 °C<br>+ 25 °C | + 85 °C<br>+ 125 °C |
|                                                                               |              |                            | 1.0                                                  | 0.1  | 0.01 | 0.001 | 1.0  | 0.1  | 0.01 | 0.001 |                        |         |          |                    |                     |
| 100 V <sub>DC</sub> AT + 85 °C, SURGE = 130 V; 67 V <sub>DC</sub> AT + 125 °C |              |                            |                                                      |      |      |       |      |      |      |       |                        |         |          |                    |                     |
| 0.033                                                                         | A            | 5                          | 5132                                                 | 5332 | 5532 | 5732  | 4329 | 6329 | 7329 | 8329  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.033                                                                         | A            | 10                         | 2438                                                 | 2678 | 2918 | 3158  | 4330 | 6330 | 7330 | 8330  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.033                                                                         | A            | 20                         | 2439                                                 | 2679 | 2919 | 3159  | 4331 | 6331 | 7331 | 8331  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.039                                                                         | A            | 5                          | 5133                                                 | 5333 | 5533 | 5733  | 4332 | 6332 | 7332 | 8332  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.039                                                                         | A            | 10                         | 2440                                                 | 2680 | 2920 | 3160  | 4333 | 6333 | 7333 | 8333  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.047                                                                         | A            | 5                          | 5134                                                 | 5334 | 5534 | 5734  | 4334 | 6334 | 7334 | 8334  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.047                                                                         | A            | 10                         | 2441                                                 | 2681 | 2921 | 3161  | 4335 | 6335 | 7335 | 8335  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.047                                                                         | A            | 20                         | 2442                                                 | 2682 | 2922 | 3162  | 4336 | 6336 | 7336 | 8336  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.056                                                                         | A            | 5                          | 5135                                                 | 5335 | 5535 | 5735  | 4337 | 6337 | 7337 | 8337  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.056                                                                         | A            | 10                         | 2443                                                 | 2683 | 2923 | 3163  | 4338 | 6338 | 7338 | 8338  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.068                                                                         | A            | 5                          | 5136                                                 | 5336 | 5536 | 5736  | 4339 | 6339 | 7339 | 8339  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.068                                                                         | A            | 10                         | 2444                                                 | 2684 | 2924 | 3164  | 4340 | 6340 | 7340 | 8340  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.068                                                                         | A            | 20                         | 2445                                                 | 2685 | 2925 | 3165  | 4341 | 6341 | 7341 | 8341  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.082                                                                         | A            | 5                          | 5137                                                 | 5337 | 5537 | 5737  | 4342 | 6342 | 7342 | 8342  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.082                                                                         | A            | 10                         | 2446                                                 | 2686 | 2926 | 3166  | 4343 | 6343 | 7343 | 8343  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.10                                                                          | A            | 5                          | 5138                                                 | 5338 | 5538 | 5738  | 4344 | 6344 | 7344 | 8344  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.10                                                                          | A            | 10                         | 2447                                                 | 2687 | 2927 | 3167  | 4345 | 6345 | 7345 | 8345  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.10                                                                          | A            | 20                         | 2448                                                 | 2688 | 2928 | 3168  | 4346 | 6346 | 7346 | 8346  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.12                                                                          | A            | 5                          | 5139                                                 | 5339 | 5539 | 5739  | 4347 | 6347 | 7347 | 8347  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.12                                                                          | A            | 10                         | 2449                                                 | 2689 | 2929 | 3169  | 4348 | 6348 | 7348 | 8348  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.15                                                                          | A            | 5                          | 5140                                                 | 5340 | 5540 | 5740  | 4349 | 6349 | 7349 | 8349  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.15                                                                          | A            | 10                         | 2450                                                 | 2690 | 2930 | 3170  | 4350 | 6350 | 7350 | 8350  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.15                                                                          | A            | 20                         | 2451                                                 | 2691 | 2931 | 3171  | 4351 | 6351 | 7351 | 8351  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.18                                                                          | A            | 5                          | 5141                                                 | 5341 | 5541 | 5741  | 4352 | 6352 | 7352 | 8352  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.18                                                                          | A            | 10                         | 2452                                                 | 2692 | 2932 | 3172  | 4353 | 6353 | 7353 | 8353  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.22                                                                          | A            | 5                          | 5142                                                 | 5342 | 5542 | 5742  | 4354 | 6354 | 7354 | 8354  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.22                                                                          | A            | 10                         | 2453                                                 | 2693 | 2933 | 3173  | 4355 | 6355 | 7355 | 8355  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.22                                                                          | A            | 20                         | 2454                                                 | 2694 | 2934 | 3174  | 4356 | 6356 | 7356 | 8356  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.27                                                                          | A            | 5                          | 5143                                                 | 5343 | 5543 | 5743  | 4357 | 6357 | 7357 | 8357  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.27                                                                          | A            | 10                         | 2455                                                 | 2695 | 2935 | 3175  | 4358 | 6358 | 7358 | 8358  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.33                                                                          | A            | 5                          | 5144                                                 | 5344 | 5544 | 5744  | 4359 | 6359 | 7359 | 8359  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.33                                                                          | A            | 10                         | 2456                                                 | 2696 | 2936 | 3176  | 4360 | 6360 | 7360 | 8360  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.33                                                                          | A            | 20                         | 2457                                                 | 2697 | 2937 | 3177  | 4361 | 6361 | 7361 | 8361  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.39                                                                          | A            | 5                          | 5145                                                 | 5345 | 5545 | 5745  | 4362 | 6362 | 7362 | 8362  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.39                                                                          | A            | 10                         | 2458                                                 | 2698 | 2938 | 3178  | 4363 | 6363 | 7363 | 8363  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.47                                                                          | A            | 5                          | 5146                                                 | 5346 | 5546 | 5746  | 4364 | 6364 | 7364 | 8364  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.47                                                                          | A            | 10                         | 2459                                                 | 2699 | 2939 | 3179  | 4365 | 6365 | 7365 | 8365  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.47                                                                          | A            | 20                         | 2460                                                 | 2700 | 2940 | 3180  | 4366 | 6366 | 7366 | 8366  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.56                                                                          | A            | 5                          | 5147                                                 | 5347 | 5547 | 5747  | 4367 | 6367 | 7367 | 8367  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.56                                                                          | A            | 10                         | 2461                                                 | 2701 | 2941 | 3181  | 4368 | 6368 | 7368 | 8368  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.68                                                                          | B            | 5                          | 5148                                                 | 5348 | 5548 | 5748  | 4369 | 6369 | 7369 | 8369  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.68                                                                          | B            | 10                         | 2462                                                 | 2702 | 2942 | 3182  | 4370 | 6370 | 7370 | 8370  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.68                                                                          | B            | 20                         | 2463                                                 | 2703 | 2943 | 3183  | 4371 | 6371 | 7371 | 8371  | 0.3                    | 5       | 6.3      | 2                  | 4                   |
| 0.82                                                                          | B            | 5                          | 5149                                                 | 5349 | 5549 | 5749  | 4372 | 6372 | 7372 | 8372  | 0.4                    | 5       | 6.3      | 2                  | 4                   |
| 0.82                                                                          | B            | 10                         | 2464                                                 | 2704 | 2944 | 3184  | 4373 | 6373 | 7373 | 8373  | 0.4                    | 5       | 6.3      | 2                  | 4                   |
| 1.0                                                                           | B            | 5                          | 5150                                                 | 5350 | 5550 | 5750  | 4374 | 6374 | 7374 | 8374  | 0.5                    | 5       | 6.3      | 2                  | 4                   |



## STANDARD RATINGS

| CAPACITANCE<br>(μF)                                                           | CASE<br>CODE | CAP.<br>TOL.<br>(± %) | PART NO. M39003/01-<br>FAILURE RATE LEVEL (%/1000 h) |      |      |       |      |      |            |            | MAX. DCL (μA) AT |         |          | MAX. DF (%) AT     |                     |
|-------------------------------------------------------------------------------|--------------|-----------------------|------------------------------------------------------|------|------|-------|------|------|------------|------------|------------------|---------|----------|--------------------|---------------------|
|                                                                               |              |                       | M                                                    | P    | R    | S     | G    | B    | C          | D          | + 25 °C          | + 85 °C | + 125 °C | - 55 °C<br>+ 25 °C | + 85 °C<br>+ 125 °C |
|                                                                               |              |                       | 1.0                                                  | 0.1  | 0.01 | 0.001 | 1.0  | 0.1  | 0.01       | 0.001      |                  |         |          |                    |                     |
| 100 V <sub>DC</sub> AT + 85 °C, SURGE = 130 V; 67 V <sub>DC</sub> AT + 125 °C |              |                       |                                                      |      |      |       |      |      |            |            |                  |         |          |                    |                     |
| 1.0                                                                           | B            | 10                    | 2465                                                 | 2705 | 2945 | 3185  | 4375 | 6375 | 7375       | 8375       | 0.5              | 5       | 6.3      | 2                  | 4                   |
| 1.0                                                                           | B            | 20                    | 2466                                                 | 2706 | 2946 | 3186  | 4376 | 6376 | 7376       | 8376       | 0.5              | 5       | 6.3      | 2                  | 4                   |
| 1.2                                                                           | B            | 5                     | 5151                                                 | 5351 | 5551 | 5751  | 4377 | 6377 | 7377       | 8377       | 0.5              | 5       | 6.3      | 4                  | 4                   |
| 1.2                                                                           | B            | 10                    | 2467                                                 | 2707 | 2947 | 3187  | 4378 | 6378 | 7378       | 8378       | 0.5              | 5       | 6.3      | 4                  | 4                   |
| 1.5                                                                           | B            | 5                     | 5152                                                 | 5352 | 5552 | 5752  | 4379 | 6379 | 7379       | 8379       | 0.7              | 10      | 13       | 4                  | 4                   |
| 1.5                                                                           | B            | 10                    | 2468                                                 | 2708 | 2948 | 3188  | 4380 | 6380 | 7380       | 8380       | 0.7              | 10      | 13       | 4                  | 4                   |
| 1.5                                                                           | B            | 20                    | 2469                                                 | 2709 | 2949 | 3189  | 4381 | 6381 | 7381       | 8381       | 0.7              | 10      | 13       | 4                  | 4                   |
| 1.8                                                                           | B            | 5                     | 5153                                                 | 5353 | 5553 | 5753  | 4382 | 6382 | 7382       | 8382       | 0.7              | 10      | 13       | 4                  | 4                   |
| 1.8                                                                           | B            | 10                    | 2470                                                 | 2710 | 2950 | 3190  | 4383 | 6383 | 7383       | 8383       | 0.7              | 10      | 13       | 4                  | 4                   |
| 2.2                                                                           | B            | 5                     | 5154                                                 | 5354 | 5554 | 5754  | 4384 | 6384 | 7384       | 8384       | 0.9              | 15      | 19       | 4                  | 4                   |
| 2.2                                                                           | B            | 10                    | 2471                                                 | 2711 | 2951 | 3191  | 4385 | 6385 | 7385       | 8385       | 0.9              | 15      | 19       | 4                  | 4                   |
| 2.2                                                                           | B            | 20                    | 2472                                                 | 2712 | 2952 | 3192  | 4386 | 6386 | 7386       | 8386       | 0.9              | 15      | 19       | 4                  | 4                   |
| 2.7                                                                           | B            | 5                     | 5155                                                 | 5355 | 5555 | 5755  | 4387 | 6387 | 7387       | 8387       | 1.1              | 15      | 19       | 4                  | 4                   |
| 2.7                                                                           | B            | 10                    | 2473                                                 | 2713 | 2953 | 3193  | 4388 | 6388 | 7388       | 8388       | 1.1              | 15      | 19       | 4                  | 4                   |
| 3.3                                                                           | C            | 5                     | 5156                                                 | 5356 | 5556 | 5756  | 4389 | 6389 | Not<br>QPL | Not<br>QPL | 1.5              | 30      | 38       | 6                  | 6                   |
| 3.3                                                                           | C            | 10                    | 5157                                                 | 5357 | 5557 | 5757  | 4390 | 6390 | Not<br>QPL | Not<br>QPL | 1.5              | 30      | 38       | 6                  | 6                   |
| 3.3                                                                           | C            | 20                    | 5158                                                 | 5358 | 5558 | 5758  | 4391 | 6391 | Not<br>QPL | Not<br>QPL | 1.5              | 30      | 38       | 6                  | 6                   |
| 3.9                                                                           | C            | 5                     | 5159                                                 | 5359 | 5559 | 5759  | 4392 | 6392 | Not<br>QPL | Not<br>QPL | 1.5              | 30      | 38       | 6                  | 6                   |
| 3.9                                                                           | C            | 10                    | 5160                                                 | 5360 | 5560 | 5760  | 4393 | 6393 | Not<br>QPL | Not<br>QPL | 1.5              | 30      | 38       | 6                  | 6                   |
| 4.7                                                                           | C            | 5                     | 5161                                                 | 5361 | 5561 | 5761  | 4394 | 6394 | Not<br>QPL | Not<br>QPL | 2.5              | 50      | 63       | 6                  | 6                   |
| 4.7                                                                           | C            | 10                    | 5162                                                 | 5362 | 5562 | 5762  | 4395 | 6395 | Not<br>QPL | Not<br>QPL | 2.5              | 50      | 63       | 6                  | 6                   |
| 4.7                                                                           | C            | 20                    | 5163                                                 | 5363 | 5563 | 5763  | 4396 | 6396 | Not<br>QPL | Not<br>QPL | 2.5              | 50      | 63       | 6                  | 6                   |
| 5.6                                                                           | C            | 5                     | 5164                                                 | 5364 | 5564 | 5764  | 4397 | 6397 | Not<br>QPL | Not<br>QPL | 2.5              | 50      | 63       | 6                  | 6                   |
| 5.6                                                                           | C            | 10                    | 5165                                                 | 5365 | 5565 | 5765  | 4398 | 6398 | Not<br>QPL | Not<br>QPL | 2.5              | 50      | 63       | 6                  | 6                   |
| 6.8                                                                           | C            | 5                     | 5166                                                 | 5366 | 5566 | 5766  | 4399 | 6399 | Not<br>QPL | Not<br>QPL | 2.5              | 50      | 63       | 6                  | 6                   |
| 6.8                                                                           | C            | 10                    | 5167                                                 | 5367 | 5567 | 5767  | 4400 | 6400 | Not<br>QPL | Not<br>QPL | 2.5              | 50      | 63       | 6                  | 6                   |
| 6.8                                                                           | C            | 20                    | 5168                                                 | 5368 | 5568 | 5768  | 4401 | 6401 | Not<br>QPL | Not<br>QPL | 2.5              | 50      | 63       | 6                  | 6                   |

**STANDARD PACKAGING QUANTITY**

| CASE CODE | QUANTITY (pcs/reel) |           |              | BULK QUANTITY |         |
|-----------|---------------------|-----------|--------------|---------------|---------|
|           | FULL REEL           | HALF REEL | PARTIAL REEL | PER TRAY      | PER BOX |
| A         | 1000                | 500       | 100          | n/a           | 100     |
| B         | 1000                | 500       | 100          | 20            | 100     |
| C         | 500                 | 250       | 100          | 20            | 100     |
| D         | 500                 | 250       | 100          | 20            | 80      |

**INSIDE TAPE SPACING**

| PACKAGING OPTION | CASE CODE | TAPE SPACING                 |
|------------------|-----------|------------------------------|
| /TR; /HR; /PR    | A, B      | 2.47 ± 0.02<br>[62.7 ± 0.51] |
|                  | C, D      | 2.88 ± 0.02<br>[73.0 ± 0.51] |
| /RR              | A, B      | 2.05 ± 0.02<br>[52.1 ± 0.51] |
|                  | C, D      | 2.47 ± 0.02<br>[62.7 ± 0.51] |
| /WR              | A, B      | -                            |
|                  | C, D      | 2.05 ± 0.02<br>[52.1 ± 0.51] |

**PRODUCT INFORMATION**

|                                     |                                                                        |
|-------------------------------------|------------------------------------------------------------------------|
| Quick Reference Guide               | <a href="http://www.vishay.com/doc?40037">www.vishay.com/doc?40037</a> |
| Selector Guide                      | <a href="http://www.vishay.com/doc?49054">www.vishay.com/doc?49054</a> |
| Parameter Comparison Guide          | <a href="http://www.vishay.com/doc?40033">www.vishay.com/doc?40033</a> |
| Mounting of Through-Hole Components | <a href="http://www.vishay.com/doc?40108">www.vishay.com/doc?40108</a> |
| Frequently Asked Questions          | <a href="http://www.vishay.com/doc?40110">www.vishay.com/doc?40110</a> |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**