

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R1	REVISED PER ECO-16-004223	21JUL2016	NK	MZ

D

C

B


A

D

C

B

A



- 1

0.76µm[.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25µm [.000010] ON REMAINDER, OVER 1.27µm[.000050] MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TYCO ELECTRONICS PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
- 2

0.76µm[.000030] MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27µm[.000050]MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 1.27µm [.000050] MIN NICKEL PLATE. CONFORMS TO THE REQUIREMENTS OF TYCO ELECTRONICS PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENT APPLICATIONS).
- 3

WIRE RANGE 26-30 AWG.
- 4

INSULATION RANGE 0.36[.014]-0.76[.030] DIA.

OBSOLETE	2	66393-4	66406-4
	1	66393-1	66406-1
	FINISH	STRIP P/N REF	PART NO.
		TE TE Connectivity	
		PIN ASSEMBLY, LOOSE PIECE, TYPE III+	
		SIZE	RESTRICTED TO
		CAGE CODE	
		DRAWING NO	
		00779	
		C=66406	
		SCALE	8:1
		SHEET	1 OF 1
		REV	R1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	9-27-90
		CHK	12-15-90
		APVD	12-10-90
		PRODUCT SPEC	
		APPLICATION SPEC	
		WEIGHT	-
		CUSTOMER DRAWING	