






37	69.32	63.50	55.68	54.71	49.68
25	53.03	47.04	39.12	38.25	33.12
15	39.14	33.32	25.18	24.54	19.18
09	30.81	24.99	16.96	16.21	10.96
SHELL	A	B	C	D	E



ORDERING INFORMATION

[illegible]

MATERIAL

SHELL : STEEL TIN/Zinc Cr 3 PLATED.

INSULATORS : SELF EXTINGUISHING BLACK POLYESTER UL CLASS 94V0

IF WE USE PROTECTIVE ADHESIVE (type Kapton or Teflon)

: COPPER ALLOY

PLATING

PLATING

ACTIVE ZONE : GOLD OVER NICKEL

TERMINATION ZONE : TIN LEAD OVER NICKEL

FOR LEAD FREE PLATING : 2μMIN.MATTE TIN TOP OVER

1.27 μ MIN.NICKEL UNDER PLATE(ON TERMINATION ZONE)

METAL BRACKET : BRASS, TIN/Zinc Cr 3 PLATED.

HARPOON : BRASS, TIN PLATED.

SCREW LOCK : BRASS, TIN/Zinc Cr 3 PLATED.

ELECTRICAL DATA

MAX.CURRENT RATING : 5A

TEST VOLTAGE : 1000V

RATED VOLTAGE : 300V

CONTACT RESISTANCE : $\leq 25\text{m}\Omega$

SHELL RESISTANCE : $\leq 5m\Omega$

INSULATION RESISTANCE	: $\geq 5000M\Omega$
-----------------------	----------------------

ENVIRONMENTAL CHARACTERISTICS.

OPERATING TEMPERATURE RANGE : -55°C +125°C

MECHANICAL CHARACTERISTICS

MATING/UNMATING CYCLES (MIN)	:	200 (FLASH Au); 500 (0.76μ Au)

INSERTION/EXTRACTION FORCE PER CONTACT : 5 N Max./ 0.3 N Min