



LOC	DIST	REVISIONS				
G	86	P	LTR	DESCRIPTION	DATE	APVD
			F	REV PER 0G3A-0637-01	030CT02	JR MS




- 1

TIN PLATE 0.00381 [0.000150] MIN THK PER ASTM B 545
- 2

CLEANED, UNPLATED
- 3

PREPRODUCTION - FASR REQ

2 -	3 1-324453-0
1 -	324453
FINISH	AMP PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DK SCHRUM 01JUL96	AMP AMP Incorporated Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK WJ VOCKROTH 02JUL96				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		APVD JL MECKLEY 02JUL96	NAME WIRE SPLICE, PARALLEL, AMPOWER™ WIRE SIZE: 700 MCM		
			PRODUCT SPEC -			
			APPLICATION SPEC -			
MATERIAL COPPER PER ASTM B-75 ANNEALED		FINISH SEE TABLE	WEIGHT .181 lbs	SIZE A3	CAGE CODE 00779	DRAWING NO C-324453
CUSTOMER DRAWING			SCALE 2:1	SHEET 1	OF 1	REV F