

**OPA137**  
**OPA2137**  
**OPA4137**

## LOW COST FET-INPUT OPERATIONAL AMPLIFIERS

### *MicroAmplifier™* Series

#### FEATURES

- FET INPUT:  $I_B = 5\text{pA}$
- LOW OFFSET VOLTAGE: 1.5mV
- WIDE SUPPLY RANGE:  $\pm 2.25\text{V}$  to  $\pm 18\text{V}$
- LOW QUIESCENT CURRENT: 220 $\mu\text{A}$ /channel
- EXCELLENT SPEED/POWER: 1MHz
- INPUT TO POSITIVE SUPPLY
- *MicroSIZE* PACKAGES: SOT-23-5, MSOP-8
- SINGLE, DUAL, AND QUAD

#### APPLICATIONS

- STRAIN GAGE AMPLIFIER
- PHOTODETECTOR AMPLIFIER
- PRECISION INTEGRATOR
- BATTERY-POWERED INSTRUMENTS
- TEST EQUIPMENT
- ACTIVE FILTERS


#### DESCRIPTION

OPA137 series FET-input operational amplifiers are designed for low cost and miniature applications. In addition to small size (SOT-23-5 and MSOP-8 packages), they provide low input bias current (5pA), low quiescent current (220 $\mu\text{A}$ /channel), and high open-loop gain (94dB).

Either single (+4.5V to +36V) or dual ( $\pm 2.25$  to  $\pm 18\text{V}$ ) supplies can be used. The input common-mode voltage range includes the positive supply—suitable for many single-supply applications. Single, dual, and quad versions have identical specifications for maximum design flexibility.

OPA137 op amps are easy to use and free from phase inversion and overload problems found in some FET-input amplifiers. High performance, including linearity, is maintained as the amplifiers swing to their specified limits. In addition, the combination of high slew rate (3.5V/ $\mu\text{s}$ ) and wide bandwidth (1MHz) provide fast settling time assuring good dynamic response. Dual and quad designs feature completely independent circuitry for lowest crosstalk and freedom from interaction.

The single (OPA137) packages are the tiny 5-lead SOT-23-5 surface mount, SO-8 surface mount, and 8-pin DIP. The dual (OPA2137) comes in the miniature MSOP-8 surface mount, SO-8 surface mount, and 8-pin DIP packages. The quad (OPA4137) packages are the SO-14 surface mount and the 14-pin DIP. All are specified from  $-40^\circ\text{C}$  to  $+85^\circ\text{C}$  and operate from  $-55^\circ\text{C}$  to  $+125^\circ\text{C}$ . A SPICE macromodel is available for design analysis.



International Airport Industrial Park • Mailing Address: PO Box 11400, Tucson, AZ 85734 • Street Address: 6730 S. Tucson Blvd., Tucson, AZ 85706 • Tel: (520) 746-1111 • Twx: 910-952-1111  
Internet: <http://www.burr-brown.com/> • FAXLine: (800) 548-6133 (US/Canada Only) • Cable: BBRCORP • Telex: 066-6491 • FAX: (520) 889-1510 • Immediate Product Info: (800) 548-6132

# SPECIFICATIONS: $V_S = \pm 15V$

At  $T_A = +25^\circ\text{C}$ ,  $R_L = 10k\Omega$  connected to ground, unless otherwise noted.

**Boldface** limits apply over the specified temperature range,  $T_A = -40^\circ\text{C}$  to  $+85^\circ\text{C}$ .

| PARAMETER                                                                                                                                                                                                                                                   | CONDITION                                                                                                                                                                   | OPA137N, U, P<br>OPA2137E, U, P<br>OPA4137U, P           |                                                       |                                                                | OPA137NA, UA, PA<br>OPA2137EA, UA, PA<br>OPA4137UA, PA |                                       |                                                       | UNITS                                                                                                                                                                                        |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------|-------------------------------------------------------|----------------------------------------------------------------|--------------------------------------------------------|---------------------------------------|-------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                                                                                                                                                                             |                                                                                                                                                                             | MIN                                                      | TYP                                                   | MAX                                                            | MIN                                                    | TYP                                   | MAX                                                   |                                                                                                                                                                                              |
| <b>OFFSET VOLTAGE</b><br>Input Offset Voltage $V_{OS}$<br>$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$<br>vs Temperature $dV_{OS}/dT$<br>vs Power Supply PSRR<br>$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$<br>Channel Separation (dual, quad) dc | $T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$<br>$V_S = \pm 3V$ to $\pm 18V$                                                                                             |                                                          | $\pm 1.5$<br>$\pm 2.5$<br>$\pm 15$<br>$\pm 90$<br>0.6 | $\pm 3$<br>$\pm 7$<br>$\pm 250$<br><b><math>\pm 250</math></b> |                                                        | $\pm 2.5$<br>$\pm 3.5$<br>*<br>*<br>* | $\pm 10$<br><b><math>\pm 15</math></b><br>*<br>*<br>* | mV<br>mV<br>$\mu\text{V}/^\circ\text{C}$<br>$\mu\text{V}/V$<br>$\mu\text{V}/V$                                                                                                               |
| <b>INPUT BIAS CURRENT</b><br>Input Bias Current $I_B$<br>vs Temperature<br>Input Offset Current $I_{OS}$                                                                                                                                                    | $V_{CM} = 0V$                                                                                                                                                               |                                                          | $\pm 5$<br>See Typical Curve<br>$\pm 2$               | $\pm 100$<br>$\pm 50$                                          |                                                        | *<br>*<br>*                           | *<br>*<br>*                                           | pA<br>pA                                                                                                                                                                                     |
| <b>NOISE</b><br>Input Voltage Noise, $f = 0.1$ to $10\text{Hz}$<br>Input Voltage Noise Density, $f = 1\text{kHz}$ $e_n$<br>Current Noise Density, $f = 1\text{kHz}$ $i_n$                                                                                   |                                                                                                                                                                             |                                                          | 2<br>45<br>1.2                                        |                                                                |                                                        | *<br>*<br>*                           |                                                       | $\mu\text{Vp-p}$<br>$\text{nV}/\sqrt{\text{Hz}}$<br>$\text{fA}/\sqrt{\text{Hz}}$                                                                                                             |
| <b>INPUT VOLTAGE RANGE</b><br>Common-Mode Voltage Range $V_{CM}$<br>Common-Mode Rejection Ratio CMRR<br>OPA137, OPA2137<br>OPA4137<br>$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$<br>OPA137, OPA2137<br>OPA4137                                        | $V_{CM} = -12V$ to $15V$<br><br>$V_{CM} = -12V$ to $15V$                                                                                                                    | $(V-) + 3$<br><br>76<br>74<br><br><b>72</b><br><b>70</b> | <br><br>84<br>84                                      | $(V+)$<br><br><br><br>                                         | *<br><br>70<br>70<br><br><b>70</b><br><b>70</b>        | *<br><br>*<br>*                       | *<br><br><br><br>                                     | V<br><br>dB<br>dB<br><br>dB<br>dB                                                                                                                                                            |
| <b>INPUT IMPEDANCE</b><br>Differential<br>Common-Mode                                                                                                                                                                                                       |                                                                                                                                                                             |                                                          | $10^{10} \parallel 1$<br>$10^{12} \parallel 2$        |                                                                |                                                        | *<br>*                                |                                                       | $\Omega \parallel \text{pF}$<br>$\Omega \parallel \text{pF}$                                                                                                                                 |
| <b>OPEN-LOOP GAIN</b><br>Open-Loop Voltage Gain $A_{OL}$<br>$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$                                                                                                                                                | $V_O = -13.8V$ to $13.9V$<br>$V_O = -13.8V$ to $13.9V$                                                                                                                      | 86<br><b>86</b>                                          | 94                                                    |                                                                | *<br>*                                                 | *<br>                                 |                                                       | dB<br>dB                                                                                                                                                                                     |
| <b>FREQUENCY RESPONSE</b><br>Gain-Bandwidth Product GBW<br>Slew Rate SR<br>Settling Time, 0.1%<br>0.01%<br>Overload Recovery Time<br>Total Harmonic Distortion + Noise THD+N                                                                                | $G = 1$<br>$G = 1$ , $10V$ Step, $C_L = 100\text{pF}$<br>$G = 1$ , $10V$ Step, $C_L = 100\text{pF}$<br>$V_{IN} \cdot G = V_S$<br>$G = 1$ , $f = 1\text{kHz}$ , $3.5V_{rms}$ |                                                          | 1<br>3.5<br>8<br>10<br>1<br>0.05                      |                                                                |                                                        | *<br>*<br>*<br>*<br>*<br>*            |                                                       | MHz<br>$V/\mu\text{s}$<br>$\mu\text{s}$<br>$\mu\text{s}$<br>$\mu\text{s}$<br>%                                                                                                               |
| <b>OUTPUT</b><br>Voltage Output $V_{OUT}$<br>$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$<br>Short-Circuit Current $I_{SC}$<br>Capacitive Load Drive $C_{LOAD}$                                                                                         |                                                                                                                                                                             | $(V-) + 1.2$<br>$(V-) + 1.2$                             | <br><br>$-25/+60$<br>1000                             | $(V+) - 1.1$<br>$(V+) - 1.1$                                   | *<br>*                                                 | <br>*<br>*                            | *<br>*                                                | V<br>V<br>mA<br>pF                                                                                                                                                                           |
| <b>POWER SUPPLY</b><br>Specified Operating Range $V_S$<br>Operating Voltage Range<br>Dual Supplies<br>Single Supply<br>Quiescent Current $I_Q$<br>$T_A = -40^\circ\text{C}$ to $+85^\circ\text{C}$                                                          | $I_O = 0$<br>$I_O = 0$                                                                                                                                                      | $\pm 2.25^{(1)}$<br>+4.5                                 | $\pm 15$<br><br>$\pm 220$                             | $\pm 18$<br>+36<br>$\pm 270$<br><b><math>\pm 375</math></b>    | *<br>*                                                 | *<br>*                                | *<br>*<br>*<br>*                                      | V<br>V<br>V<br>$\mu\text{A}$<br>$\mu\text{A}$                                                                                                                                                |
| <b>TEMPERATURE RANGE</b><br>Specified Range<br>Operating Range<br>Storage Range<br>Thermal Resistance $\theta_{JA}$<br>SOT-23-5 Surface Mount<br>MSOP-8 Surface Mount<br>SO-8 Surface Mount<br>8-Pin DIP<br>SO-14 Surface Mount<br>14-Pin DIP               |                                                                                                                                                                             | -40<br>-55<br>-55                                        |                                                       | +85<br>+125<br>+125                                            | *<br>*<br>*                                            |                                       | *<br>*<br>*                                           | $^\circ\text{C}$<br>$^\circ\text{C}$<br>$^\circ\text{C}$<br>$^\circ\text{C}/W$<br>$^\circ\text{C}/W$<br>$^\circ\text{C}/W$<br>$^\circ\text{C}/W$<br>$^\circ\text{C}/W$<br>$^\circ\text{C}/W$ |

\* Specifications the same as OPA137N, U, P.

NOTE: (1) At minimum power supply voltage inputs must be biased above ground in accordance with common-mode voltage range restrictions—see “Operating Voltage” discussion.

## ABSOLUTE MAXIMUM RATINGS<sup>(1)</sup>

|                                           |                          |
|-------------------------------------------|--------------------------|
| Supply Voltage, V+ to V– .....            | 36V                      |
| Input Voltage .....                       | (V–) –0.7V to (V+) +0.7V |
| Input Current .....                       | 2mA                      |
| Output Short-Circuit <sup>(2)</sup> ..... | Continuous               |
| Operating Temperature .....               | –55°C to +125°C          |
| Storage Temperature .....                 | –55°C to +125°C          |
| Junction Temperature .....                | +150°C                   |
| Lead Temperature (soldering, 10s) .....   | 300°C                    |

NOTE: (1) Stresses above these ratings may cause permanent damage. Exposure to absolute maximum ratings for extended periods may affect device reliability. (2) Short circuit to ground, one amplifier per package.



## ELECTROSTATIC DISCHARGE SENSITIVITY

This integrated circuit can be damaged by ESD. Burr-Brown recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

## PACKAGE/ORDERING INFORMATION







| PRODUCT       | PACKAGE                       | PACKAGE DRAWING NUMBER <sup>(1)</sup> | SPECIFIED TEMPERATURE RANGE | PACKAGE MARKING    | ORDERING NUMBER <sup>(2)</sup> | TRANSPORT MEDIA |
|---------------|-------------------------------|---------------------------------------|-----------------------------|--------------------|--------------------------------|-----------------|
| <b>Single</b> |                               |                                       |                             |                    |                                |                 |
| OPA137N       | 5-Lead SOT-23-5 Surface Mount | 331                                   | –40°C to +85°C              | E37 <sup>(3)</sup> | OPA137N/250                    | Tape and Reel   |
| OPA137NA      | 5-Lead SOT-23-5 Surface Mount | 331                                   | –40°C to +85°C              | E37 <sup>(3)</sup> | OPA137NA/3K                    | Tape and Reel   |
| OPA137U       | SO-8 Surface Mount            | 182                                   | –40°C to +85°C              | OPA137U            | OPA137NA/3K                    | Tape and Reel   |
| OPA137UA      | SO-8 Surface Mount            | 182                                   | –40°C to +85°C              | OPA137UA           | OPA137U                        | Rails           |
| OPA137P       | 8-Pin DIP                     | 006                                   | –40°C to +85°C              | OPA137P            | OPA137U/2K5                    | Tape and Reel   |
| OPA137PA      | 8-Pin DIP                     | 006                                   | –40°C to +85°C              | OPA137PA           | OPA137UA                       | Rails           |
|               |                               |                                       |                             |                    | OPA137UA/2K5                   | Tape and Reel   |
|               |                               |                                       |                             |                    | OPA137P                        | Rails           |
|               |                               |                                       |                             |                    | OPA137PA                       | Rails           |
| <b>Dual</b>   |                               |                                       |                             |                    |                                |                 |
| OPA2137E      | MSOP-8 Surface Mount          | 337                                   | –40°C to +85°C              | E37 <sup>(3)</sup> | OPA2137E/250                   | Tape and Reel   |
| OPA2137EA     | MSOP-8 Surface Mount          | 337                                   | –40°C to +85°C              | E37 <sup>(3)</sup> | OPA2137E/2K5                   | Tape and Reel   |
| OPA2137U      | SO-8 Surface Mount            | 182                                   | –40°C to +85°C              | OPA2137U           | OPA2137EA/250                  | Tape and Reel   |
| OPA2137UA     | SO-8 Surface Mount            | 182                                   | –40°C to +85°C              | OPA2137UA          | OPA2137EA/2K5                  | Tape and Reel   |
| OPA2137P      | 8-Pin DIP                     | 006                                   | –40°C to +85°C              | OPA2137P           | OPA2137U                       | Rails           |
| OPA2137PA     | 8-Pin DIP                     | 006                                   | –40°C to +85°C              | OPA2137PA          | OPA2137U/2K5                   | Tape and Reel   |
|               |                               |                                       |                             |                    | OPA2137UA                      | Rails           |
|               |                               |                                       |                             |                    | OPA2137UA/2K5                  | Tape and Reel   |
|               |                               |                                       |                             |                    | OPA2137P                       | Rails           |
|               |                               |                                       |                             |                    | OPA2137PA                      | Rails           |
| <b>Quad</b>   |                               |                                       |                             |                    |                                |                 |
| OPA4137U      | SO-14 Surface Mount           | 235                                   | –40°C to +85°C              | OPA4137U           | OPA4137U                       | Rails           |
| OPA4137UA     | SO-14 Surface Mount           | 235                                   | –40°C to +85°C              | OPA4137UA          | OPA4137U/2K5                   | Tape and Reel   |
| OPA4137P      | 14-Pin DIP                    | 010                                   | –40°C to +85°C              | OPA4137P           | OPA4137UA                      | Rails           |
| OPA4137PA     | 14-Pin DIP                    | 010                                   | –40°C to +85°C              | OPA4137PA          | OPA4137UA/2K5                  | Tape and Reel   |
|               |                               |                                       |                             |                    | OPA4137P                       | Rails           |
|               |                               |                                       |                             |                    | OPA4137PA                      | Rails           |

NOTES: (1) For detailed drawing and dimension table, please see end of data sheet, or Appendix C of Burr-Brown IC Data Book. (2) Models with a slash (/) are available only in Tape and Reel in the quantities indicated (e.g., /2K5 indicates 2500 devices per reel). Ordering 3000 pieces of "OPA137NA/3K" will get a single 3000-piece Tape and Reel. For detailed Tape and Reel mechanical information, refer to Appendix B of Burr-Brown IC Data Book. (3) Grade information is marked on the reel.

The information provided herein is believed to be reliable; however, BURR-BROWN assumes no responsibility for inaccuracies or omissions. BURR-BROWN assumes no responsibility for the use of this information, and all use of such information shall be entirely at the user's own risk. Prices and specifications are subject to change without notice. No patent rights or licenses to any of the circuits described herein are implied or granted to any third party. BURR-BROWN does not authorize or warrant any BURR-BROWN product for use in life support devices and/or systems.







# TYPICAL PERFORMANCE CURVES

At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.









# TYPICAL PERFORMANCE CURVES (CONT)

At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.



# TYPICAL PERFORMANCE CURVES (CONT)

At  $T_A = +25^\circ\text{C}$ ,  $V_S = \pm 15\text{V}$ ,  $R_L = 10\text{k}\Omega$ , connected to ground, unless otherwise noted.



## APPLICATIONS INFORMATION

OPA137 series op amps are unity-gain stable and suitable for a wide range of general-purpose applications. Power supply pins should be bypassed with 10nF ceramic capacitors or larger. All circuitry is completely independent in dual and quad versions, assuring normal performance when one amplifier in a package is overdriven or short circuited. Many key parameters are guaranteed over the specified temperature range,  $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ .

### OPERATING VOLTAGE

OPA137 op amps can be operated on power supplies as low as  $\pm 2.25\text{V}$ . Performance remains excellent with power supplies ranging from  $\pm 2.25\text{V}$  to  $\pm 18\text{V}$  ( $+4.5\text{V}$  to  $+36\text{V}$  single supply). Most parameters vary only slightly throughout this supply voltage range. Quiescent current and short-circuit current vs supply voltage are shown in Typical Performance Curves.

Operation at very low supply voltage ( $V_S \leq \pm 3\text{V}$ ) requires careful attention to ensure that the common-mode voltage remains within the linear range,  $V_{CM} = (V-) + 3\text{V}$  to  $(V+)$ . Inputs may need to be biased above ground in accordance with the common-mode voltage range restrictions for linear operation.

### INPUT VOLTAGE

The input common-mode voltage range of OPA137 series op amps extends from  $(V-) + 3\text{V}$  to the positive rail,  $V+$ . For normal operation, inputs should be limited to this range. The inputs may go beyond the power supplies without output phase-reversal. Many FET-input op amps (such as TL061 types) exhibit phase-reversal of the output when the input common-mode range is exceeded. This can occur in voltage-follower circuits, causing serious problems in control loop applications.

Input terminals are diode-clamped to the power supply rails for ESD protection. If the input voltage can exceed the negative supply by 500mV, input current should be limited to 2mA (or less). If the input current is not adequately limited, you may see unpredictable behavior in the other amplifiers in the package. This is easily accomplished with an input resistor as shown in Figure 1. Many input signals are inherently current-limited, therefore, a limiting resistor may not be required.




FIGURE 1. Input Current Protection for Voltages Exceeding the Supply Voltage.

## HIGH-SIDE CURRENT SENSING

Many applications require the sensing of signals near the positive supply. The common-mode input range of OPA137 op amps includes the positive rail, enabling them to be used to sense power supply currents as shown in Figure 2.




FIGURE 2. High-Side Current Monitor.

### INPUT BIAS CURRENT

The input bias current is approximately 5pA at room temperature and increases with temperature as shown in the typical performance curve "Input Bias Current vs Temperature."

Input Bias current also varies with common-mode voltage and power supply voltage. This variation is dependent on the voltage between the negative power supply and the common-mode input voltage. The effect is shown in the typical performance curve "Input Bias Current vs Common-Mode Voltage."






FIGURE 3. Photodetector Amplifier.

**SOT-23-5**  
(Package Drawing #331)



**MSOP-8**  
(Package Drawing #337)



Refer to end of data sheet or Appendix C of Burr-Brown Data Book for tolerances and detailed package drawing. For further information on solder pads for surface-mount devices consult Application Bulletin AB-132.

FIGURE 4. Recommended SOT-23-5 and MSOP-8 Solder Footprints.

**PACKAGING INFORMATION**

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins   | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)       |
|-------------------------------|---------------|----------------------|------------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|---------------------------|
| <a href="#">OPA137N/250</a>   | Obsolete      | Production           | SOT-23 (DBV)   5 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | E37                       |
| <a href="#">OPA137N/3K</a>    | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU   SN                          | Level-2-260C-1 YEAR               | -40 to 85    | E37                       |
| OPA137N/3K.A                  | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | NIPDAU                               | Level-2-260C-1 YEAR               | -40 to 85    | E37                       |
| <a href="#">OPA137NA/250</a>  | Obsolete      | Production           | SOT-23 (DBV)   5 | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | E37                       |
| <a href="#">OPA137NA/3K</a>   | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| OPA137NA/3K.A                 | Active        | Production           | SOT-23 (DBV)   5 | 3000   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| <a href="#">OPA137U</a>       | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | OPA<br>137U               |
| OPA137U.A                     | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | OPA<br>137U               |
| <a href="#">OPA137UA</a>      | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | OPA<br>137U<br>A          |
| OPA137UA.A                    | Active        | Production           | SOIC (D)   8     | 75   TUBE             | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | OPA<br>137U<br>A          |
| <a href="#">OPA137UA/2K5</a>  | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -40 to 85    | (137UA, OPA)<br>137U<br>A |
| OPA137UA/2K5.A                | Active        | Production           | SOIC (D)   8     | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | (137UA, OPA)<br>137U<br>A |
| OPA2137E/250                  | Obsolete      | Production           | VSSOP (DGK)   8  | -                     | -           | Call TI                              | Call TI                           | -40 to 85    | E37                       |
| <a href="#">OPA2137E/2K5</a>  | Active        | Production           | VSSOP (DGK)   8  | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| OPA2137E/2K5.A                | Active        | Production           | VSSOP (DGK)   8  | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| <a href="#">OPA2137EA/250</a> | Obsolete      | Production           | VSSOP (DGK)   8  | -                     | -           | Call TI                              | Call TI                           | -            | E37                       |
| <a href="#">OPA2137EA/2K5</a> | Active        | Production           | VSSOP (DGK)   8  | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -            | E37                       |
| OPA2137EA/2K5.A               | Active        | Production           | VSSOP (DGK)   8  | 2500   LARGE T&R      | Yes         | SN                                   | Level-1-260C-UNLIM                | -40 to 85    | E37                       |
| <a href="#">OPA2137P</a>      | Active        | Production           | PDIP (P)   8     | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -            | OPA2137P                  |
| OPA2137P.A                    | Active        | Production           | PDIP (P)   8     | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85    | OPA2137P                  |

| Orderable part number         | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C)  | Part marking<br>(6)         |
|-------------------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|---------------|-----------------------------|
| <a href="#">OPA2137PA</a>     | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -             | (OPA2137P, OPA2137PA)<br>A  |
| OPA2137PA.A                   | Active        | Production           | PDIP (P)   8   | 50   TUBE             | Yes         | NIPDAU                               | N/A for Pkg Type                  | -40 to 85     | (OPA2137P, OPA2137PA)<br>A  |
| <a href="#">OPA2137U</a>      | Obsolete      | Production           | SOIC (D)   8   | -                     | -           | Call TI                              | Call TI                           | -             | OPA<br>2137U                |
| <a href="#">OPA2137U/2K5</a>  | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -             | (2137U, OPA)                |
| OPA2137U/2K5.A                | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85     | (2137U, OPA)                |
| <a href="#">OPA2137UA</a>     | Obsolete      | Production           | SOIC (D)   8   | -                     | -           | Call TI                              | Call TI                           | -40 to 85     | OPA<br>2137U<br>A           |
| <a href="#">OPA2137UA/2K5</a> | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -40 to 85     | (2137UA, OPA)<br>2137U<br>A |
| OPA2137UA/2K5.A               | Active        | Production           | SOIC (D)   8   | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85     | (2137UA, OPA)<br>2137U<br>A |
| <a href="#">OPA4137P</a>      | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | -             | OPA4137P                    |
| OPA4137P.A                    | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | -40 to 85     | OPA4137P                    |
| <a href="#">OPA4137PA</a>     | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | -             | OPA4137P<br>A               |
| OPA4137PA.A                   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | -40 to 85     | OPA4137P<br>A               |
| OPA4137PAG4                   | Active        | Production           | PDIP (N)   14  | 25   TUBE             | Yes         | Call TI                              | N/A for Pkg Type                  | See OPA4137PA | OPA4137P<br>A               |
| <a href="#">OPA4137U</a>      | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -40 to 85     | OPA4137U                    |
| <a href="#">OPA4137U/2K5</a>  | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -40 to 85     | OPA4137U                    |
| OPA4137U/2K5.A                | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85     | OPA4137U                    |
| <a href="#">OPA4137UA</a>     | Obsolete      | Production           | SOIC (D)   14  | -                     | -           | Call TI                              | Call TI                           | -40 to 85     | OPA4137U<br>A               |
| <a href="#">OPA4137UA/2K5</a> | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | Call TI   Nipdau                     | Level-3-260C-168 HR               | -40 to 85     | (OPA4137U, OPA4137UA)<br>A  |

| Orderable part number | Status<br>(1) | Material type<br>(2) | Package   Pins | Package qty   Carrier | RoHS<br>(3) | Lead finish/<br>Ball material<br>(4) | MSL rating/<br>Peak reflow<br>(5) | Op temp (°C) | Part marking<br>(6)            |
|-----------------------|---------------|----------------------|----------------|-----------------------|-------------|--------------------------------------|-----------------------------------|--------------|--------------------------------|
| OPA4137UA/2K5.A       | Active        | Production           | SOIC (D)   14  | 2500   LARGE T&R      | Yes         | Call TI                              | Level-3-260C-168 HR               | -40 to 85    | (OPA4137U, OPA4137<br>UA)<br>A |

- (1) **Status:** For more details on status, see our [product life cycle](#).
- (2) **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.
- (3) **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.
- (4) **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.
- (5) **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.
- (6) **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "-" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

## TAPE AND REEL INFORMATION



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| OPA137N/3K    | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| OPA137NA/3K   | SOT-23       | DBV             | 5    | 3000 | 180.0              | 8.4                | 3.2     | 3.2     | 1.4     | 4.0     | 8.0    | Q3            |
| OPA137UA/2K5  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA2137E/2K5  | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| OPA2137EA/2K5 | VSSOP        | DGK             | 8    | 2500 | 330.0              | 12.4               | 5.25    | 3.35    | 1.25    | 8.0     | 12.0   | Q1            |
| OPA2137U/2K5  | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA2137UA/2K5 | SOIC         | D               | 8    | 2500 | 330.0              | 12.4               | 6.4     | 5.2     | 2.1     | 8.0     | 12.0   | Q1            |
| OPA4137U/2K5  | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |
| OPA4137UA/2K5 | SOIC         | D               | 14   | 2500 | 330.0              | 16.4               | 6.5     | 9.0     | 2.1     | 8.0     | 16.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS



\*All dimensions are nominal

| Device        | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| OPA137N/3K    | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| OPA137NA/3K   | SOT-23       | DBV             | 5    | 3000 | 210.0       | 185.0      | 35.0        |
| OPA137UA/2K5  | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| OPA2137E/2K5  | VSSOP        | DGK             | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| OPA2137EA/2K5 | VSSOP        | DGK             | 8    | 2500 | 366.0       | 364.0      | 50.0        |
| OPA2137U/2K5  | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| OPA2137UA/2K5 | SOIC         | D               | 8    | 2500 | 353.0       | 353.0      | 32.0        |
| OPA4137U/2K5  | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |
| OPA4137UA/2K5 | SOIC         | D               | 14   | 2500 | 353.0       | 353.0      | 32.0        |

## TUBE



\*All dimensions are nominal

| Device      | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|-------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| OPA137U     | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| OPA137U.A   | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| OPA137UA    | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| OPA137UA.A  | D            | SOIC         | 8    | 75  | 506.6  | 8      | 3940   | 4.32   |
| OPA2137P    | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| OPA2137P.A  | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| OPA2137PA   | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| OPA2137PA.A | P            | PDIP         | 8    | 50  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137P    | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137P.A  | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137PA   | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137PA.A | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |
| OPA4137PAG4 | N            | PDIP         | 14   | 25  | 506    | 13.97  | 11230  | 4.32   |

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2025, Texas Instruments Incorporated