

05A4E110.31552018G4.DGN
DO NOT SCALE DRAWING

DWG. NO.
SD-52018-002

F

D

V

C

B

A

F


E

D


C

B

A




後番号 -42*6に適用
MATERIAL NO. SUFFIX -42*6



基板穴推奨寸法
RECOMMENDED P.C.B. LAYOUT
(ジャック取付け側)
(JACK ASS'Y SIDE)

後番号 -44*6に適用
MATERIAL NO. SUFFIX -44*6

製品番号
MATERIAL No.
トレードマーク
TRADE MARK



注) NOTES

- 材質 MATERIAL
ハウジング: ガラス入りポリエステル UL94V-0
HSG.: POLYESTER G.F.15% UL94V-0
ターミナル: リン青銅
TERM.: PHOSPHOR BRONZE
- メッキ仕様 PLATING
接点部: 金メッキ、表参照
CONTACT AREA: GOLD PER TABLE
半田付け部: 錫メッキ 1.0µmMIN.
SOLDER AREA: TIN 1.0 MICROMETER MINIMUM.
下地メッキ: ニッケルメッキ 1.0µmMIN.
UNDERPLATE: NICKEL 1.0 MICROMETER MINIMUM.
- 推奨基板厚: t=1.6±0.05
RECOMMENDED P.C.B. THICKNESS: 1.6±0.05
- 金メッキ厚標示
COLOR CODING TO INDICATE GOLD PLATING
黄色: 0.1µmMIN.
YELLOW: 0.1 MICROMETER MINIMUM.
緑色: 0.38µmMIN.
GREEN: 0.38 MICROMETER MINIMUM.
オレンジ色: 0.76µmMIN.
ORANGE: 0.76 MICROMETER MINIMUM.
無色: 1.27µmMIN.
UNMARKED: 1.27 MICROMETER MINIMUM.
- ハウジングの色は、グレイ。
HOUSING COLOR IS GRAY.
- 本製品は52018-4**5の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 52018-4**5.

4	4	3.05	1.27	52018-4446
			0.76	-4436
			0.38	-4426
			0.1	-4416
4	2	1.02	1.27	52018-4246
ポジション POSITION	極数 CIRCUITS	(A)	金メッキ厚 (µmMIN.) GOLD PLATING THK(MIN.) (µmMIN.)	製品番号 MATERIAL NO.
MODEL NO.		52018-4**6		SHT REV
SCALE 4:1		DESIGN UNITS mm mm INCH	DIMENSIONS: mm mm INCH mm ONLY	REVISE ON CAD ONLY
DRAWN BY & DATE M.NAGATA '04/05/13		TITLE: MODULAR JACK HOUSING ASS'Y -LEAD FREE-		
CHECKED BY & DATE K.TOJO '04/05/13		MOLEX INCORPORATED		
APPROVED BY & DATE M.SASAO '04/05/13				
CAD FILENAME SD-52018-002.S01		MATERIAL NO. SEE CHART	DRAWING NO. SD-52018-002	SHEET NO. 1 OF 1
DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				SIZE B

					新規格作成 RELEASED 04/05/13 DRWN:M.NAGATA CHK:K.TOJO APPR:M.SASAO	DESCRIPTION	MATERIAL 材料	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		
							注参照 SEE NOTES	10 UNDER 未満	±0.2	
								10 OVER 以上	30 UNDER 未満	±0.25
								30 OVER 以上		±0.3
164NO. DRWN: CHK: APPR:	163NO. DRWN: CHK: APPR:	162NO. DRWN: CHK: APPR:	161NO. DRWN: CHK: APPR:	0	REV	WIRE RANGE 適用電線範囲	— # —	ANGLE 角度	±3°	
						INS. RANGE 被覆外径	— # —			