

Bridge Rectifiers

GBPC Series





Features:



- Plastic material
- Integrally moulded heatsink provide very low thermal resistance for maximum heat dissipation
- Surge overload ratings from 300 to 400 A
- Terminals solderable per MIL-STD-202, method 208 (for wire type)
- Typical I_R less than 0.2 μ A
- High temperature soldering guaranteed, 260°C / 10 seconds 0.375 inch (9.5 mm) lead lengths (for wire type)
- Isolated voltage from case to lead over 2,500 V

GBPC-W



Dimensions : Inches (Millimetres)

Bridge Rectifiers



GBPC Series

Maximum Ratings and Electrical Characteristics


Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%

Type Number	Symbol	-005	-01	-02	-04	-06	-08	-10	Unit
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1,000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1,000	
Maximum Average Forward Rectified Current at T _C = 55°C	GBPC15 GBPC25 GBPC35 I _(AV)	15 25 35							A
Peak Forward Surge Current, Single Sine-wave Superimposed on Rated Load (JEDEC method)	GBPC15 GBPC25 GBPC35 I _{FSM}	300 300 400							
Maximum Instantaneous Forward Voltage Drop Per Element at Specified Current	GBPC15 7.5 A GBPC25 12.5 A GBPC35 17.5 A V _F	1.1							V
Maximum DC Reverse Current at Rated DC Blocking Voltage Per Element	I _R	5							mW
Typical Thermal Resistance (Note 1)	R _{θJC}	1.5							°C / W
Operating and Storage Temperature Range	T _J , T _{STG}	-50 to +150							°C


Notes: 1. Thermal resistance from junction to case
2. Suffix "W" - wire lead structure

Ratings and Characteristic Curves (GBPC15005 thru GBPC1510, GBPC25005 thru GBPC2510, GBPC35005 thru GBPC3510)

Maximum Forward Current Derating Curve



Typical Reverse Characteristics Per Bridge Element




Bridge Rectifiers




GBPC Series

Maximum Non-Repetitive Forward Surge Current Per Bridge Element




Typical Forward Characteristics Per Bridge Element



Part Number Table

Description	Part Number
Bridge Rectifier, 15 A, 50 V	GBPC15005W
Bridge Rectifier, 15 A, 100 V	GBPC1501W
Bridge Rectifier, 15 A, 200 V	GBPC1502W
Bridge Rectifier, 15 A, 400 V	GBPC1504W
Bridge Rectifier, 15 A, 600 V	GBPC1506W
Bridge Rectifier, 15 A, 800 V	GBPC1508W
Bridge Rectifier, 15 A, 1000 V	GBPC1510W
Bridge Rectifier, 25 A, 100 V	GBPC2501W
Bridge Rectifier, 25 A, 200 V	GBPC2502W
Bridge Rectifier, 25 A, 400 V	GBPC2504W
Bridge Rectifier, 25 A, 600 V	GBPC2506W
Bridge Rectifier, 25 A, 800 V	GBPC2508W
Bridge Rectifier, 25 A, 1,000 V	GBPC2510W
Bridge Rectifier, 35 A, 50 V	GBPC35005W
Bridge Rectifier, 35 A, 100 V	GBPC3501W
Bridge Rectifier, 35 A, 200 V	GBPC3502W
Bridge Rectifier, 35 A, 400 V	GBPC3504W
Bridge Rectifier, 35 A, 600 V	GBPC3506W
Bridge Rectifier, 35 A, 800 V	GBPC3508W
Bridge Rectifier, 35 A, 1,000 V	GBPC3510W

Typical Junction Capacitance



Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.