


DESIGNED FOR USE WITH RG174/U, 188 & 316 CABLES	
CABLE ENTRY DIAMETER MINIMUM	
FERRULE	.125
HOUSING	.062
CONTACT	.041

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
	B	REV PER ECO-09-013650		10JUN2009	AM	BOB



- 1
- BRASS

2

STAINLESS STEEL

3

BERYLLIUM COPPER

4

PTFE

5

SILICONE RUBBER

6

GOLD PLATE

7

NICKEL PLATE

8

PASSIVATE

9

WIHTE BRONZE

ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 310.1	TEMPERATURE RATING -40° TO +95°
Frequency Range (GHz) DC to 6	Recommended Mating Torque 7-10 In-Lbs	DURABILITY:500 CYCLES
Volt Rating (VRMS MAX) @ Sea Level 250	Mating Characteristics:	.XXX = in XX.X = mm
VSWR 1.18+.02f(GHz)	Insertion (MAX Lbs) N/A	
Insertion Loss (dB MAX) .07 √ f(GHz)	Withdrawal (MIN Oz) N/A	
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750	Force to Engage and Disengage (In-Lbs MAX) 2.0	
Contact Resistance (Milliohms MAX)	Center Contact Captivation	
Center Contact 3.0	Axial (Lbs) 6.0	
Outer Contact 2.0	Radial (In-Oz) N/A	
Cable to Housing 0.5	Cable Retention	
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500	Axial Force (Lbs) 20 Min	
I.R.(Megohms MIN) 5,000	Torque (In-Oz) N/A	
	Weight (Grams) TBD	

1 9	1 9	1 7	4	1 6	1 7	3	5	1056462-3
2 8	2 8	2 8	4	1 6	1 7	3	5	1056462-1
CAP	HOUSING	COUPLING NUT	DIELEC-TRIC	CENTER CONTACT	FERRULE	RETAINING RING	GASKET	TE PN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BB 2/1/93	Tyco Electronics Tyco Electronics Corporation Kunshan,Jiangsu, RPC 215312					
DIMENSIONS: INCHES		CHK -						
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME OSM RIGHT ANGLE CABLE PLUG CRIMP ATTACHMENT				
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD DC 2/3/93				
MATERIAL -		FINISH -		PRODUCT SPEC -		APPLICATION SPEC 408-4659		
				WEIGHT -		SIZE A2 CAGE CODE 00779 DRAWING NO C=1056462		
				CUSTOMER DRAWING		RESTRICTED TO -		
						SCALE 4:1 SHEET 1 of 1 REV C		