

Thursday, 29 November 2012

**HIRSCHMANN®**
Test & Measurement
A BRAND OF SKS

www.sks-kontakt.de

News

contact

sitemap

Login

main menu



Home ▸ sockets ▸ sockets ▸ BIL 20

[home](#)
[products](#)
[skills](#)
[download](#)

online catalogue T&M

[clamp-type test probes](#)
[crocodile clips](#)
[test probes](#)
[oscilloscope test probes](#)
[measuring leads](#)
[plugs](#)
[sockets](#)
 ▸ 2 mm system
 ▸ 2 mm safety system
 ▸ 4 mm system
 ▸ 4 mm safety system
[sets](#)
[miscellaneous](#)

[company](#)
[portrait](#)
[corporate association](#)
[location maps](#)
[fairs and exhibitions](#)
[jobs](#)
[imprint](#)
[terms and conditions](#)

BIL 20

datasheet for BIL 20
article number: 930176104[View Full-Size Image](#)

product description:	order number: 930 176-104
description:	Socket with insulated head and ring for installation in equipment chassis and switchpanels with a wall thickness up to 2 mm. 4 mm diameter tin-plated brass socket, with solder connection.
typ:	BIL 20 green/green
system:	4mm system
order number:	930 176-104
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
norm	IEC 61010
type of contact:	socket (unsprung)
type of termination:	M6 thread, solder
rated voltage:	30 VAC / 60 VDC
rated current:	32 A
Please consider derating curve!	
contact resistance:	5 mOhm
mounting:	screw
material	
contact material:	brass
contact surface material:	Tin
housing material:	PA
connecting nut material:	brass nickel - plated
environmental conditions:	
temperature range:	-25 °C to +85 °C
inflammable class:	
housing (basic material):	UL 94 V - 2
drawing	

search online catalogue



Search

Messetermine

SPS / IPC / DRIVES
29. 11. 2012 - 29. 11. 2012

Newsletter Anmeldung

☒ Test & Measurement

QR-Code



© 2012 www.sks-kontakt.de

Joomla! is Free Software released under the GNU General Public License.