H7N0308LD, H7N0308LS, H7N0308LM

Silicon N Channel MOS FET
High Speed Power Switching

REJ03G1124-0500
(Previous: ADE-208-1535C)
Rev.5.00
Apr 07, 2006

Features

- Low on-resistance
  $R_{DS\ (on)}$ = 3.8 mΩ typ.
- Low drive current
- 4.5 V gate drive device can be driven from 5 V source

Outline

RENESAS Package code: PRSS0004AE-A
(Package name: LDPAK (L))



H7N0308LD

RENESAS Package code: PRSS0004AE-B
(Package name: LDPAK (S)-(1))



H7N0308LS

1. Gate
2. Drain
3. Source
4. Drain

RENESAS Package code: PRSS0004AE-C
(Package name: LDPAK (S)-(2))



H7N0308LM



Absolute Maximum Ratings

(Ta = 25°C)

Item	Symbol	Value	Unit
Drain to source voltage	V_{DSS}	30	V
Gate to source voltage	V_{GSS}	±20	V
Drain current	I_D	70	A
Drain peak current	$I_{D\ (pulse)}$ Note 1	280	A
Body to drain diode reverse drain current	I_{DR}	70	A
Channel dissipation	Pch Note 2	100	W
Channel to case thermal impedance	θ ch-c	1.25	°C/W
Channel to ambient thermal impedance	θ ch-a	89	°C/W
Channel temperature	Tch	150	°C
Storage temperature	Tstg	–55 to +150	°C

Notes: 1. PW ≤ 10 µs, duty cycle ≤ 1%
2. Value at Tc = 25°C

Electrical Characteristics

(Ta = 25°C)

Item	Symbol	Min	Typ	Max	Unit	Test Conditions
Drain to source breakdown voltage	$V_{(BR)\ DSS}$	30	—	—	V	I_D = 10 mA, V_{GS} = 0
Gate to source breakdown voltage	$V_{(BR)\ GSS}$	±20	—	—	V	I_G = ±100 µA, V_{DS} = 0
Gate to source leak current	I_{GSS}	—	—	±10	µA	V_{GS} = ±16 V, V_{DS} = 0
Zero gate voltage drain current	I_{DSS}	—	—	10	µA	V_{DS} = 30 V, V_{GS} = 0
Gate to source cutoff voltage	$V_{GS\ (off)}$	1.0	—	2.5	V	I_D = 1 mA, V_{DS} = 10 V Note 3
Static drain to source on state resistance	$R_{DS\ (on)}$	—	3.8	4.8	mΩ	I_D = 35 A, V_{GS} = 10 V Note 3
		—	6.0	8.5	mΩ	I_D = 35 A, V_{GS} = 4.5 V Note 3
Forward transfer admittance	$\|y_{fs}\|$	54	90	—	S	I_D = 35 A, V_{DS} = 10 V Note 3
Input capacitance	Ciss	—	3350	—	pF	V_{DS} = 10 V
Output capacitance	Coss	—	840	—	pF	V_{GS} = 0
Reverse transfer capacitance	Crss	—	480	—	pF	f = 1 MHz
Total gate charge	Qg	—	52	—	nC	V_{DD} = 10 V
Gate to source charge	Qgs	—	11	—	nC	V_{GS} = 10 V
Gate to drain charge	Qgd	—	10	—	nC	I_D = 70 A
Turn-on delay time	$t_{d\ (on)}$	—	30	—	ns	V_{GS} = 10 V, I_D = 35 A
Rise time	t_r	—	370	—	ns	R_L = 0.29 Ω
Turn-off delay time	$t_{d\ (off)}$	—	80	—	ns	Rg = 4.7 Ω
Fall time	t_f	—	27	—	ns	
Body to drain diode forward voltage	V_{DF}	—	0.93	—	V	I_F = 70 A, V_{GS} = 0
Body to drain diode reverse recovery time	t_{rr}	—	60	—	ns	I_F = 70 A, V_{GS} = 0 di_F/dt = 50 A/µs

Note: 3. Pulse test

Main Characteristics

Power vs. Temperature Derating



Maximum Safe Operation Area



Typical Output Characteristics



Typical Transfer Characteristics



Drain to Source Saturation Voltage vs. Gate to Source Voltage



Static Drain to Source on State Resistance vs. Drain Current



Static Drain to Source on State Resistance vs. Temperature



Forward Transfer Admittance vs. Drain Current



Body to Drain Diode Reverse Recovery Time



Typical Capacitance vs. Drain to Source Voltage



Dynamic Input Characteristics



Switching Characteristics



Reverse Drain Current vs.
Souece to Drain Voltage



Normalized Transient Thermal Impedance vs. Pulse Width



Package Dimensions

Package Name	JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
LDPAK(L)	—	PRSS0004AE-A	LDPAK(L) / LDPAK(L)V	1.40g

Unit: mm



Package Name	JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
LDPAK(S)-(1)	SC-83	PRSS0004AE-B	LDPAK(S)-(1) / LDPAK(S)-(1)V	1.30g

Unit: mm



Package Name	JEITA Package Code	RENESAS Code	Previous Code	MASS[Typ.]
LDPAK(S)-(2)	—	PRSS0004AE-C	LDPAK(S)-(2) / LDPAK(S)-(2)V	1.35g

Unit: mm



Ordering Information

Part Name	Quantity	Shipping Container
H7N0308LD-E	500 pcs	Box (Conductive Sack)
H7N0308LSTL-E	1000 pcs	Taping
H7N0308LMTL-E	1000 pcs	Taping

Note: For some grades, production may be terminated. Please contact the Renesas sales office to check the state of production before ordering the product.

Renesas Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

RENESAS SALES OFFICES

http://www.renesas.com

Refer to "**http://www.renesas.com/en/network**" for the latest and detailed information.

Renesas Technology America, Inc.
450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

Renesas Technology Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

Renesas Technology (Shanghai) Co., Ltd.
Unit 204, 205, AZIACenter, No.1233 Lujiazui Ring Rd, Pudong District, Shanghai, China 200120
Tel: <86> (21) 5877-1818, Fax: <86> (21) 6887-7898

Renesas Technology Hong Kong Ltd.
7th Floor, North Tower, World Finance Centre, Harbour City, 1 Canton Road, Tsimshatsui, Kowloon, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2730-6071

Renesas Technology Taiwan Co., Ltd.
10th Floor, No.99, Fushing North Road, Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology Singapore Pte. Ltd.
1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001

Renesas Technology Korea Co., Ltd.
Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea
Tel: <82> (2) 796-3115, Fax: <82> (2) 796-2145

Renesas Technology Malaysia Sdn. Bhd
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jalan Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: <603> 7955-9390, Fax: <603> 7955-9510

Colophon .6.0