



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDM-211-028 REV: 1.0

2.3" 5*8 LED Lamp Dot Matrix Displays

MODEL NO : ELLM-2181WB/UYC/S400 ECN : Page: 1/5

■ Features :

- Large emitting dot 0.2"diameter.
- Low power/high brightness.

■ Applications:

- Instrument panels
- Digital read out display

■ Description :

- The LM-2181 series are a large emitting area(5.0mm diameter)Lamp sources configured in a 40 dots 5*8 matrix array.
- These device is made with water clear dots and black surface.

PART NO	CHIP		C.C. or C.A.
	Material	Emitted Color	
ELLM-2181WB/UYC/S400	AlGaInP	Super Yellow	C.C.

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936

FAX : 886-2-2267-6244,22676189,22676306

<http://www.everlight.com>




2.3" 5*8 LED Lamp Dot Matrix Displays

MODEL NO ELLM-2181WB/UYC/S400

ECN : Page: 2/5

■ Package Dimension:



■ NOTES:

1. All dimensions are millimeters, tolerance is 0.25mm unless otherwise noted.
 2. Above specification may be changed without notice.
- Supplier will reserve authority on material change for above specification.



2.3" 5*8 LED Lamp Dot Matrix Displays

MODEL NO : ELLM-2181WB/UYC/S400 ECN : _____ Page: 3/5

■ Absolute maximum ratings at Ta = 25°C :

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	50	mA
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature	Tstg	-40to+100	°C
Soldering Temperature	Tsol	260 ± 5	°C
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	120	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	200	mA

■ Electronic optical characteristics :

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Luminous Intensity	Iv	----	137.4	----	mcd	If=2mA
		1430	2290			If=20mA
Peak Wavelength	λ_p	----	591	----	nm	If=20mA
Dominant Wavelength	λ_d	----	589	----	nm	If=20mA
Spectrum Radiation Bandwidth	$\Delta \lambda$	----	15	----	nm	If=20mA
Forward Voltage	Vf	----	2.0	2.4	V	If=20mA
Reverse Current	Ir	----	----	10	μA	Vr=5V



2.3" 5*8 LED Lamp Dot Matrix Displays

MODEL NO : ELLM-2181WB/UYC/S400

ECN : _____

Page:

4/5

■ Reliability test item and condition:

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min ∫ 5 min L : -55°C 30min	50 CYCLE	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min ∫ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	If = 20 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS	0/1



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number :

DDM-211-028

REV: 1.0

2.3" 5*8 LED Lamp Dot Matrix Displays


MODEL NO: ELLM-2181WB/UYC/S400

ECN :

Page: 5/5

■ Typical Electro-Optical Characteristic Curves:

Forward Current Derating Curve
 $T_a=25^\circ$



Spectrum Distribution
 $T_a=25^\circ$

