




FCIconnect.com

Copyright FCI

PRODUCT NUMBER




SEE SHEET 2



mat'l. code NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecm	no	dr	date	tolerances unless otherwise specified		title
A	v12794	RDS		10/23/91	angles	.XX $\pm .01/.3$	VERTICAL SHROUD-RETENTIVE
B	v20223	MRC		3/03/92	linear	.XXX $\pm .005/.13$	3 ROW W/1 GUIDE PINS
C	v23529	JM		11/08/92	$\sigma \pm 2'$	.XXXX $\pm .0020/.051$	
D	v41077	GAH	7/06/94	dr	D. SHEAFFER	8/07/91	scale 1:1
E	v94440	JWS	12/29/99	enr	S. CLARK	10/23/91	FCI
F	M06-0255	AEA	7/07/06	chr	S. CLARK	10/23/91	dwg no
				appd	S. CLARK	10/23/91	sheet 1 of 2 size
sheet index	revision sheet	F	F				A3
		1	2				type Product Customer Drawing

form: A3

PRODUCT NUMBER	DIM.	LENGTH FORMULAS
50429-XXXXX	DIM A	.100/2.54 x NO. OF COLUMNS + 1.05/26.7
	DIM B	.100/2.54 x NO. OF COLUMNS + .750/19.05
	DIM C	.100/2.54 x NO. OF COLUMNS DIVIDED BY 2 - .100/2.54



NOTES:

- PRODUCT NUMBERING CODE:
50429-X YYX
ALWAYS "X"
NO. OF POSITIONS (NOTE 2)
ALWAYS "X"
BASE NUMBER
- THIS PRODUCT IS CONFIGURED IN SIZES OF 20 THRU 122 COLUMNS IN INCREMENTS OF TWO.
i.e.: 20, 22, 24, 26,.....120, 122.
- MATERIAL: GLASS AND MINERAL FILLED THERMOPLASTIC
FLAME RETARDANT PER UL94 V-0 COLOR: BLACK
- MANUFACTURE'S NAME, P/N, AND LOT CODE TO APPEAR ON THIS SURFACE.
- FOR DOCUMENTATION MENU, SEE SPECIFICATION BUS-01-057.
- DIMENSION APPLIES TO HOLES AT END COLUMNS OF EACH PIN FIELD.

mat'l. code NOTE 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ec	no	dr	date	tolerances unless otherwise specified		title
F					angles linear .XX ±.01/.3 .XXX ±.005/.13 .XXXX ±.0020/.051	INCH/MM	VERTICAL SHROUD-RETENTIVE 3 ROW W/1 GUIDE PINS
					0°±2°	scale 1:1	
			dr	D. SHEAFFER	8/07/91	FCI	dwg no
			enr	S. CLARK	10/23/91		sheet 2 of 2 size
			chr	S. CLARK	10/23/91		50428 A3
			appd	S. CLARK	10/23/91		type Product Customer Drawing
sheet index	revision sheet						

form: A3