

LOW PROFILE SHIELDED SMD CHIP POWER INDUCTOR



3.0 x 3.0 x 1.5mm

ASPI-0315FS

RoHS
Compliant

FEATURES:

- Small size and low profile: 1.5mm
- Small DCR and high rated current
- High reliability to mechanical stress
- Magnetically shielded by magnetic powder molding
- Suitable for RoHS reflow profile

APPLICATIONS:

- Mobile phones
- MP3 & 4 and other portable communication equipment
- Digital cameras.

ELECTRICAL SPECIFICATIONS:

Abraco P/N:	ASPI-0315FS Series		
Operating Temperature & Humidity:	-25°C to +120°C (Including self generated heat)		
Storage Temperature & Humidity:	-10°C to +40°C, 30% to 70% RH		

Part Number	Inductance	Inductance Tolerance	DCR	DCR Tolerance	Saturation Current	Temperature Rise Current
Units	µH	%	mΩ	%	A	A
Symbol	L	M, N	DCR		Isat	Irms
ASPI-0315FS-1R0	1.0	N	28	±30%	2.3	2.3
ASPI-0315FS-1R5	1.5	N	37		2.1	2.1
ASPI-0315FS-2R2	2.2	M	58		1.62	2
ASPI-0315FS-2R7	2.7	M	60		1.5	1.95
ASPI-0315FS-3R3	3.3	M	75		1.35	1.8
ASPI-0315FS-4R7	4.7	M	100		1.20	1.6
ASPI-0315FS-5R6	5.6	M	120		1.00	1.4
ASPI-0315FS-6R8	6.8	M	150		0.97	1.3
ASPI-0315FS-100	10	M	220		0.8	1.1
ASPI-0315FS-150	15	M	300		0.65	1
ASPI-0315FS-220	22	M	475		0.55	0.8
ASPI-0315FS-330	33	M	650		0.45	0.7
ASPI-0315FS-390	39	M	850		0.4	0.5
ASPI-0315FS-470	47	M	1100		0.35	0.45
ASPI-0315FS-680	68	M	1700		0.3	0.35
ASPI-0315FS-820	82	M	1900		0.27	0.32
ASPI-0315FS-101	100	M	2100		0.25	0.3

Test Conditions

1. Inductance is measured in HP-4285A Precision LCR Meter.
2. RDC is measured in DU-5011 milli ohm meter.(or equivalent).
3. Isat : Based on inductance change ($\Delta L/L_0 \leq -30\%$)
4. Irms : Based on temperature rise ($\Delta T : 40^\circ\text{C TYP.}$)
5. Test Freq: 100KHz, 1Vrms

OPTIONS AND PART IDENTIFICATION


ASPI-0315FS- -

Inductance Code
Please refer to the
Electrical Spec Table

Tolerance
N: ±30%*
M: ±20%*

Packaging
T2: Tape and Reel (2kpcs / reel)

*N for L = 1.0 ~ 1.5µH
*M for L = 2.2 ~ 100µH



LOW PROFILE SHIELDED SMD CHIP POWER INDUCTOR

ASPI-0315FS





RoHS
Compliant




3.0 x 3.0 x 1.5mm

OUTLINE DRAWING:


Mechanical Dimensions



A	B	C Max.
3.0±0.1	3.0±0.1	1.5




Circuit Schematic



No Polarity

Recommended Land Pattern



Materials

Dimension: mm

No	Part Name	Material
1	Drum core	Ni-Zn Ferrite
2	Terminals	Copper alloy, Sn
3	Coil	Cu/UEW
4	Adhesive	Epoxy base resin
	Magnetic powder	Ni-Zn Ferrite

LOW PROFILE SHIELDED SMD CHIP POWER INDUCTOR



ASPI-0315FS




RoHS
Compliant


3.0 x 3.0 x 1.5mm

➤ TAPE & REEL:

T2: 2,000pcs / reel




A	3.15
B	3.15
K	1.55
F	4
T	0.25



Dimension: mm

➤ REFLOW PROFILE:



ATTENTION: Abracor Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracor's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracor Corporation is required. Please contact Abracor Corporation for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ASPI-0315FS-100M-T3](#) [ASPI-0315FS-220M-T3](#) [ASPI-0315FS-2R2M-T3](#) [ASPI-0315FS-3R3M-T3](#) [ASPI-0315FS-4R7M-T3](#) [ASPI-0315FS-6R8M-T3](#) [ASPI-0315FS-100M-T4](#) [ASPI-0315FS-220M-T4](#) [ASPI-0315FS-2R2M-T4](#) [ASPI-0315FS-3R3M-T4](#) [ASPI-0315FS-4R7M-T4](#) [ASPI-0315FS-6R8M-T4](#)