

Rotary Switch

9-position Low-profile Vertical Type

SRBQ Series



Low-profile rotary switch with unique detent mechanism contributes to a lighter operating feel.

Detector

Push

Slide

Rotary


Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products



Typical Specifications

Items		Specifications
Rating (max.) / (min.) (Resistive load)		0.1A 16V DC/50μA 3V DC
Contact resistance (Initial/After operating life)		50mΩ max./100mΩ max.
Rotational torque		6±3mN·m/13±5mN·m
Operating life	Without load	10,000cycles
	With load	10,000cycles (0.1A 16V DC)


Product Line

Poles	Positions	Changeover angle	Changeover timing	Rotational torque	Actuator configuration	Soldering	Actuator length (mm)	Minimum order unit (pcs.)	Product No.	Drawing No.
1	9	40±3°	Non shorting	6±3mN·m	Flat	Insertion	5.1	2,000	SRBQ090200	1
				13±5mN·m					SRBQ490100	2
				6±3mN·m	Non shaft	Reflow	—	4,800	SRBQ290301	3

Packing Specifications

Taping

Unit:mm



Series	Number of packages (pcs.)			Tape width (mm)	Export package measurements (mm)
	1 reel	1 case /Japan	1 case /export packing		
SRBQ290301	1,200	2,400	4,800	24	406 × 406 × 190

Bulk

Series	Number of packages (pcs.)		Export package measurements (mm)
	1 case /Japan	1 case /export packing	
SRBQ090200	1,000	2,000	506 × 455 × 147
SRBQ490100			

Notes

- Products other than those listed in the above chart are also available. Please contact us for details.
- Please place purchase orders per minimum order unit N (integer).

Dimensions

Insertion Type

Unit:mm


No.	Style	PC board mounting hole dimensions (Viewed from direction A)
1	Standard torque 	
2	Heavy torque 	

Reflow Type

Unit:mm

No.	Style	PC board mounting hole and land dimensions (Viewed from direction A)
3		

Circuit Diagram (Viewed from Direction A)



Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

List of Varieties

Series			SRBD	SRBQ		SRRM	SRBV	SRBM		SRRN	
				Insertion	Reflow type			Rotary	Pulse		
Photo											
Outline specifications	Step angle		36°	40±3°		30±3°			18±3°	30±3°	
	Number of poles		1		1 2 3 4	1	1 2		2 3 4		
Dimensions (mm)		W	10	11.4		—	16.2	12.5		—	
		D		12.4			18.5	10			
		H	1.7		3.5		7.5	11.5			
Operating temperature range			-25℃ to +85℃		-10℃ to +60℃		-40℃ to +85℃			-10℃ to +60℃	
Automotive use			—		—	—			—		
Rating(max.)/(min.) (Resistive load)			1mA 5V DC 50μA 3V DC		0.1A 16V DC 50μA 3V DC	0.25A 30V DC 50μA 3V DC	0.3A 16V DC 50μA 3V DC	0.1A 16V DC 50μA 3V DC	0.15A 12V DC 50μA 3V DC		
Electrical performance	Insulation resistance		100MΩ min. 100V DC			100MΩ min. 500V DC	100MΩ min. 100V DC			100MΩ min. 500V DC	
	Voltage proof		100V AC for 1minute			500V AC for 1minute	100V AC for 1minute			500V AC for 1minute	
	Terminal strength		3N for 1minute	5N for 1minute		10N for 1minute	5N for 1minute				
Mechanical performance	Actuator strength	Rotational direction	—			1N·m	0.6N·m	0.5N·m	—	1N·m	
		Push direction	50N	20N		100N					
	Wobble of actuator		Load at the tip of shaft SRRM : 5N SRBV, SRBQ : 1N		The below table shows for SRBQ (Unit : mm)		The below table shows for SRBV (Unit : mm)		Measuring position from mounting surface	Shaft wobble (max. value)	Applicable mounting dimension
									10mm	0.17 mm	15 mm
									15mm	0.25 mm	20 mm
									Load at the tip of shaft : 5N		
Durability	Operating life without load		10,000cycles 250mΩ max.	10,000cycles 100mΩ max.	10,000cycles 40mΩ max.	10,000cycles 100mΩ max.		30,000 cycles 100mΩ max.	10,000cycles 70mΩ max.		
	Operating life with load Load : (at rated load)		10,000cycles 250mΩ max.	10,000cycles 100mΩ max.	10,000cycles 60mΩ max.	10,000cycles 150mΩ max.		10,000cycles 100mΩ max.			
Environmental performance	Cold		-40±2℃ for 500h		-20±2℃ for 96h						
	Dry heat		85±2℃ for 500h		85±2℃ for 96h						
	Damp heat		60±2℃, 90 to 95%RH for 500h		40±2℃, 90 to 95%RH for 96h						
Soldering	Manual soldering		—		350±10℃ 3 ⁺ ±s	350±5℃ 3s max.	350±10℃, 3 ⁺ ±s				
	Dip soldering		—		260±5℃ 5±1s	—	260±5℃ 10±1s		260±3℃ 5s max.	260±5℃ 10±1s	
	Reflow soldering		Please see P.193			—					
Page			179	181	188	186	183		190		

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

● Rotary Switches Shaft Style	192
● Rotary Switches Soldering Conditions	193
● Rotary Switches Attached Parts	194
● Rotary Switches Cautions	195


Notes

● marks in "Available for automotive use" indicate that all of the series products can work at the operating temperature range from -40°C to +85°C.


Soldering Conditions

Example of Reflow Soldering Condition

1. Heating method: Double heating method with infrared heater.
2. Temperature measurement: Thermocouple 0.1 to 0.2 ϕ CA (K) or CC (T) at soldering portion (copper foil surface) .A heat resisting tape should be used for fixed measurement.
3. Temperature profile



Series (Reflow type)	A (°C) 3s max.	B (°C)	C (°C)	D (s)	E (s)	F (s)
SRBQ	240	230	150	120	—	—



Series (Reflow type)	A (°C) 3s max.	B (°C)	C (s)	D (°C)	E (°C)	F (s)
SRBD	260	230	40	180	150	120

Notes

1. The condition mentioned above is the temperature on the mounting surface of a PC board. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the PC board's material, size, thickness, etc. The above-stated conditions shall also apply to switch surface temperatures.
2. Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.