


Resettable Fuse



Specifications:

Applications	: Wide variety of electronic equipment
Product Features	: Very low resistance, very high hold current, solid state, Radial leaded product ideal for up to 16V
Max. Voltage	: 16V
Temperature Range	: -40°C to +85°C

Electrical Characteristics (23°C)

Hold Current	Trip Current	Max. Time to trip	Max. Current	Rated Voltage	Typical Power	Resistance		Part Number
						R Min.	R1 Max.	
I_H , A	I_T , A	at $5 \times I_H$	I Max., A	V Max., V DC	P_d , W	ohms	ohms	
2.5	4.7	5	100	16	1	0.022	0.053	MC36177
6	10.2	5.8			2.8	0.009	0.033	MC36178
7	11.9	8			3	0.006	0.021	MC36179
8	13.6	9				0.005	0.018	MC36180
9	15.3	12			3.3	0.004	0.015	MC36181
10	17	12.5				0.003	0.012	MC36176

I_H	= Hold current-maximum current at which the device will not trip at 23°C still air
I_T	= Trip current-minimum current at which the device will always trip at 23°C still air
V_{MAX}	= Maximum voltage device can withstand without damage at its rated current
I_{MAX}	= Maximum fault current device can withstand without damage at rated voltage (V maximum)
P_d	= Typical power dissipated from device when in the tripped state in 23°C still air environment
R_{MIN}	= Minimum device resistance at 23°C
$R1_{MAX}$	= Maximum device resistance at 23°C 1 hour after tripping


Physical specifications:

Lead Material	: Tin plated copper,
Soldering Characteristics	: MIL-STD-202, Method 208E
Insulating Coating	: Flame retardant epoxy

Resettable Fuse




Production Dimensions



A	B	C	D	E	F	Part Number	Figure
Max.	Max.	Typical	Min.	Max.	Typical		
8.9	12.8	5.1	7.6	3	1.2	MC36177	1
10.7	17.1					MC36178	2
11.2	19.7					MC36179	2
12.7	20.9					MC36180	2
14	21.7					MC36187	2
16.5	24.1					MC36176	2

Dimensions : Millimetres


Thermal Derating Curve



Resettable Fuse



Typical Time-To-Trip at 23°C



A=MC36177

E=MC36178

F=MC36179

G=MC36180

H=MC36181

I=MC36176

Part Number Table

Description	Part Number
Radial Leaded PTC Resettable Fuse	MC36177
	MC36178
	MC36179
	MC36180
	MC36181
	MC36176

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.