

PolySwitch® PTC Devices Overcurrent Protection Device

PRODUCT: TRF250-080U

DOCUMENT: SCD26315
REV LETTER: G
REV DATE: MAY 11, 2011
PAGE NO.: 1 OF 1

Specification Status: Released

Operating Conditions at 20°C:

Maximum Continuous Operating Voltage (V_{MCO}): 60V_{DC}
Maximum Interrupt Current (I_{INT}): 3A_{RMS}

Fault Ratings at 20°C:

250V_{RMS}, 3A, 10 applications

Additional Info at 20°C:

- Resistance matched: n/a
- Lightning withstand: 1.0 kV per ITU-T K.20, K.21
- Helps equipment meet ITU-T K.20, K.21 Recommendations

Lead Material:

22 AWG Sn-Plated Copper (0.64 mm [0.025"] nominal diameter)

External Coating Material:

None

Marking:

None




TABLE I. DIMENSIONS:

	A		B		C		D		E
mm:	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	NOM
in*:	--	4.8	--	9.3	--	3.8	4.7	--	5.0
	--	(0.19)	--	(0.37)	--	(0.15)	(0.19)	--	(0.20)

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS @ 20°C:

HOLD CURRENT (A)	TRIP CURRENT (A)	RESISTANCE (Ω)			TIME TO TRIP(Sec) @ 0.35A		OPERATING TEMPERATURE (°C)		TRIPPED POWER DISSIPATION (W) @ 60V _{DC}	
		R MIN	R MAX	R ₁ MAX*	TYP	MAX	MIN	MAX	TYP	MAX
0.080	0.160	14.0	20.0	33.0	2.5	4.0	-40	85	0.6	0.7

*Maximum device resistance at 20°C measured 1 hour post trip and 24 hours post reflow

TABLE III. APPLICABLE PART DESCRIPTIONS:

PART DESCRIPTION	PACKAGING TYPE	NOTES
TRF250-080U	Bulk	N/A

Agency Recognitions:
Reference Documents:
Precedence:
Effectivity:
CAUTION:

UL File #E74889, CSA File #78165C, TUV
PS300, ITU-T K.20/K.21
This specification takes precedence over documents referenced herein.
Reference documents shall be the issue in effect on the date of invitation for bid.
Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant

ELV Compliant

Pb-Free

Directive 2002/95/EC
Compliant

Directive 2000/53/EC
Compliant

