

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [76020-5004](#)
Status: **Active**
Overview: GbX I-Trac™ Backplane Connector System
Description: GbX I-Trac™ Right Angle Receptacle Module, 1.85mm by 3.70mm Pitch, Right Guide 7 Row, 4 Columns, 56 Circuits, Lead-Free

Documents:

[3D Model](#) [Product Specification PS-75710-999 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Backplane Connectors
Series [76020](#)
Application Coplanar, Daughtercard
Component Type PCB Receptacle
Overview [GbX I-Trac™ Backplane Connector System](#)
Product Name GbX I-Trac™
UPC 822350969338

Physical

Circuits (Loaded) 56
Circuits (maximum) 56
Color - Resin Black
Durability (mating cycles max) 200
First Mate / Last Break No
Flammability 94V-0
Guide to Mating Part Yes
Keying to Mating Part None
Material - Metal High Performance Alloy (HPA)
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 9.716/g
Number of Columns 4
Number of Pairs 4, Open Pin Field
Number of Rows 7
Orientation Right Angle
PC Tail Length 2.00mm
PCB Locator Yes
PCB Retention Yes
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 1.85mm, 3.70mm
Pitch - Termination Interface 1.00mm, 2.70mm
Plating min - Mating 0.762µm
Plating min - Termination 0.762µm
Polarized to PCB Yes
Stackable No
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -55°C to +80°C
Termination Interface: Style Through Hole - Compliant Pin

Electrical



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[76020Series](#)

Mates With

[76015](#) GbX I-Trac™ Vertical Header
Module.

Use With

[78234](#) GbX I-Trac™ Right Angle Power
Header. [76153](#) Pirate Cannon Wide Guide
Module

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Press-In Tool for Right Angle Receptacle and	0622018610

Current - Maximum per Contact	1.0A	Header 7-Row, 4-
Data Rate	12.0 Gbps	Column
Real Signals (per 25mm)	48	Daughter Card
Shield Type	N/A	Signal Module
Shielded	No	Removal Tool
Voltage - Maximum	120V AC (RMS)/DC	
Material Info		
Reference - Drawing Numbers		
Product Specification	PS-75710-999	
Sales Drawing	SD-76020-004	

This document was generated on 04/22/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION