



AMP WIRE RANGE	 E13288 Listed
22-16 AWG STRANDED	22-16 AWG STRANDED

 LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

Technical drawing of a mechanical part with dimensions and tolerances:

- Overall length: 11.07 MAX [.436]
- Distance from left face to start of step: 6.35 MIN [.250]
- Left face diameter: 1.65 MIN DIA [.065]
- Right face diameter: 0.79 ± 0.05 [.031 $\pm$.002]
- Overall length including right face: 14.58 MAX [.574]

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -		DR 2-3-93 TA BRINKMAN	AMP AMP Incorporated Harrisburg, PA 17105-3508		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE	MATERIAL COPPER PER ASTM B-152 ANNEALED	CHK 2-3-93 DA PATTERSON	NAME TERMINAL, RING TONGUE, BUDGET			
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² [509-3,260] CIR MILS STRANDED		APPD 2-3-93 DE MILLER				
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AND NOT TO BE REPRODUCED OR COPIED AND FOR CONTROLLING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727	APPD 2-3-93 JL HECKLEY	PRODUCT SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO C-31264
					APPLICATION SPEC -	WEIGHT -	SCALE 10:1	SHEET 1 OF 1