



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		D	REVISED PER ECO-08-027222	05NOV08	HMR	FD


D




44 POS.



52 POS.



68 POS.




84 POS.

RECOMMENDED HOLE LAYOUT
TOLERANCE: ±0.05[.002] UNLESS OTHERWISE NOTED

NOTES:


- 1 MATERIALS:
CONTACT: COPPER ALLOY, 0.004572[.000180] MIN TIN PLATE
OVER 0.00127[.000050] MIN NICKEL.
INSULATOR: PPS, 40% GLASS FILLED, UL 94V-O

- 2 DATE CODE (PER BELOW) TO BE LASER CODED
AND CENTERED ON THIS SURFACE.




3. UL RECOGNITION E320916.

C



B



A

PART NO.	POS.	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"
1571541-1	44	22.61 [.890]	16.76 [.660]	12.70 [.500]	17.78 [.700]
1571541-2	52	25.15 [.990]	19.30 [.760]	15.24 [.600]	20.32 [.800]
1571541-3	68	30.23 [1.190]	24.38 [.960]	20.32 [.800]	25.40 [1.000]
1571541-4	84	35.31 [1.390]	29.46 [1.160]	25.40 [1.000]	30.48 [1.200]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MURREN 26AUG2003	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK K. WRIGHT 24APR03				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. WRIGHT 24APR03	NAME OUTLINE DRAWING PLCC SOCKET			
0 PLC ± - 1 PLC ± 1 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC 108-38000 APPLICATION SPEC	SIZE A2			
MATERIAL 1		FINISH 1	CAGE CODE 00779			
			DRAWING NO 1571541			
			RESTRICTED TO -			
			SCALE 2:1			
			SHEET 1 of 1			
			REV D			