

# Digital Multimeter

## Solar Powered



### Specifications

Basic Functions	Range	Best Accuracy
DC Voltage	400 mV / 4 V / 40 V / 400 V / 1,000 V	$\pm (0.8\% + 1)$
AC Voltage	4 V / 40 V / 400 V / 750 V	$\pm (1\% + 5)$
DC Current	400 mA / 4,000 mA / 40 mA / 400 mA / 4 A / 10 A	$\pm (1\% + 2)$
AC Current		$\pm (1.5\% + 5)$
Resistance	400 W / 4 kW / 40 kW / 400 kW / 4 MW / 40 MW	$\pm (1\% + 2)$
Capacitance	40 nF / 400 nF / 4 mF / 40 mF / 100 mF	$\pm (3\% + 5)$
Frequency	10 Hz - 10 MHz	$\pm (0.1\% + 3)$
<b>Special Functions</b>		
Fused 10 A range	-	✓
mA Fuse	-	Traditional
Auto ranging	-	✓
Diode	-	
Continuity buzzer	-	
Relative mode	-	
Data hold	-	
Full icon display	-	
Sleep mode	-	
Low battery display	-	
Input impedance for DC Voltage measurement	Around 10 MW	
Maximum display	3,999	



# Digital Multimeter

## Solar Powered



### General Characteristics

Power	Charging at 230 V ac or 12-36 V ac / dc
LCD size	60 × 26 mm
Product colour	Orange + Grey
Product net weight	340 g
Product size	179 × 88 × 39 mm
Standard accessories	Test lead, English manual, holster
Standard individual	Gift box
Standard quantity per	40 pieces
Standard carton measurement	598 × 418 × 340 mm (Around 0.085 CBM per standard carton)
Standard carton gross	23 kg

Specifications and other information are subject to change without further notice

### Part Number Table

Description	Part Number
Multimeter, Digital, Solar Powered	72-9375

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA™ is the registered trademark of the Group. © Premier Farnell plc 2011.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)  
[www.cpc.co.uk](http://www.cpc.co.uk)  
[www.mcmelectronics.com](http://www.mcmelectronics.com)

