




THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
AD	39	P	LTR	DESCRIPTION	DATE	APVD
		-	-	SEE SHEET 1	-	-

- 1

CONTACT AREA PLATED WITH .000030 GOLD;
SOLDER CLIPS AND LEADS PLATED WITH .000150 TIN-LEAD;
ALL OVER .000050 NICKEL
- 2

POINT OF MEASUREMENT FOR GOLD THICKNESS
IS .030 FROM MATING END OF CONTACT
- 3

HOUSING: THERMOPLASTIC, COLOR-BLACK.
CONTACT: COPPER ALLOY.
SOLDER CLIP: PHOSPHOR BRONZE
- 4

CONTACT AREA PLATED WITH .000030 GOLD;
SOLDER CLIPS AND LEADS PLATED WITH .000150 TIN
ALL OVER .000050 NICKEL
- 5

PRELIMINARY - NOT FOR PRODUCTION
- 6

ROHS 2002/95/EC COMPLIANT
- 7

FINISH, .000001 MIN. GOLD ON GOLD PLATED AREA, .000150-.000250
MATTE TIN LEAD ON TIN PLATE AREA, UNDER PLATING SHOULD BE .000050-.000100
NICKEL ON ENTIRE CONTACT.
- 8

SUPERCEDED BY 5-103911-5
- 9


OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 10

OBSOLETE
- 11

FINISH: .000001 MIN GOLD ON GOLD PLATED AREA. .000150-.000250 MATTE
TIN ON TIN PLATED AREA. UNDER PLATING: .000050-.000100 NICKEL ON ENTIRE CONTACT

1 6	-	.050	.450	.550	11	.644	24	5	7-103911-9
	1.175	.050	2.350	2.450	49	2.544	100		7-103911-8
	-	.050	.600	.700	14	.794	30	5	7-103911-7
	.925	.050	1.850	1.950	39	2.044	80	5	7-103911-6
	-	.050	.850	.950	19	1.044	40	5	7-103911-5
	.675	.050	1.100	1.200	24	1.294	50	5	7-103911-4
	-	.050	1.350	1.450	29	1.544	60	5	7-103911-3
4 6	-	.050	.350	.450	9	.544	20		7-103911-2
	-	.100	-	.200	4	.294	10	5	7-103911-1
	-	.050	.450	.550	11	.644	24	10	5-103911-9
	1.175	.050	2.350	2.450	49	2.544	100		5-103911-8
	-	.050	.600	.700	14	.794	30		5-103911-7
	.925	.050	1.850	1.950	39	2.044	80	9	5-103911-6
	-	.050	.850	.950	19	1.044	40		5-103911-5
FINISH	-	.050	1.100	1.200	24	1.294	50		5-103911-4
	.675	.050	1.350	1.450	29	1.544	60		5-103911-3
	-	.050	.350	.450	9	.544	20		5-103911-2
	-	.100	-	.200	4	.294	10		5-103911-1
	F	E	D	C	B	A	NO OF POSN	PART NUMBER	

7	-	.050	.450	.550	11	.644	24	5	2-103911-9
	1.175	.050	2.350	2.450	49	2.544	100	5	2-103911-8
	-	.050	.600	.700	14	.794	30	5	2-103911-7
	.925	.050	1.850	1.950	39	2.044	80	5	2-103911-6
	-	.050	.850	.950	19	1.044	40	5	2-103911-5
	.675	.050	1.100	1.200	24	1.294	50	5	2-103911-4
	-	.050	.350	.450	9	.544	20	5	2-103911-2
1	-	.100	-	.200	4	.294	10		2-103911-1
	-	.050	.450	.550	11	.644	24	10	103911-9
	1.175	.050	2.350	2.450	49	2.544	100		103911-8
	-	.050	.600	.700	14	.794	30		103911-7
	.925	.050	1.850	1.950	39	2.044	80	9	103911-6
	-	.050	.850	.950	19	1.044	40	8	103911-5
	.675	.050	1.100	1.200	24	1.294	50		103911-4
FINISH	-	.050	1.350	1.450	29	1.544	60		103911-3
	-	.050	.350	.450	9	.544	20		103911-2
	-	.100	-	.200	4	.294	10		103911-1
FINISH	F	E	D	C	B	A	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D CLOUSER 3-20-86	TE Connectivity				
		CHK J S STARON 3-20-86					
DIMENSIONS: INCHES		APVD J S STARON 3-20-86	NAME				
		PRODUCT SPEC 108-1093	RECEPTACLE ASSEMBLY, RIGHT ANGLE, AMPMODU System 50				
		APPLICATION SPEC 114-25031					
MATERIAL -		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=103911	RESTRICTED TO -	
SEE TABLE			CUSTOMER DRAWING		SCALE 4:1	SHEET 2 of 2	REV M