





	014	024	036	050
A	1.728	2.154	2.667	3.264
	43.90	54.70	67.75	82.90
B	0.992	1.417	1.925	2.624
	25.20	36.00	48.90	64.10
C	1.417	1.843	2.352	2.947
	36.00	46.80	59.74	74.85



MATERIAL:

INSULATION: GLASS-FILLED THERMOPLASTIC
 UL RATED 94V-0, 230°C PROCESS TEMP.
 CONTACTS: COPPER ALLOY
 CONTACT PLATING: GOLD FLASH IN THE MATING AREA
 BRIGHT TIN IN THE SOLDER AREA
 SHELL: STEEL, NICKEL PLATED

ELECTRICAL:

CURRENT RATING: 1 AMP
 VOLTAGE RATING: 1,000V AC r.m.s.
 INSULATION RESISTANCE: 1,000MegOhms Min. @ 500VDC
 CONTACT RESISTANCE: 30MilliOhms Max.
 OPERATING TEMPERATURE: -55°C TO +125°C

111-YYY-213L001

SERIES
POSITIONS014
024
036
050

GENDER

2 = FEMALE

TERMINATION
1 = DIP SOLDERRoHS COMPLIANT
L = LOW TEMP. PROCESS

SHELL PLATING

3 = NICKEL

HARDWARE

00 = NO HARDWARE

PLATING
1 = GOLD FLASH

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
 THE PROPERTY OF NorComp AND SHALL NOT
 BE REPRODUCED, COPIED OR USED AS THE
 BASIS FOR THE MANUFACTURE OF SALE OF
 APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINSDATE:
09-15-05

CHECKED:

DATE:


SCALE: NONE SHEET OF 1 2 REV 9

DWG NO. 111-YYY-213L001


NorComp

RoHS COMPLIANT


	014	024	036	050
C	1.417	1.843	2.352	2.947
	36.00	46.80	59.74	74.85




14 POSITION



36 POSITION



24 POSITION



50 POSITION

NOTEDIMENSION "C" =
CENTER TO CENTER OF MOUNTING HOLES
CENTER OF RADII
OVERALL LENGTH OF CUTOUT

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OF SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
01-14-11

CHECKED:

DATE:

SCALE:
NONE

OF
2 2

REV
9

DWG NO.

111-YYY-213L001

NorComp