








REV.	DATE	DESCRIPTION
A	08/30/00	MODIFY BARREL O.D. DIMENSION
B	05/22/05	UPDATE DRAWING FORMAT/ MODIFY PLATING SPEC



NOTE:
USE .151 HEX CRIMP DIE TO
TERMINATE FERRULE TO CABLE.
— CONNEX TOOL 47-10160
— IDEAL TOOL 36-489

8						UNLESS OTHERWISE SPECIFIED MEASUREMENTS ARE IN INCHES AND DECIMALS THEREOF. DIMENSIONS FOR MATERIALS ARE: UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MATERIALS ARE: D.5 - .001mm ± 0.020mm B - .30mm ± 0.40mm 30 - 120mm ± 0.60mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR ANGLES ARE: .020 - .315 = ± 0.007° .315 - 1.180 = ± 0.015° 1.180 - 4.724 = ± 0.030°
7						
6	FERRULE	BRASS	NEKOCOTE	1		
5	HEX NUT	BRASS	NEKOCOTE	1		
4	BARREL	BRASS	NEKOCOTE	1		
3	CONTACT PIN	BRASS	COLD	1		
2	INSULATOR	TEFLON	NATURAL	1		
1	BODY	BRASS	NEKOCOTE	1		
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	
					APPROVALS	DATE
					DRAWN G.R.S.	05/22/05
					CHECKED	
					ISSUED	
					SHEET 1 OF 1	
					PART NO.	172171
					DWG. NO.	172171.DWG
					REV.	B
					SIZE	A
					SCALE	1A

Amphenol Connex

N CRIMP PLUG
(FOR RG-316/U DOUBLE BRAID CABLE)