


PNP Silicon Planar Epitaxial Transistor

Dimensions SOT-23



1	BASE
2	EMITTER
3	COLLECTOR

Absolute Maximum Ratings (Ta=25°C unless specified otherwise)

Desription	SYMBOL	VALUE	UNITS
Collector-Emitter Voltage ($V_{BE} = 0V$)	$(-V_{CES})$	50	V
Collector Emitter Voltage (open base) $-I_C = 10mA$	$(-V_{CEO})$	45	V
Emitter Base Voltage	$(-V_{EBO})$	5	V
Collector Current (DC)	$(-I_C)$	500	mA
Collector Current - Peak	$(-I_{CM})$	1000	mA
Emitter Current - Peak	I_{EM}	1000	mA
Base Current - (DC)	$(-I_B)$	100	mA
Base Current - Peak	$(-I_{BM})$	200	mA
Total Power Dissipation up to $T_{amb} = 25^\circ C$	P_{tot}	250	mW
Storage Temperature	T_{stg}	(-55 to +150)	°C
Junction Temperature	T_J	150	°C

Thermal Resistance

From junction to ambient	$R_{th(j-a)}$	500	k / W
--------------------------	---------------	-----	-------

Electical Characteristics (at Ta = 25°C unless otherwise specified)

	Symbol	Test Conditions		Typ.	Unit
Collector Cut off Current	I_{CBO}	($-V_{CB} = 20V, I_E = 0, T_J = 25^{\circ}C$) ($-V_{CB} = 20V, I_E = 0, T_J = 150^{\circ}C$)	< <	100 5	nA μA
Emitter cut-off current	I_{EBO}	$I_C = 0, V_{EB} = 5V$	<	10	μA
Base Emitter on Voltage	V_{BE}	($-I_C = 500\text{ mA}, -V_{CE} = 1V$)	<	1, 2V	V
Saturation Voltage	V_{CEsat}	($-I_C = 500\text{ mA}, I_B = 50mA$)	<	700	mV
DC Current Gain	h_{FE}	($-I_C = 500\text{ mA}, -V_{CE} = 1V$) ($-I_C = 100\text{ mA}, -V_{CE} = 1V$)	> -	40 100 to 600	
Collector Capacitance	C_C	$I_E = I_E = 0, -V_{CB} = 10V,$ $f = 1MHz$	typ.	5	pF
Transition Frequency	f_T	($-I_C = 10mA, -V_{CE} = 5V$) $f = 100MHz$	>	100	MHz