

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0877057030

Status: Planned for Obsolescence

Description: 1.00mm (.039") Pitch DDR-II DIMM 240 Circuits Socket, Vertical, 1.8 Voltage, 2.54mm (.100") Tail Length, White Latches, Nylon 6/6 Glass-filled, Green Housing, Gold (Au) Flash, Beveled Metal Pins Width 2.70mm (.106"), Lead Free

Documents:

- 3D Model
- Drawing (PDF)
- Product Specification PS-87705-801 (PDF)
- Test Summary TS-87705-801 (PDF)
- RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Memory Module Sockets
Series	87705
Comments	White Latches Insertion Force: 10Kg (98N) Max. Beveled Metal Pin Width: 2.70mm (.106")
Component Type	Socket
JEDEC Outline	MO-237
Product Name	DDR2 DIMM

Physical

Circuits (Loaded)	240
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	Yes
Material - Plating Mating	Gold
PC Tail Length	2.54mm (.100")
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Pitch - Mating Interface	1.00mm (.039")
Temperature Range - Operating	-10°C to +85°C
Termination Interface: Style	Through Hole


Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	30V
Voltage Key	1.8V, Center

Material Info

Reference - Drawing Numbers

Product Specification	PS-87705-801
Sales Drawing	SD-87705-801
Test Summary	TS-87705-801



EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

87705Series

Mates With

JEDEC standard 1.27mm modules