

Fuse holder terminal blocks


for 6,35 x 25,4 mm 1/4 x 1 in.
and 6,35 x 32 mm 1/4 x 1 1/4 in. fuses

Compression clamp

┌ ┐ DIN 1 - DIN 3

MU 10/13.SF2


Spacing 13 mm (.512")



13 mm block for blown fuse indicator (to be ordered separately).

MU 10/14,5.SF2

Spacing 14,5 mm (.571")



14,5 mm block for blown fuse indicator (to be ordered separately).



Color	Type	Part numbers
Black V0	♣ MU 10/13.SF2	0199 014.11



Color	Type	Part numbers
Black V0	♣ MU 10/14,5.SF2	0199 013.10

Characteristics

Wire size		NFC DIN	UL	CSA
Compression clamp	Solid wire	0,5-16 mm ²	22-10 AWG	6 AWG max.
	Stranded wire	0,5-10 mm ²	22-10 AWG	6 AWG max.

Voltage			
Rated	750 V Gr.C (1)	600 V (1)	600 V (1)
Pulse			
Pollution degree			

Current			
Rated	16 A	16 A	16 A

Wire size			
Rated / Gauge	10 mm ²	10 AWG	6 AWG
Wire stripping length	Recomm. screwdriver	Recomm. torque	Protection
12 mm .47"	5,5 mm .22"	1,2-1,4 Nm 10.6-12.3 lb.in	IP 20 NEMA 1

Characteristics

Wire size		NFC DIN	UL	CSA
Compression clamp	Solid wire	0,5-16 mm ²	22-10 AWG	6 AWG max.
	Stranded wire	0,5-10 mm ²	22-10 AWG	6 AWG max.

Voltage			
Rated	750 V Gr.C (1)	600 V (1)	600 V (1)
Pulse			
Pollution degree			

Current			
Rated	16 A	16 A	16 A

Wire size			
Rated / Gauge	10 mm ²	10 AWG	6 AWG
Wire stripping length	Recomm. screwdriver	Recomm. torque	Protection
12 mm .47"	5,5 mm .22"	1,2-1,4 Nm 10.6-12.3 lb.in	IP 20 NEMA 1

End stop	┌	th. 9,1 mm	BADL V0	0199 408.02
End stop	┐	th. 9,1 mm	BAM	0103 002.26
Other end stops : See Accessories section				
Rail	┌	35 x 7,5 x 1	PR30 prepunched	0173 220.05
Rail	┐	35 x 15 x 2,3	PR4	0168 500.12
Rail	┌	35 x 15 x 1,5	PR5 prepunched	0101 598.26
Rail	┐	32 x 15	PR1Z2	0163 050.04
Other rails : See Accessories section				

Notes

The use of some accessories may decrease the block's voltage rating. For more information, consult us.

Accessories

Type Part numbers

FEM13U	V0	th. 1,5 mm	0199 635.24
FC2		DIA. 2 mm	0007 865.26
FC4		DIA. 4 mm	0167 860.01
AL2		DIA. 2 mm	0163 043.21
AL3		DIA. 3 mm	0163 261.00
AL4		DIA. 4 mm	0163 262.01
BJS131		10 poles	0175 991.11
VJS11			0163 394.26
RDJ11			0168 783.01
FU633		6,35 x 32	
		0,25 A	0168 554.03
		0,63 A	0168 555.04
		1 A	0168 556.05
		1,6 A	0168 557.06
		2,5 A	0168 558.17
		4 A	0168 559.10
		6,3 A	0168 560.15
		10 A	0168 561.02
		16 A	0168 562.03
LEN	Neon	110 - 230 VAC	0167 075.25
	Neon	480 VAC	0103 909.00
Leakage current with neon indicator			
< 0,5 mA (110 & 480 VAC)			
< 0,7 mA (230 VAC)			

Type Part numbers

FC2		DIA. 2 mm	0007 865.26
FC4		DIA. 4 mm	0167 860.01
AL2		DIA. 2 mm	0163 043.21
AL3		DIA. 3 mm	0163 261.00
AL4		DIA. 4 mm	0163 262.01
FU633		6,35 x 32	
		0,25 A	0168 554.03
		0,63 A	0168 555.04
		1 A	0168 556.05
		1,6 A	0168 557.06
		2,5 A	0168 558.17
		4 A	0168 559.10
		6,3 A	0168 560.15
		10 A	0168 561.02
		16 A	0168 562.03
LEN	Neon	110 - 230 VAC	0167 075.25
	Neon	480 VAC	0103 909.00
Leakage current with neon indicator			
< 0,5 mA (110 & 480 VAC)			
< 0,7 mA (230 VAC)			

(11) (17) Sides of block (26)
Note : (1) Insulation voltage of terminal block - operating voltage : In accordance with fuse rating.