






NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50mA @ 12VDC
5. OPERATING FORCE: 260 ± 50 gms
- ▲ 6. TRAVEL: $0.35\text{mm} \pm 0.1$
7. CONTACT RESISTANCE: 100 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
9. INSULATION RESISTANCE: 100M OHMS MIN. AT 500VAC
11. DIELECTRIC STRENGTH: 250VAC FOR 1 MINUTE
- ▲ 10. PACKAGING: 500 PCS. PER TAPE & REEL
11. 2002/95/EC (ROHS) COMPLIANT
12. ▲ DENOTES CRITICAL PARAMETER



ISOMETRIC



E-SWITCH®



TITLE TL3300AF260Q

SCALE 2:1

DATE 7/9/2010

DR BLR

DWG N301103

REV B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

B	19309	ADJUST DIM FOR TERMINAL WIDTH	9/20/10	BLR
A	19149	Released For Production	4/30/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY