


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2000
 © COPYRIGHT 2000 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS | | | |
|-----|------|-------------|------------------------------|----------|-------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| A1 | | B2 | RELEASED ASPER ECR-09-010234 | 6-May-09 | CJ TS |




PN 0-1 As Shown

Contact arrangement
view from connecting side




NOTES

- SUITABLE CRIMP CONTACTS: SERIES HSS
CUSTOMER DRAWING: 1105150
OUTER DIMENSIONS OF INSULATION: MAX. Ø9.5mm
- SUITABLE MODULE FIXING FRAME: SERIES HVS SIZE 3 TO 8
CUSTOMER DRAWING: 1103250
- SUITABLE INSERTION TOOL:
CUSTOMER DRAWING: 1102855
- SUITABLE EXTRACTION TOOL:
CUSTOMER DRAWING: 1102855
- STANDARDS:
DIN EN 61984; DIN EN 60664-1
- POLARIZATION RIPS
- MARKING OF POLARIZATION ACCORDING TO MARKING OF MODULE FRAME
- PACKAGING:
10 PIECES IN A CARTON



Contact arrangement
view from termination side



| QTY | DESCRIPTION | MATERIAL | COLOR | ITEM |
|--------------------------|-------------|----------|------------|------|
| 1 | MALE INSERT | PBT-GF10 | LIGHT-GREY | 1 |
| PN 0-1 / HVS-HSS.2.STI.C | | | | |

| | | | | | |
|--|--|--|--|--|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. | | DWN 20.02.2006 SCHNEIDER | | Tyco Electronics AMP GmbH 53757 Sankt Augustin, Germany | |
| DIMENSIONS: mm | | TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 8075 DIN ISO 2768 mH-E DIN 16901-120 | | NAME MALE INSERT HVS-HSS.2.STI.C | |
| | | 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± | | PRODUCT SPEC 108-74082 | |
| MATERIAL | | FINISH | | APPLICATION SPEC 114-74084 | |
| | | | | WEIGHT | |
| CUSTOMER DRAWING | | | | SCALE 2:1 | |
| SIZE A3 | | | | CAGE CODE 00779 | |
| DRAWING NO. C-1103275 | | | | RESTRICTED TO | |
| SHEET 1 OF 1 | | | | REV B2 | |