




LOC	DIST	REVISIONS					
AG	53	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECO-06-002423	08JUN06	JDP	MDB

D




- 1 HOUSING-MATERIAL: LIQUID-CRYSTAL-POLYMER.
- 2 CONTACT-MATERIAL: PHOS. BRONZE, AMP 100-255.
- 3 LATCH-MATERIAL: BRASS, AMP 100-86 NICKEL PLATE 0.00127[.000050] MIN PER AMP SPEC 112-25-1.
- 4 CONTACT-PLATE: 0.00508[.000200] MIN MATTE TIN OVER 0.00127[.000050]MIN NICKEL.
5. IN ADDITION TO THOSE RECOMMENDED "SIMM" P. C. BOARD DIMENSIONS AND TOLERANCES SHOWN, ALL JEDEC SPECIFICATIONS APPLY AS SHOWN ON MO-116, ISSUE A.
6. RECOMMENDED MATING S.I.M.M. TAB METALLURGY: BASE METAL-COPPER. PLATING TO BE 0.00762[.000300] MIN TIN/LEAD OVER 0.00127[.000050] MIN NICKEL.
- 7 DATE CODE: (YEAR WEEK) XXXX FORMAT, LOCATED APPROXIMATELY AS SHOWN ON OPPOSITE SIDE.

C



B



A

RECOMMENDED P.C. BOARD HOLE PATTERN
SOCKET SIDE

111.76[4.400]		115.32[4.540]		44.45[1.750]		95.25[3.750]		72		5822019-4	
D		C		B		A		NO. OF POS		PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S.WAITMAN CHK M.YEOMANS APVD -		SJA005 SJA005		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME		CONNECTOR, MICRO-EDGE, .050q VERTICAL TIN PLATE, METAL LATCH			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ANGLES ± -		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO		RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A1 00779		C=5822019		-	
				CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2		REV B	

