





ISO VIEW
(GREEN CODING)



COLOR: GREEN




COLOR: BLACK




COLOR: WHITE


OVERALL DIMENSIONS




B AXIS MATCHES WITH
THE FEMALE HOUSING AXIS



MINIMUM FREE AREA AVAILABLE
TO UNPLUG THE CONNECTOR






MALE TERMINALS SETTING




HEADER'S DEFINITION

GREEN CODING REPRESENTED



MALE TERMINALS VARIABLE SETTING



A	(1)	(63)		
REV.	FIRST	LAST	DELETED	SUPERSEDED
INSPECTION NUMBERS				

PRINT 1ST RELEASE




EC NO: G2012-0180	2012/04/18
DRWN:GDSEBRUES	2012/04/18
CH'KD:JOUCLDS	2012/04/18
APPR:OPIESSIS	2012/04/23

QUALITY SYMBOL	DESCRIPTION
 = 0	
 = 0	
 = 0	

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± .005	± .0004
3 PLACES	± .004	± .0003
2 PLACES	± 0.1	± .002
1 PLACE	± 0.1	± .001
0 PLACE	±	±
ANGULAR ± 2 °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		



DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
GDESBRUERES	2012/04/18
CHECKED BY	DATE
JDCLOS	2012/04/18
APPROVED BY	DATE
OPLESSIS	2012/04/23
MATERIAL NO.	
N/A	
SIZE	THIS DRAWING CONT INCORPORATED AND
A1	

SCALE 4:1	DESIGN UNITS METRIC		FIRST ANGLE PROJECTION
TITLE 3W INTERFACE 1.5 TERM. (FOR FEMALE HOUSING)			
molex			
DOCUMENT NO. SD-98815-003		SHEET NO. 1 OF 1	
ALL INFORMATION THAT IS PROPRIETARY TO MOLEX SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			



CODING 4:1

HANDLING AREA




NOTE : 1 - The using conditions of the hinge are shown in the MOLEX specification n°AS-98821-001.

- 2 - Female terminal used : SCC RCPT TERM 1.5mm
 - Range 1 : 0988971109 (0.22 mm² to 2x0.22 mm²)
 - Range 2 : 0988971119 (0.5 mm² to 1 mm² included)
 - Range 3 : 0988971129 (2x0.5 mm² to 2 mm² included)


3 - Female connector will mate with male connector P/N 098822103x.

AREA REQUIRED WHEN THE CONNECTOR IS MATED




FIRST RELEASE EC No: G2007-0386 DRAWN: LPOUCHAUD 2008/03/10 CHKD: YIGEL 2008/03/10 APPR: LSTICKEIR 2008/03/10 A	DESCRIPTION	QUALITY SYMBOLS  	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE NSCC RCPT HSG 1.5 3CKT  MOLEX INCORPORATED SD-98817-002
				mm	INCH	DRAWN BY LPOUCHAUD	DATE 2008/02/21				
			4 PLACES	± ---	± ---	CHECKED BY YIGEL	DATE 2008/02/22				
			3 PLACES	± ---	± ---	APPROVED BY LSTICKEIR	DATE 2008/02/27				
			2 PLACES	± 0.05	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
			1 PLACE	± 0.1	± ---	SEE CHART		SD-98817-002		1 OF 2	
			ANGULAR ± 1 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

DATUM MONTH/YEAR




5



6.80 ± 0.10


8



14.1 Maxi

9

CAVITY NUMBER



34.8 Maxi


10

SUPPLIER ENGINEERING CONTROL ID

RAW MATERIAL

PRINT NUMBER

SUPPLIER MODIFICATION LEVEL



SUPPLIER PART NUMBER

GREEN CODING (P/N 0988171035) IS SHOWN.

NSCC Rcpt Hsg 1.5 3CKT		0988171035	Green	POLYESTER (PBT)	2.149 g		
		0988171031	Black				
		0988171030	White				
Description		Part-Number	Color	Raw Material	Weight effective		
QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
QUALITY SYMBOLS ▽=0 ▽=0 DESCRIPTION REV		MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	NSCC RCPT HSG 1.5 3CKT	
		DRAWN BY DATE		TITLE			
		LPOUCHAUD 2008/02/21					
		CHECKED BY DATE					
		YIGEL 2008/02/22					
		APPROVED BY DATE					
		LSTICKEIR 2008/02/27					
		MATERIAL NO.		DOCUMENT NO.			
		SEE CHART		SD-98817-002			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NO. 2 OF 2			
SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					