

### Mono Faders for Audio Mixers Slide Potentiometers

Japan  
Malaysia

Type: **EVANF**




#### ■ Features

- Slim-type fader series: Width=9.0 mm, Height=8.0 mm
- Excellent cost performance for mid and low level audio mixers

#### ■ Recommended Applications

- Fade control for audio mixers (popular type)
- MTR (Multi-track recorders)
- Paper position sensors (detectors) for PPC

#### ■ Explanation of Part Numbers



#### ■ Specifications

| Power Rating                  | Taper                          | Taper B | Others         |
|-------------------------------|--------------------------------|---------|----------------|
|                               | 100.0 mm Type                  | 0.5 W   | 0.25 W         |
|                               | Max. Operating Voltage: 30 Vac |         |                |
| Resistance *                  | 5 kΩ, 10 kΩ, 20 kΩ             | ±20 %   | +40 %<br>-20 % |
| Taper *                       | A, B, D, Y                     |         |                |
| Maximum Attenuation           | 100 dB min. (Except taper B)   |         |                |
| Operating Force               | 0.1 N to 1.0 N                 |         |                |
| Operating Life                | 50000 cycles min.              |         |                |
| Minimum Quantity/Packing Unit | 100 pcs. (Tray Pack)           |         |                |
| Quantity/Carton               | 500 pcs.                       |         |                |

Note: Customer's design for Lever Shape can be also negotiable.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.  
Should a safety concern arise regarding this product, please be sure to contact us immediately.

● 100.0 mm Travel, Single .....EVANF

