

2.1x0.7 mm SMD CHIP LED LAMP


XZSG65W



SUN LED

Email : sales@us.sunled.com

Web Site : www.sunled.com



Notes:


1. All dimensions are in millimeters (inches).
2. Tolerance is ± 0.15 (0.006") unless otherwise noted.

Absolute maximum ratings (T _A =25°C)		SG (InGaAlP)	Unit
Reverse voltage	V _R	5	V
Forward current	I _F	30	mA
Forward current (peak) 1/10Duty cycle 0.1ms pulse width	i _{FS}	150	mA
Power dissipation	P _T	105	mW
Operating temperature	T _A	-40 ~ +85	°C
Storage temperature	T _{stg}		





Operating Characteristics (T _A =25°C)		SG (InGaAlP)	Unit
Forward voltage (typ.) (I _F =20mA)	V _F	2.1	V
Forward voltage (max.) (I _F =20mA)	V _F	2.5	V
Reverse current (V _R =5V)	I _R	10	uA
Wavelength at peak emission (I _F =20mA)	λ _{peak}	574	nm
Wavelength at Dominate emission (I _F =20mA)	λ _D	568	nm
Spectral Line half-width (I _F =20mA)	Δλ	26	nm
Capacitance (V _F =0V, f=1MHz)	C	20	pF

Part Number	Emitting Color	Emitting Material	Lens-color	Luminous Intensity (I _F =20mA) mcd		Wavelength nm λ _P	Viewing Angle 2θ1/2
				min.	typ.		
XZSG65W	Green	InGaAlP	Water Clear	36	60	574	120°

XZSG65W




◆SG




XZSG65W


❖SMT Reflow Soldering Instructions



❖Recommended Soldering Pattern (Units : mm; Tolerance : ± 0.1)



❖Tape Specification (Units : mm)



PACKAGE : 2000PCS / REEL.