


## BAL SEAL® SEALS IN RECIPROCATING SURGICAL SAWS

Surgical saws must be reusable after sterilization, and free from mechanical defects. The Bal Seal® seals protect the reciprocating shaft from surgical environments and autoclaving temperatures at a continuous 275°F (135°C) or an intermittent 350°F (177°C). The seal maintains the bearing grease. Seal friction must be low to allow the drive mechanism to operate freely.



### Operating Parameters

Pressure:	Atmospheric to autoclaved 30 psi (2 kg/cm <sup>2</sup> )
Speed:	60 cpm
Temperature:	70°F to autoclaved 275°F (21°C to 135°C)
Media:	Bone, tissue, bearing grease and sterilization fluids
Additional:	Low friction and autoclavable

### Seal Selection: KSCX

#### Features:

- Bal Seal series KSCX selected for its excellent press-in metal locking ring retention system.
- Excellent sealing performance through autoclave sterilization cycles.
- Bearing grease kept from weeping out into the environment, and environmental contamination kept out.
- Low-friction seal design minimizes heat buildup and power losses.
- Patented, canted-coil spring energizer provides near-constant force for long seal life.
- Filled PTFE seal materials operate unlubricated and are FDA-compatible.

For more information and technical assistance, consult the Technical Sales Department.

PATENTS: The items described in this page include products that are the subject of issued United States and foreign patents or products where patents are pending, including the following: Patents 6,641,141 B2; 7,210,398 B2; 6,161,838; 5,992,856; 5,134,244

U.S. Address 19650 Pauling Foothill Ranch, CA 92610-2610 • Phone: (949) 460-2100 • Fax: (949) 460-2300

BV Address: Jollemanhof 16, • 1019 GW Amsterdam • The Netherlands • Phone: 31 20 638 65 23 • Fax: 31 20 625 60 18

Rev.B 10-19-07 (11-264)

Bal Seal Engineering, Inc. is certified to ISO 9001 | [www.balseal.com](http://www.balseal.com)