

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

JUN ,1996.

© COPYRIGHT 1996 BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC
J

DIST

REVISIONS

変更

P

LTR

DESCRIPTION

DATE

DWN

APVD

A

REVISED




ECR-08-000340

01FEB08



T.T

T.F


DIRECTION OFF TOP OF REEL



CONNECTOR DETAIL




PAPER REEL




PLASTIC REEL

DETAIL G



SEE DETAIL F

SEE DETAIL G




4 THIS PRODUCT WAS COATED BY FLUX-PENETRATION
-INHIDITING AGENT.

5 CAP HOUSING AND EMBOSS TAPE FOR ONLY 280P HAS
THESE ORIENTATION AND SUNK FEATURES.

SEALANT	REEL	TOOLING STATUS	QTY	W	E	D	C	B	A	POS.	PART NO.
SEALANT	---	NOT AVAILABLE	650	77.5	54.7	55	72	68.4	34.2	320	6-5353206-1
	PAPER	AVAILABLE	↑	77.5	48.7	49	72	68.4	34.2	280	6-↑-0
	---	NOT AVAILABLE	↑	61.5	42.7	43	56	52.4	26.2	240	5-↑-9
NON SEALANT	---	NOT AVAILABLE	650	61.5	36.7	37	56	52.4	26.2	200	5-5353206-8
	PLASTIC	AVAILABLE	↑	77.6	48.7	49	72	68.4	34.2	280	1-↑-0
	---	NOT AVAILABLE	↑	61.5	42.7	43	56	52.4	26.2	240	↑-9
SEALANT	PAPER	AVAILABLE	650	61.5	36.7	37	56	52.4	26.2	200	5353206-8

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
mmMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ± 0.2
1 PLC ± 0.2
2 PLC ± 0.2
3 PLC ± 0.2
4 PLC ± 0.2
ANGLES ± 5°

FINISH
仕上

DWN 14DEC04

HAWKING HE

CHK 14DEC04

STEVEN YAO

APVD 14DEC04

I.ENOMOTO

PRODUCT SPEC

製品規格
108-60047

APPLICATION SPEC

取付適用規格
114-5255

WEIGHT

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Kawasaki, Japan

NAME
名称

EMBOSS ASSY

FH 0.6BTB CONNECTOR

REC 4H 2ROW TYPE W/G-CONT

SIZE

CAGE CODE

DRAWING NO

番号
A300779C-5353206

RESTRICTED TO

SCALE
尺度 1:1

SHEET

1 OF 3

REV
A

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

JUN , 1996.

© COPYRIGHT 1996 BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

	DIST
--	------

REVISIONS

变更

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

APVD

SEE SHEET 1

[illegible]

0.25
0.11
0.9 ± 0.05
2 ± 0.1
6 ± 0.1
0.9 ± 0.05
2 ± 0.1
0.15
A-A
(SCALE 5:1)
TYP. ALL

[illegible]

REFERENCE P.C.BOARD LAYOUT

① MATERIAL ; HOUSING : HIGH TEMP THERMO PLASTIC
UL94V-0
CONTACT : COPPER ALLOY

② FINISH ; UNDER PL Ni 0.0013mm MIN ALL OVER.
CONTACT AREA 0.0002 MIN Au PL.
SOLDERING AREA
SIGNAL POS: 0.00005 MIN Au PL.
GROUND POS: 0.001 MIN TIN PL.

③ ■ THIS POSITION IS GROUND CIRCUIT.

GENERAL TOLERANCE
一般公差

10 $\geq$: ± 0.2
30 $\geq$ >10: ± 0.25
100 $\geq$ >30: ± 0.3
ANGLES: $\pm 3^\circ$

THIS DRAWING IS A CONTROLLED DOCUMENT

DIMENSIONS:
單位： 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差



0	PLC
1	PLC
2	PLC
3	PLC
4	PLC
ANGLES	

2


DWN	 Tyco Electronics		Tyco Electronics Corporation		
CHK			Kawasaki, Japan		
APVD					
PRODUCT SPEC 製品規格	NAME 名称 EMOSS ASSY FH 0.6BTB CONNECTOR REC 4H 2ROW TYPE W/G-CONT				
APPLICATION SPEC 取付適用規格					
WEIGHT					
	SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-5353206		RESTRICTED
CUSTOMER DRAWING			SCALE 1:1	SHEET 2 OF 3	REV A

CUSTOMER DRAWING

SCALE	2:1
比例	

SHEET 2 OF 4

REV	
-----	--



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位： 耗
mm

GENERAL TOLERANCE
一般公差

10≥:±0.2
30≥ >10:±0.25
100≥ >30:±0.3
ANGLES:±3°

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH
仕上

MATERIAL
材料

①

DWN

CHK

APVD

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Kawasaki, Japan

NAME
名称

EMBOSS ASSY
FH 0.6BTB CONNECTOR
REC 4H 2ROW TYPE W/G-CONT

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

SCALE
尺度

3:1

SHEET
3 OF 3

REV
A

AMP 1470-19 REV 31MAR2000