







RECOMMENDED PC BOARD LAYOUT



- △ NYLON, RED.
- △ BRASS PER ASTM B36.
- △ 3.81μm [0.000150] MIN TIN-LEAD OVER 2.54μm [0.000100] MIN COPPER OR 1.27μm [0.000050] MIN NICKEL.
- △ 0.76μm [0.000030] MIN GOLD FOR A LENGTH OF 5.08 [0.200] MIN FROM MATING END, 3.81μm [0.000150] MIN TIN-LEAD FOR A LENGTH OF 5.51 [0.217] MIN FROM OPPOSITE END, BOTH OVER 1.27μm [0.000050] MIN NICKEL.
- △ .000150 MIN TIN OVER .000100 MIN CU, OR .000050 MIN TIN.
- △ 0.76μm [0.000030] MIN GOLD FOR A LENGTH OF 5.08 [0.200] MIN FROM MATING END, 3.81μm [0.000150] MIN TIN FOR A LENGTH OF 5.51 [0.217] MIN FROM OPPOSITE END, BOTH OVER 1.27μm [0.000050] MIN NICKEL.

6	207378-7
5	207378-6
4	207378-3
3	207378-1
FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L SIPE 07/07/92		Tyco Electronics Corporation Harrisburg, Pa	
DIMENSIONS: INCHES		CHK R. STONE 7-24-92		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. TRAVIS 7-24-92		PRODUCT SPEC	
0 PLC ± -		APPLICATION SPEC		SIZE	
1 PLC ± -		WEIGHT		CAGE CODE	
2 PLC ± 0.25 [0.010]		CUSTOMER DRAWING		DRAWING NO	
3 PLC ± -		SCALE 2:1		SHEET 1 OF 1	
4 PLC ± -		REV K		RESTRICTED TO	
ANGLES ± -					
MATERIAL FINISH					
HOUSING: 1					
CONTACTS: SEE TBL					