

SO-1890-03-01-01-L

SO-2515-02-01-01-L

SO-1524-03-01-01-L

SO-0715-01-01-01

SO SERIES

PRECISION BOARD STACKING STANDOFF

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SO


Material:

Aluminum

Locking Compound:

Nylon

APPLICATIONS



See QMS/QFS Series SUMIT™ & PCI/104-Express™ connectors

Requires Standoff
SO-1524-03-01-02-L 15.24mm
board spacing. Connectors designed
to not fully seat when mated.

APPLICATIONS



Ideal for use with all
Samtec SI connectors

Precision
machined tolerances
($\pm .002"$ (0.05 mm))

RUGGEDIZED
BY SAMTEC

- Precision machined
- Locking compound

Stack heights from
5 mm to 25 mm

#4-40
Thread

Standard Nylon
thread locking
compound

ALSO AVAILABLE (MOQ Required)

- Other heights
- Stainless Steel
- Locking compound removed
- Other materials and threading
- No Hardware
Contact Samtec.

SO

BOARD
STACKERLEAD
STYLETHREAD
STYLE

01

L

Specify
BOARD STACKER
from chart

-01
= Female Thread/Press-In
(-0515 thru -0865 only)

-02
= Male/Male Thread
(-0515 and
-1115 thru -2515 only)

-03
= Male/Female Thread
(-0815 thru -2515 only)

-05
= Female/Female Thread
(-1524 thru -2515 only)

-01
= #4-40
Thread

-02
= M3 x 0.5
Thread


-L
= -02 & -03 Lead Style
thread locking compound
(Leave blank for -01 Lead Style)

BOARD STACKER	A	BOARD STACK HEIGHT
-0515	(5.15) .203	5 mm
-0715	(7.15) .282	7 mm
-0815	(8.15) .321	8 mm
-0865	(8.65) .341	8.5 mm
-1115	(11.15) .439	11 mm
-1215	(12.15) .478	12 mm
-1524	(15.24) .600	15.24 mm
-1615	(16.15) .636	16 mm
-1890	(18.90) .744	18.75 mm
-1915	(19.15) .754	19 mm
-2515	(25.15) .990	25 mm

Notes:

Standoffs are designed,
0.15 mm longer than
connector stack heights to
allow for processing variables.

Some sizes, styles and
options are non-standard,
non-returnable.



Components are to be packaged in separate bags unassembled.

WWW.SAMTEC.COM

Due to technical progress, all designs, specifications and components are subject to change without notice.