


MF72



CANTHERM


Supplying high-quality bimetal and thermal sensor products.



Power NTC Thermistor

The image displays five traffic cones of varying sizes and colors (black, green, and white) against a blue background. Each cone features the 'ME72 5D 25' model number and a reflective cat eye. The cones are arranged in a cluster, with some standing upright and others tilted.

Specification



Application

Can be installed into the power circuits of:

- Power supplies and inverters
- Uninterruptible Power Supplies
- Energy saving lamps
- Electronic Ballasts
- Filament Protection of various types of lamps
- Some types of heaters
- For higher power circuits ask about the MF73 and MF74 series surge suppressors.

Characteristics

- Small Size and fast response
- High Power handling capability
- Fast response to surge current
- High material constant (B value)
- Low residual resistance
- Wide operating temperature range -55 to +200C
- R25 allowable tolerance is $\pm 20\%$
- Long-term Stability and Reliability
- UL 1434 File# E241319
- CQC File# 04001010556

Main Techno-Parameter

Operating Temperature: -55 to 200°C

Part No.	R ₂₅ (Ω)	Max. Steady State Current (A)	Approx. R of Max. Current (Ω)	Dissip. Coef. (mW/°C)	Thermal Time Constant (S)	Max. Load Capacitance in uF		UL
						120 VAC	240 VAC	
MF72-005D5	5	1	0.353	6	20	188	47	
MF72-010D5	10	0.7	0.771	6	20	188	47	
MF72-060D5	60	0.3	1.878	6	18	188	47	
MF72-200D5	200	0.1	18.70	6	18	88	22	
MF72-005D7	5	2	0.283	10	30	224	56	
MF72-008D7	8	1	0.539	9	28	224	56	
MF72-010D7	10	1	0.616	9	27	224	56	
MF72-012D7	12	1	0.816	9	27	224	56	
MF72-016D7	16	0.7	1.003	9	27	224	56	
MF72-022D7	22	0.6	1.108	9	27	224	56	
MF72-033D7	33	0.5	1.485	10	28	188	47	
MF72-200D7	200	0.2	11.65	11	28	188	47	
MF72-003D9	3	4	0.120	11	35	272	68	✓
MF72-004D9	4	3	0.190	11	35	272	68	✓
MF72-005D9	5	3	0.210	11	34	272	68	✓
MF72-006D9	6	2	0.315	11	34	272	68	✓
MF72-008D9	8	2	0.400	11	32	400	100	✓
MF72-010D9	10	2	0.458	11	32	400	100	✓
MF72-012D9	12	1	0.652	11	32	400	100	✓
MF72-016D9	16	1	0.802	11	31	400	100	✓
MF72-020D9	20	1	0.864	11	30	600	150	✓
MF72-022D9	22	1	0.950	11	30	600	150	✓
MF72-030D9	30	1	1.022	11	30	600	150	✓
MF72-033D9	33	1	1.124	11	30	600	150	✓
MF72-050D9	50	1	1.252	11	30	600	150	✓
MF72-060D9	60	0.8	1.502	11	30	600	150	✓
MF72-080D9	80	0.8	2.010	11	30	272	68	✓

Part No.	R ₂₅ (Ω)	Max. Steady State Current (A)	Approx. R of Max. Current (Ω)	Dissip. Coef. (mW/°C)	Thermal Time Constant (S)	Max. Load Capacitance in uF		UL
						120 VAC	240 VAC	
MF72-120D9	120	0.8	3.015	11	30	272	68	✓
MF72-200D9	200	0.5	5.007	11	32	188	47	✓
MF72-400D9	400	0.2	30.30	11	32	188	47	✓
MF72-002.5D11	2.5	5	0.095	13	43	600	150	✓
MF72-003D11	3	5	0.100	13	43	600	150	✓
MF72-004D11	4	4	0.150	13	44	600	150	✓
MF72-005D11	5	4	0.156	13	45	600	150	✓
MF72-006D11	6	3	0.240	13	45	880	220	✓
MF72-008D11	8	3	0.255	14	47	880	220	✓
MF72-010D11	10	3	0.275	14	47	880	220	✓
MF72-012D11	12	2	0.462	14	48	880	220	✓
MF72-016D11	16	2	0.470	14	50	880	220	✓
MF72-020D11	20	2	0.512	15	52	880	220	✓
MF72-022D11	22	2	0.563	15	52	880	220	✓
MF72-030D11	30	1.5	0.667	15	52	880	220	✓
MF72-033D11	33	1.5	0.734	15	52	880	220	✓
MF72-050D11	50	1.5	1.021	15	52	880	220	✓
MF72-060D11	60	1.5	1.215	15	52	880	220	✓
MF72-080D11	80	1.2	1.656	15	52	600	150	✓
MF72-001.3D13	1.3	7	0.062	13	60	880	220	✓
MF72-001.5D13	1.5	7	0.073	13	60	880	220	✓
MF72-002.5D13	2.5	6	0.088	13	60	880	220	✓
MF72-003D13	3	6	0.092	14	60	880	220	✓
MF72-004D13	4	5	0.120	15	67	880	220	✓
MF72-005D13	5	5	0.125	15	68	880	220	✓
MF72-006D13	6	4	0.170	15	65	880	220	✓
MF72-007D13	7	4	0.188	15	65	1320	330	✓

— Main Techno-Parameter (cont.)

Operating Temperature: -55 to 200°C

Part No.	R ₂₅ (Ω)	Max. Steady State Current (A)	Approx. R of Max. Current (Ω)	Dissip. Coef. (mW/°C)	Thermal Time Constant (S)	Max. Load Capacitance in uF		UL
						120 VAC	240 VAC	
MF72-008D13	8	4	0.194	15	60	1320	330	✓
MF72-010D13	10	4	0.206	15	65	1320	330	✓
MF72-012D13	12	3	0.316	16	65	1320	330	✓
MF72-015D13	15	3	0.335	16	60	1320	330	✓
MF72-016D13	16	3	0.338	16	60	1320	330	✓
MF72-020D13	20	3	0.372	16	65	1320	330	✓
MF72-030D13	30	2.5	0.517	16	65	1320	330	✓
MF72-047D13	47	2	0.810	17	65	880	220	✓
MF72-120D13	120	1.2	2.124	16	65	880	220	✓
MF72-001.3D15	1.3	8	0.048	18	68	1320	330	✓
MF72-001.5D15	1.5	8	0.052	19	69	1320	330	✓
MF72-003D15	3	7	0.075	18	76	1320	330	✓
MF72-005D15	5	6	0.112	20	76	1880	470	✓
MF72-006D15	6	5	0.155	20	80	1880	470	✓
MF72-007D15	7	5	0.173	20	80	1880	470	✓
MF72-008D15	8	5	0.178	20	80	1880	470	✓
MF72-010D15	10	5	0.180	20	75	1880	470	✓
MF72-012D15	12	4	0.250	20	75	1880	470	✓
MF72-015D15	15	4	0.268	21	85	1880	470	✓
MF72-016D15	16	4	0.276	21	70	1880	470	✓
MF72-020D15	20	4	0.288	17	86	1880	470	✓
MF72-030D15	30	3.5	0.438	18	75	1320	330	✓

Part No.	R ₂₅ (Ω)	Max. Steady State Current (A)	Approx. R of Max. Current (Ω)	Dissip. Coef. (mW/°C)	Thermal Time Constant (S)	Max. Load Capacitance in uF		UL
						120 VAC	240 VAC	
MF72-047D15	47	3	0.680	21	86	1320	330	✓
MF72-120D15	120	1.8	1.652	22	87	1320	330	✓
MF72-000.7D20	0.7	11	0.018	25	89	1880	470	✓
MF72-001.3D20	1.3	9	0.037	24	88	1880	470	✓
MF72-003D20	3	8	0.055	24	88	1880	470	✓
MF72-005D20	5	7	0.087	23	87	2240	560	✓
MF72-006D20	6	6	0.113	25	103	2240	560	✓
MF72-008D20	8	6	0.142	25	105	2240	560	✓
MF72-010D20	10	6	0.162	24	102	2240	560	✓
MF72-012D20	12	5	0.195	24	100	2720	680	✓
MF72-016D20	16	5	0.212	25	100	2720	680	✓
MF72-000.7D25	0.7	12	0.014	30	120	2240	560	
MF72-001.5D25	1.5	10	0.027	30	121	2240	560	
MF72-003D25	3	9	0.044	32	124	2240	560	
MF72-005D25	5	8	0.070	32	125	2720	680	
MF72-008D25	8	7	0.114	33	125	2720	680	
MF72-0010D25	10	7	0.130	32	125	2720	680	
MF72-012D25	12	6	0.156	32	126	3280	820	
MF72-016D25	16	6	0.160	35	126	3280	820	

Note: Unless otherwise specified, the allowable tolerance of R₂₅ is +/- 20%
Specifications may change without notice.



CANTHERM

Supplying high-quality bimetal and thermal sensor products.

8415 Mountain Sights Avenue • Montreal (Quebec), H4P 2B8, Canada
Tel: (514) 739-3274 • 1-800-561-7207 • Fax: (514) 739-2902 • E-mail: sales@cantherm.com

Website: www.cantherm.com | Division of Microtherm

2018/Aug MF72