












PRODUCT DATASHEET

2VA LOW PROFILE ENCAPSULATED TRANSFORMER



-  Independantly Approved to
EN60950 UL506 cUL506 & CSA 22.2
-  CE Marked
-  Dual 115V Primaries
-  Comprehensive choice of secondary voltages
-  5KV Isolation between primary and secondary windings.
-  UL94-V0 Vacuum Encapsulated Construction
-  Suitable for flow soldering
-  Identical footprint from 2VA to 9VA

Weight	0.120	Kg	 EN c 
Typical Regulation	22	%	
Frequency	50/60	Hz	
Max Ambient	40	°C	
Bobbin Material	UL94-V0	"B" 130 °C	

Part No	Primary	Secondary	Reccomended Secondary Fuse
D2085	115+115	6+6	0.160AT
D2086	115+115	9+9	0.100AT
D2087	115+115	12+12	0.080AT

Please see sheet 2 for outline drawing and connection info.

DAGNALL ELECTRONICS LIMITED

Shuttleworth Road, Elms Industrial Estate, Bedford. MK41 0EP UK

TEL +44(0)1234 330077 FAX +44(0)1234 330088

E-mail sales@dagnall-electronics.com


Issue 1. 25/10/02

2 of 2


PRODUCT DATASHEET

2VA Approved Low Profile Encapsulated Transformer


Outline Drawing



Connection Diagrams for D2085 - 230V supply



Connection Diagrams for D2085 - 115V supply





Nemko

Nemko Ltd

Test Certificate

Cert No: 9973

Relating to **RANGE OF ENCAPSULATED TRANSFORMERS**
2VA/4VA/14VA

No. of samples inspected **EIGHT**

Specifications to which above unit has been tested and
compliance confirmed.

THE RELEVANT CLAUSES OF BS EN 60950: 1992 COVERING CLAUSES

1, 2, 3, 4 & 5 ONLY*****

*In our opinion the sample complies with the Principal Elements of
the Safety Objectives of the Low Voltage Directive 73/23/EEC*

Client **DAGNALL ELECTRONICS LIMITED**
WOOD END ROAD
CRANFIELD
BEDS MK43 0ED

Signed 
MIKE BURNS Certifying Officer

Date of Issue **27.06.97**

Relating to Laboratory Report No. **22328**

THIS TEST CERTIFICATE MUST BE
READ IN CONJUNCTION WITH
LABORATORY REPORT NO:

22328, 21067 & 20720





Underwriters Laboratories Inc.®

DAGNALL ELECTRONICS LTD
MR R BARTON
ELMS INDUSTRIAL ESTATE
SHUTTLEWORTH RD
BEDFORD
MK41 0EP ENGLAND UNITED KINGDOM

Northbrook, Illinois • (847) 272-8800
Melville, New York • (631) 271-6200
Santa Clara, California • (408) 985-2400
Research Triangle Park,
North Carolina • (919) 549-1400
Camas, Washington • (360) 817-5500

RE: Project Number(s) - 01ME19066

Your most recent Certification is shown below. You may also view this information, or a portion of this information (depending on the product category), on UL's Online Certifications Directory at www.ul.com/database. Please review the text and contact the Conformity Assessment Services staff member who handled your project if revisions are required. For instructions on placing an order for this information in a 3 x 5-inch format, you may refer to the enclosed order form for UL Card Service.

XPTQ2 February 18, 2002
Transformers, General Purpose - Component

DAGNALL ELECTRONICS LTD
ELMS INDUSTRIAL ESTATE SHUTTLEWORTH RD BEDFORD,
MK41 0EP ENGLAND UNITED KINGDOM

E178378

Cat. Nos. D2005 thru D2210.
Cat. No. D9122.
Marking: Company name or File No. and catalog designation.

See General Information Preceding These Recognitions

For use only in equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.



Certificate of Compliance

Certificate Number: LR 110435-2

Revision:

Date Issued: January 9, 1998

Issued to: **Dagnall Electronics Ltd.**
Wood End Rd.,
Cranfield,
Bedfordshire MK43 OED England
Attention: Mr. Roy Barton

The products listed below are eligible to bear the CSA Mark

Issued by: **M. Lloyd**
Toronto, ON Canada

Signature: _____


PRODUCTS

Power Transformers Series D2XXX, Primary; Dual Winding 2 by 120V max, 50/60Hz, Single Winding 240V max, 50/60Hz; Secondary 2 by 24V max, 30VA max, encapsulated, pwb mounted for use in equipment where the suitability of the combination is to be determined by the Canadian Standards Association.

APPLICABLE REQUIREMENTS

CSA Std C22.2 No.

66-1988-Specialty Transformers



Northbrook, Illinois • (847) 272-8800
Melville, New York • (516) 271-6200
Santa Clara, California • (408) 985-2400
Research Triangle Park,
North Carolina • (919) 549-1400
Camas, Washington • (360) 817-5500

DAGNALL ELECTRONICS (CRANFIELD) LTD
MR R BARTON
WOOD END RD
CRANFIELD
BEDFORD
MK43 0ED ENGLAND UNITED KINGDOM



Your most recent listing is shown below. Please review this information and report any inaccuracies to the UL Engineering staff member who handled your UL project.

XPTQ8 March 12, 1998
Component - Transformers, General Purpose Certified for Canada

DAGNALL ELECTRONICS (CRANFIELD) LTD
WOOD END RD CRANFIELD BEDFORD, MK43 0ED ENGLAND
UNITED KINGDOM

E178378 (M)

Cat. Ns. 2005 thru 2210 and 3000 thru 5074. Cat. Nos. 2005-2210 are prefixed by letter D.
Marking: Company name, File No. catalog designation and the Recognized Component Mark for Canada



See General Information Preceding These Recognitions.
For use only in equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.
Report: March 13, 1998.

398531001

Underwriters Laboratories Inc.®

011/0341035
135

For information on placing an order for UL Listing Cards in a 3 x 5 inch card format, please refer to the enclosed ordering information.

UNDERWRITERS LABORATORIES INC.

A not-for-profit organization
dedicated to public safety and
committed to quality service