

COIL

Coil Power	Standard:450mW (24V、48V:500mW) Sensitive:310mW~330mW
------------	---




SAFETY APPROVAL RATINGS

UL&CUL	6A 120VAC/28VDC 10A 120VAC
TüV	10A/250VAC 10A/28VDC

OUTLINE DIMENSIONS, WIRING DIAGRAM AND PC BOARD LAYOUT.

Unit: inch(mm)


Outline Dimensions

Wiring Diagram
(Bottom view)PCB Layout
(Bottom view)


Remark:1) In case of no tolerance shown in outline dimension: outline dimension $\leq 1\text{mm}$, tolerance should be $\pm 0.2\text{mm}$; outline dimension $> 1\text{mm}$ and $\leq 5\text{mm}$, tolerance should be $\pm 0.3\text{mm}$; outline dimension $> 5\text{mm}$, tolerance should be $\pm 0.4\text{mm}$.
2) The tolerance without indicating for PCB layout is always $\pm 0.1\text{mm}$.

CHARACTERISTIC CURVES


MAXIMUM SWITCHING POWER



ENDURANCE CURVE



COIL TEMPERATURE RISE



This datasheet is for customers' reference. All the specifications are subject to change without notice.