STFI13NK60Z

N-channel 600 V, 0.48 Ω, 13 A, Zener-protected SuperMESH™ Power MOSFET in I²PAKFP package

Datasheet — production data

Features

Order code	V_{DSS}	$R_{DS(on)}$ max	I_D	P_{TOT}
STFI13NK60Z	600 V	<0.55 Ω	13 A	35 W

- Fully insulated and low profile package with increased creepage path from pin to heatsink plate
- Gate charge minimized
- Very low intrinsic capacitance



I²PAKFP (TO-281)

Applications

- Switching applications

Description

This device is an N-channel Zener-protected Power MOSFET developed using STMicroelectronics' SuperMESH™ technology, achieved through optimization of ST's well established strip-based PowerMESH™ layout. In addition to a significant reduction in on-resistance, this device is designed to ensure a high level of dv/dt capability for the most demanding applications.

Figure 1. Internal schematic diagram



Table 1. Device summary

Order code	Marking	Package	Packaging
STFI13NK60Z	13NK60Z	I²PAKFP (TO-281)	Tube

Contents

1 Electrical ratings

Table 2. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{DS}	Drain-source voltage	600	V
V_{GS}	Gate-source voltage	± 30	V
I_D	Drain current (continuous) at T_C = 25 °C	13 (1)	A
I_D	Drain current (continuous) at T_C = 100 °C	8.2 (1)	A
I_{DM} (2)	Drain current (pulsed)	52(1)	A
P_{TOT}	Total dissipation at T_C = 25 °C	35	W
ESD	Gate-source human body model (R=1,5 kΩ, C=100 pF)	4	kV
dv/dt (3)	Peak diode recovery voltage slope	4.5	V/ns
V_{ISO}	Insulation withstand voltage (RMS) from all three leads to external heat sink (t=1 s;T_C=25 °C)	2500	V
T_j T_{stg}	Operating junction temperature Storage temperature	-55 to 150	°C

1. Limited by maximum junction temperature.
2. Pulse width limited by safe operating area.
3. I_{SD} < 13 A, di/dt < 200 A/µs, V_{DD}= 80% $V_{(BR)DSS}$.

Table 3. Thermal data

Symbol	Parameter	Value	Unit
$R_{thj\text{-}case}$	Thermal resistance junction-case Max	3.6	°C/W
$R_{thj\text{-}amb}$	Thermal resistance junction-amb Max	62.5	°C/W

Table 4. Avalanche characteristics

Symbol	Parameter	Max value	Unit
I_{AR}	Repetitive or non repetitive avalanche current	10(1)	A
E_{AS}	Single pulse avalanche energy (starting T_j=25 °C, I_D=I_{AR}, V_{DD}= 50 V)	400	mJ

1. Limited by maximum junction temperature

2 Electrical characteristics

(T_{CASE} = 25 °C unless otherwise specified).

Table 5. On/off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage (V_{GS}= 0)	I_D = 1 mA	600			V
I_{DSS}	Zero gate voltage drain current (V_{GS} = 0)	V_{DS} = 600 V, V_{DS} = 600 V, Tc=125 °C			1 50	µA µA
I_{GSS}	Gate body leakage current (V_{DS} = 0)	V_{GS} = ±20 V			±10	µA
$V_{GS(th)}$	Gate threshold voltage	V_{DS}= V_{GS} , I_D = 100 µA	3	3.75	4.5	V
$R_{DS(on)}$	Static drain-source on resistance	V_{GS}= 10 V, I_D= 4.5 A		0.48	0.55	Ω

Table 6. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
g_{fs} (1)	Forward transconductance	V_{DS} =8 V, I_D = 5 A	-	11		S
C_{iss} C_{oss} C_{rss}	Input capacitance Output capacitance Reverse transfer capacitance	V_{DS} =25 V, f=1 MHz, V_{GS}=0	-	2030 210 48		pF pF pF
$C_{oss\ eq.}$ (2)	Equivalent output capacitance	V_{GS}=0, V_{DS} =0 to 480 V	-	125		pF
Q_g Q_{gs} Q_{gd}	Total gate charge Gate-source charge Gate-drain charge	V_{DD}=480 V, I_D = 10 A V_{GS} =10 V (see *Figure 16*)	-	66 11 33	92	nC nC nC

1. Pulsed: pulse duration = 300 µs, duty cycle 1.5%
2. $C_{oss\ eq.}$ is defined as a constant equivalent capacitance giving the same charging time as C_{oss} when V_{DS} increases from 0 to 80% V_{DSS}

Table 7. Switching times

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$ t_r	Turn-on delay time Rise time	V_{DD}= 300 V, I_D= 5 A, R_G=4.7 Ω, V_{GS}=10 V (see *Figure 15*)	-	22 14	-	ns ns
$t_{d(off)}$ t_f	Turn-off delay time Fall time	V_{DD}=300 V, I_D= 5 A, R_G=4.7 Ω, V_{GS}=10 V (see *Figure 15*)	-	61 12	-	ns ns
$t_{r(Voff)}$ t_f t_c	Off-voltage rise time Fall time Cross-over time	V_{DD}=480 V, I_D= 10 A, R_G=4.7 Ω, V_{GS}=10 V (see *Figure 15*)	-	10 9 20	-	ns ns ns

Table 8. Gate-source Zener diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)GSO}$	Gate-source breakdown voltage (I_D=0)	Igs=±1 mA	30	-	-	V

The built-in back-to-back Zener diodes have specifically been designed to enhance not only the device's ESD capability, but also to make them safely absorb possible voltage transients that may occasionally be applied from gate to source. In this respect the Zener voltage is appropriate to achieve an efficient and cost-effective intervention to protect the device's integrity. These integrated Zener diodes thus avoid the usage of external components.

Table 9. Source drain diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{SD} I_{SDM} (1)	Source-drain current Source-drain current (pulsed)		-		10 40	A A
V_{SD} (2)	Forward on voltage	I_{SD} = 10 A, V_{GS}=0	-		1.6	V
t_{rr} Q_{rr} I_{RRM}	Reverse recovery time Reverse recovery charge Reverse recovery current	I_{SD}= 10 A, di/dt = 100 A/µs, V_{DD}=35 V, T_j=150 °C	-	570 4.5 16		ns µC A

1. Pulse width limited by safe operating area
2. Pulsed: pulse duration = 300 µs, duty cycle 1.5%

2.1 Electrical characteristics (curves)

Figure 2. Safe operating area



Figure 3. Thermal impedance



Figure 4. Output characteristics



Figure 5. Transfer characteristics



Figure 6. Transconductance



Figure 7. Static drain-source on resistance



Figure 8. Gate charge vs gate-source voltage



Figure 9. Capacitance variations



Figure 10. Normalized gate threshold voltage vs temperature



Figure 11. Normalized on resistance vs temperature



Figure 12. Source-drain diode forward characteristics



Figure 13. Normalized B_{VDSS} vs temperature



Figure 14. Maximum avalanche energy vs temperature



3 Test circuits

Figure 15. Switching times test circuit for resistive load



Figure 16. Gate charge test circuit



Figure 17. Test circuit for inductive load switching and diode recovery times



Figure 18. Unclamped inductive load test circuit



Figure 19. Unclamped inductive waveform



Figure 20. Switching time waveform



4 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

Table 10. I^2PAKFP (TO-281) mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	4.40		4.60
B	2.50		2.70
D	2.50		2.75
D1	0.65		0.85
E	0.45		0.70
F	0.75		1.00
F1			1.20
G	4.95	-	5.20
H	10.00		10.40
L1	21.00		23.00
L2	13.20		14.10
L3	10.55		10.85
L4	2.70		3.20
L5	0.85		1.25
L6	7.30		7.50

Figure 21. I^2PAKFP (TO-281) drawing



5 Revision history

Table 11. Document revision history

Date	Revision	Changes
06-Jul-2011	1	First release.
07-Nov-2011	2	*Figure 2: Safe operating area* and *Figure 3: Thermal impedance* have been added.
20-Mar-2012	3	Document status promoted from preliminary data to production data. The package name has been updated.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST’s terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST’S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY TWO AUTHORIZED ST REPRESENTATIVES, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER’S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com