

Technical Data Sheet

Infrared Remote-control Receiver Module

IRM-V5XX/TR1

Features

- High shielding against electric field disturbance.
- Circular lens to improve the receive characteristic.
- Line-up for various center carrier frequencies.
- Low voltage and low power consumption.
- High immunity against ambient light.
- Photodiode with integrated circuit.
- TTL and CMOS compatibility.
- · Side-received SMD.
- Suitable burst length ≥ 10 pulses/burst.
- This product itself will remain within RoHS compliant version.
- Ph free
- External dimensions 5.3(L)*3.8(W)*2.65(H) mm.

Descriptions

The device is a miniature SMD type infrared remote control system receiver that has been developed and designed by utilizing the most updated IC technology. The PIN diode and preamplifier are assembled on PCB, the epoxy package is designed as an IR filter. The demodulated output signal can directly be decoded by a microprocessor.

Applications

- 1. Light detecting portion of remote control
 - AV instruments such as Audio, TV, VCR, CD, MD, etc.
 - Home appliances such as Air-conditioner, Fan, etc.
 - The other equipments with wireless remote control.
 - CATV set top boxes
 - Multi-media Equipment

Device Selection Guide


PART	MATERIAL	COLOR
Chip	Silicon	
Package	Ероху	Black
Metal case	SPCC	Silver white

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 5 Page 1 of 12

Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU_NPID2



Package Dimensions




Notes: 1. All dimensions are in millimeters.

2. Tolerances unless dimensions ± 0.2 mm.

Soldering patterns

The following soldering patterns are recommended for reflow-soldering:



Unit: mm



IRM-V5XX/TR1

Available Parts for Different Carrier Frequencies

Part	Carrier Frequency
IRM-V538/TR1	38 kHz
IRM-V536/TR1	36 kHz
IRM-V540/TR1	40 kHz

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit	Notice
Supply Voltage	Vcc	0~6	V	
Operating Temperature	Topr	-25 ∼ +85	$^{\circ}\!\mathbb{C}$	
Storage Temperature	Tstg	-40 ∼ +85	$^{\circ}\! \mathbb{C}$	

Recommended Operating Condition

Supply Voltage Rating: Vcc 2.7V to 5.5V

Electro-Optical Characteristics (Ta=25°C, and Vcc=3.0V)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Supply Current	Icc			1.2	mA	No signal input
Peak Wavelength	$\lambda_{ m p}$		940		nm	
Reception Distance	L_0	8			m	
	L ₄₅	5			m	
Half Angle(Horizontal)	$\Theta_{ m h}$		45		deg	At the ray axis *1
Half Angle(Vertical)	$\Theta_{ m v}$		45		deg	
High Level Pulse Width	T_{H}	400		800	μs	At the ray axis
Low Level Pulse Width	$T_{ m L}$	400		800	μs	*2
High Level Output Voltage	V_{H}	2.7			V	
Low Level Output Voltage	$V_{\rm L}$		0.2	0.5	V	

Notes:

*1 : The ray receiving surface at a vertex and relation to the ray axis in the range of θ = 0° and θ =45°.

*2: A range from 30cm to the arrival distance. Average value of 50 nulses

Everlight Electronics Co., Ltd. http:\\www.everlight.com Rev 5 Page 3 of 12

Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU_NPID2



The Notice of Application:

Transmission remote control signal consist of four parts: Encode Part, IR Transmitter Source, IRM device, Decode Part

- 1. When IRM-V5XX code select frequency, it need to well understand the center system of encode part.
- 2. Strong or weak light of IR Transmitter can affect distance of transmission.
- 3. Minimum Burst Length Tburst (number of pulses per burst): 10 cycles
- 4. It needs to ensure the translation range of decode part if it is applied to the pulse-width range.

If the above items hardly assure of its application, it'll cause NG (no good) message from the edge of signal.

Test Method:

The specified electro-optical characteristics are satisfied under the following conditions at the controllable distance.

①Measurement place

A place that is nothing of extreme light reflected in the room.

②External light

Project the light of ordinary white fluorescent lamps which are not high Frequency lamps and must be less then 10 Lux at the module surface. (Ee \leq 10Lux)

Standard transmitter

A transmitter whose output is so adjusted as to Vo = 400 mVp-p and the output Wave form shown in Fig.-1.According to the measurement method shown in Fig.-2 the standard transmitter is specified.


However, the infrared photodiode to be used for the transmitter should be $\lambda p=940$ nm, $\Delta \lambda=50$ nm. Also, photodiode is used of PD438B (Vr=5V). (Standard light / Light source temperature 2856°K).

Measuring system

According to the measuring system shown in Fig.-3

Fig.-1 Transmitter Wave Form

D.U.T output Pulse



Everlight Electronics Co., Ltd.

Device No: DMO-538-397

http://www.everlight.com

Rev 5

Page 4 of 12

Prepared date: 12/21/2007

Prepared by : IBU NPID2

IRM-V5XX/TR1

Fig.-2 Measuring Method







Fig.-3 Measuring System





Application Circuit:



RC Filter should be connected closely between Vcc pin and GND pin.

Everlight Electronics Co., Ltd. Device No: DMO-538-397

http:\\www.everlight.com Prepared date: 12/21/2007 Rev 5

Page 5 of 12

Prepared by : IBU NPID2



IRM-V5XX/TR1

Typical Electro-Optical Characteristics Curves

Fig.-4 Relative Spectral Sensitivity vs.




Fig.-5 Relative Transmission Distance vs. Direction






Fig.-6 Output Pulse Length vs. Arrival Distance Fig.-7 Arrival Distance vs. Supply Voltage






Everlight Electronics Co., Ltd. http://www.everlight.com Rev 5 Page 6 of 12

Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU NPID2

Typical Electro-Optical Characteristics Curves

Fig.-8 Arrival Distance vs. Ambient Temperature Fig.-9 Relative Transmission Distance vs. Center Carrier Frequency








Fig.-9 Relative Transmission Distance vs. Center Fig.-9 Relative Transmission Distance vs. Center Carrier Frequency

Carrier Frequency

IRM-V538/TR1





Everlight Electronics Co., Ltd. http://www.everlight.com Rev 5 Page 7 of 12

Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU NPID2



Reliability Test Item And Condition

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

Reflow Terms: JEDEC Level 4 Specification

Drying; Temp.:125°C 24hrs → Moisture 30°C / 60% RH 96hrs → Reflow Temp.: 260°C±5°C

10sec, 3 times

Note:

1. Not sooner than 15 minutes and not longer than 4 hours after removal from the temperature/humidity chamber.

2. The time between reflow shall be 5 minutes minimum and 60 minutes maximum.

Test Items	Test Conditions	Failure Judgments Criteria	Samples(n) Defective(c)
Temperature cycle	200 avala tast	$L_0 \le L \times 0.8$ $L_{45} \le L \times 0.8$	n=76,c=0
High temperature test	Temp: +85°C Vcc: 5V 1000hrs	L: Lower specification limit *Icc : Operate Current (mA)	n=76,c=0
Low temperature storage	Temp: -40°C 1000hrs		n=76,c=0
High temperature High humidity	Ta: 85℃, RH: 85% 1000hrs	Variation $\leq \pm 20\%$:	n=76,c=0

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 5 Page 8 of 12


Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU NPID2



Recommended method of storage

The following are general recommendations for moisture sensitive level (MSL) 4 storage and use:

- Shelf life in sealed bag: 12 months at < 40 °C and < 90% relative humidity (RH)
- After bag is opened, devices that will be subjected to reflow solder or other high temperature process must
 - a) Mounted within 72 hours of factory conditions < 30 °C/60%RH, or
 - b) Stored at <20% RH
- Devices require bake, before mounting, if:
 Humidity Indicator Card is > 20% when read at 23 ± 5 °C
- If baking is required, devices may be baked:
 - a) 192 hours at 40°C, and <5% RH(dry air/nitrogen) or
 - b) 96 hours at 60°C, and <5% RH for all device containers
 - c) 24 hours at 125 °C
- Soldering Condition
 - a) Pb-free solder temperature profile



- b) Reflow soldering should not be done more than two times.
- c) When soldering, do not put stress on the unit during heating.
- d) After soldering, do not warp the circuit board.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 5 Page 9 of 12

Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU NPID2




Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

Repairing

Repair should not be done after the Devices have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the Devices will or will not be damaged by repairing.



Everlight Electronics Co., Ltd. http://www.everlight.com Rev 5 Page 10 of 12

Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU NPID2





IRM-V5XX/TR1

Packing Quantity Specification


- 1. 2000 PCS/1 Reel
- 2. 5 Reel /1 Carton

Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel





Packing process




Everlight Electronics Co., Ltd. http://www.everlight.com Rev 5 Page 11 of 12

Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU NPID2



Label Form Specification



CPN: Customer's Production Number

QTY: Packing Quantity

CAT: None HUE: None

REF: Reference

LOT No: Lot Number

MADE IN TAIWAN: Production Place

Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD.

Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

http:\\www.everlight.com

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 5 Page 12 of 12

Device No: DMO-538-397 Prepared date: 12/21/2007 Prepared by: IBU NPID2