



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION: NOT REQUIRED
4. PACKAGING: NOT REQUIRED
5. MATES WITH: NONE
6. 'XX' REFERS TO THE QUANTITY OF CIRCUITS.
7. INCH DIMENSIONS ARE SHOWN IN BRACKETS [XXX].
8. ASSEMBLY IS ROHS COMPLIANT.

C

6	XX*2	SCREW, #6-32X.250, PAN HD, PH-SL W/WSHR (-50 OPTION)	STEEL	ZINC W/CHROMATE
5	XX*2	SCREW, #6-32X.250, BGHD, PHIL-SLOT (-49 OPTION)	BRASS	NICKEL
4	XX*2	SCREW, #6-32X.250, BGHD, PHIL-SLOT (STANDARD)	STEEL	ZINC W/CHROMATE
3	XX	TERMINAL PLATE (-49 OPTION)	BRASS	TIN
2	XX	TERMINAL PLATE	BRASS	NICKEL
1	1	INSULATOR	THERMOPLASTIC	BLACK
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

REV	DESCRIPTION	DATE	BY	APPR
1	ADDED -49 & -50 OPTION	2006/11/13	DRW:NEHLE	CHKD:IMACNEIL
2	EC NO: ETC2007-0195	2006/11/13	DRW:NEHLE	CHKD:IMACNEIL
3	APPR:IMACNEIL	2006/11/13	DRW:NEHLE	CHKD:IMACNEIL

GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
mm	MM/IN	2:1	INCH	
4 PLACES ± ---	± .0015	R. KEMP	2002/10/10	
3 PLACES ± 0.038	± .005	CHECKED BY	DATE	
2 PLACES ± 0.13	± .01	P. WALTZ	2002/10/14	
1 PLACE ± 0.3	± ---	APPROVED BY	DATE	
ANGULAR ± 2 °		L. ROTHAU	2002/10/14	
DRAFT WHERE APPLICABLE	SEE CHART	MATERIAL NO.	DOCUMENT NO.	
MUST REMAIN WITHIN DIMENSIONS		SD-38760-001		

SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION
B	

ITEM	QTY	DESCRIPTION	MATERIAL	FINISH
6	XX*2	SCREW, #6-32X.250, PAN HD, PH-SL W/WSHR (-50 OPTION)	STEEL	ZINC W/CHROMATE
5	XX*2	SCREW, #6-32X.250, BGHD, PHIL-SLOT (-49 OPTION)	BRASS	NICKEL
4	XX*2	SCREW, #6-32X.250, BGHD, PHIL-SLOT (STANDARD)	STEEL	ZINC W/CHROMATE
3	XX	TERMINAL PLATE (-49 OPTION)	BRASS	TIN
2	XX	TERMINAL PLATE	BRASS	NICKEL
1	1	INSULATOR	THERMOPLASTIC	BLACK
ITEM	QTY	DESCRIPTION	MATERIAL	FINISH

