


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
J	—	P	LTR	DATE	DWN
		B	REDRAWN WITH CHANGE	FJD0-0068-03	7APR'03
					K.K
					M.S




注記:


1. かん合相手側製品型番: [-1123823-]
2. 取付け基板寸法: FIG. 1参照
FIG. 1のポスト用穴径はハトメを使用しない場合の寸法。
3. ハトメの適用条件はFIG. 2参照
4. 適用基板厚: 1.6+


NOTES:

1. MATING CONN P/N: [-1123823-]
2. APPLICABLE P.C.B LAY OUT: SEE FIG. 1
DIMENSION OF HOLE DIA FOR POST MOUNTING AT FIG1 INDICATES WITHOUT EYELET.
3. APPLICABLE EYELET: SEE FIG. 2
4. APPLICABLE P.C.B THICKNESS: 1.6+

表1
(TABLE 1)

NO	名称 (NAME)	材料 (MATERIAL)
①	ヘッダーハウジング (HEADER HOUSING)	66ナイロン UL94V-0 (66NYLON UL94V-0)
②	ポストコンタクト (POST CONTACT)	錫めっき済み黄銅 (BRASS • TIN PL)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.KOMACHI 07APR2003	tyco Electronics		Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位： 耗 MM		CHK M.SHINDO 7APR2003	NAME 名称 ECONOMY POWER(EP)CONN.1POS HEADER ASSY エコノミーパワー(EP)コネクタ 1POS ヘッダーアッセンブリ			
		APVD M.SHINDO 7APR2003				
		PRODUCT SPEC 製品規格 108-5609				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 10 ≧ : ± 0.2 30 ≧ > 10 : ± 0.25 100 ≧ > 30 : ± 0.3		APPLICATION SPEC 取付適用規格 //	SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-1123824	RESTRICTED TO —
MATERIAL 材料 表1参照 (SEE TABLE1)		FINISH 仕上 //	WEIGHT //		CUSTOMER DRAWING	
			SCALE 尺度 1:1		SHEET 1 OF 1	REV B