

PART NO. : HFJ11-RP44E-S1L12RL

FASTJACK™ WITH 10/100BASE-TX MAGNETICS

COMPLIANT TO IEEE802.3u STANDARDS

DESIGNED FOR PoE, IEEE802.3af APPLICATIONS

POWER ON USED OR UNUSED PAIRS FOR UP TO 350mADC

LEAD-FREE/RoHS COMPLIANT

COMPATIBLE TO LEAD-FREE WAVE SOLDERING PROCESS
FOR THROUGH HOLE COMPONENTS

OPERATING TEMPERATURE 0/70°C

ELECTRICAL SPECIFICATIONS @ 25° C**TURNS RATIO**

P1-P3:J1-J2,P4-P6:J3-J6 1CT:1 ±3%

OCL (100KHz,0.1Vrms,8mADC)

P1-P3,P4-P6 350μH min

INSERTION LOSS

0.1-100MHz -1.1dB max

RETURN LOSS

0.5-30MHz -18dB min

40MHz -15.5dB min

50MHz -13.6dB min

60-80MHz -12dB min

CROSSTALK 0.1-100MHz

-40dB typ

CMR 0.1-30MHz


-50dB typ

30-60MHz -40dB typ

60-100MHz -35dB typ

ISOLATION

1,500Vrms

**HALO/PBL**CALIFORNIA, USA
KOWLOON, HONG KONG
SINGAPORE


TITLE FastJack™ TAB-DOWN

FOR FAST ETHERNET IEEE802.3af


PART NO. HFJ11-RP44E-S1L12RL

SCALE NONE PAGE 1 OF 2

SIGNATURES	DATE	REV.	DESC.	DATE
DRAWN PETER LU	7/18/06	A		
CHECKED				
APPROVED				
FILE HFJ11-RP44E-S1L12RL.DWG				



Housing Material: Polyester, Black UL94V-0
 Contacts: Phosphor Bronze 30µin Au plating over Ni
 Leads: Matte Sn over Ni plating
 Shield: Cu Alloy with Ni plating 40µin min
 Durability: 1000 mating cycles
 Dimensions: Inch [mm]
 Tolerances: ±0.008 inch if not specified



RECOMMENDED P.C. BOARD PATTERN (COMP. SIDE)

HALO/PBL

CALIFORNIA, USA
 KOWLOON, HONG KONG
 SINGAPORE

TITLE	FastJack™ TAB-DOWN	
FOR	FAST ETHERNET IEEE802.3af	
PART NO.	HFJ11-RP44E-S1L12RL	
SCALE	NONE	PAGE 2 OF 2

SIGNATURES	DATE	REV.	DESC.	DATE
DRAWN PETER LU	7/18/06	A		
CHECKED				
APPROVED				
FILE HFJ11-RP44E-S1L12RL.DWG				