

Monolithic, Quad SPST, CMOS Analog Switches

The DG444 and DG445 monolithic CMOS analog switches are drop-in replacements for the popular DG211 and DG212 series devices. They include four independent single pole single throw (SPST) analog switches and TTL and CMOS compatible digital inputs.


These switches feature lower analog ON resistance ($<85\Omega$) and faster switch time ($t_{ON} < 250\text{ns}$) compared to the DG211 and DG212. Charge injection has been reduced, simplifying sample and hold applications.

The improvements in the DG444 series are made possible by using a high voltage silicon-gate process. An epitaxial layer prevents the latch-up associated with older CMOS technologies. The 44V maximum voltage range permits controlling $\pm 20\text{V}$ signals when operating with $\pm 20\text{V}$ power supplies.

The four switches are bilateral, equally matched for AC or bidirectional signals. The ON resistance variation with analog signals is quite low over a $\pm 5\text{V}$ analog input range. The switches in the DG444 and DG445 are identical, differing only in the polarity of the selection logic.

Pinout

DG444, DG445 (PDIP, SOIC)
TOP VIEW



Features

- ON Resistance (Max) 85Ω
- Low Power Consumption (P_D) $<35\mu\text{W}$
- Fast Switching Action
 - t_{ON} (Max) 250ns
 - t_{OFF} (Max, DG444) 140ns
- Low Charge Injection
- Upgrade from DG211/DG212
- TTL, CMOS Compatible
- Single or Split Supply Operation


Applications

- Audio Switching
- Battery Operated Systems
- Data Acquisition
- Hi-Rel Systems
- Sample and Hold Circuits
- Communication Systems
- Automatic Test Equipment

Ordering Information

PART NUMBER	TEMP. RANGE ($^{\circ}\text{C}$)	PACKAGE	PKG. NO.
DG444DJ	-40 to 85	16 Ld PDIP	E16.3
DG444DY	-40 to 85	16 Ld SOIC	M16.15
DG445DJ	-40 to 85	16 Ld PDIP	E16.3
DG445DY	-40 to 85	16 Ld SOIC	M16.15

Functional Diagrams




TRUTH TABLE

LOGIC	V _{IN}	DG444	DG445
0	≤0.8V	ON	OFF
1	≥2.4V	OFF	ON

Pin Descriptions

PIN	SYMBOL	DESCRIPTION
1	IN ₁	Logic Control for Switch 1
2	D ₁	Drain (Output) Terminal for Switch 1
3	S ₁	Source (Input) Terminal for Switch 1
4	V-	Negative Power Supply Terminal
5	GND	Ground Terminal (Logic Common)
6	S ₄	Source (Input) Terminal for Switch 4
7	D ₄	Drain (Output) Terminal for Switch 4
8	IN ₄	Logic Control for Switch 4
9	IN ₃	Logic Control for Switch 3
10	D ₃	Drain (Output) Terminal for Switch 3
11	S ₃	Source (Input) Terminal for Switch 3
12	V _L	Logic Reference Voltage.
13	V+	Positive Power Supply Terminal (Substrate)
14	S ₂	Source (Input) Terminal for Switch 2
15	D ₂	Drain (Output) Terminal for Switch 2
16	IN ₂	Logic Control for Switch 2

Schematic Diagram (One Channel)



Absolute Maximum Ratings

V₊ to V₋ 44V
 GND to V₋ 25V
 V_L (GND - 0.3V) to (V₊) + 0.3V
 Digital Inputs, V_S, V_D (Note 1) (V₋) -2V to (V₊) + 2V or 30mA,
 Whichever Occurs First
 Continuous Current (Any Terminal) 30mA
 Peak Current, S or D (Pulsed 1ms, 10% Duty Cycle Max) .. 100mA

Thermal Information

Thermal Resistance (Typical, Note 2) θ_{JA} (°C/W)
 PDIP Package 90
 SOIC Package 115
 Maximum Junction Temperature (Plastic Packages) 150°C
 Maximum Storage Temperature Range -65°C to 150°C
 Maximum Lead Temperature (Soldering 10s) 300°C
 (SOIC - Lead Tips Only)

Operating Conditions

Temperature Range -40°C to 85°C
 Voltage Range $\pm 20V$ (Max)
 Temperature Range -55°C to 125°C
 Input Low Voltage 0.8V (Max)
 Input High Voltage 2.4V (Min)
 Input Rise and Fall Time $\leq 20ns$

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

NOTES:

1. Signals on S_X, D_X, or IN_X exceeding V₊ or V₋ will be clamped by internal diodes. Limit forward diode current to maximum current ratings.
2. θ_{JA} is measured with the component mounted on an evaluation PC board in free air.

Electrical Specifications

Test Conditions: V₊ = +15V, V₋ = -15V, V_L = 5V, V_{IN} = 2.4V, 0.8V (Note 3),
 Unless Otherwise Specified

PARAMETER	TEST CONDITIONS	TEMP (°C)	(NOTE 4) MIN	(NOTE 5) TYP	(NOTE 4) MAX	UNITS
DYNAMIC CHARACTERISTICS						
Turn-ON Time, t _{ON}	R _L = 1k Ω , C _L = 35pF, V _S = $\pm 10V$ (Figure 1)	25	-	120	250	ns
Turn-OFF Time, t _{OFF}		25	-	110	140	ns
DG444		25	-	160	210	ns
DG445	C _L = 1nF, V _G = 0V, R _G = 0 Ω	25	-	-1	-	pC
Charge Injection, Q (Figure 2)	R _L = 50 Ω , C _L = 5pF, f = 1MHz	25	-	60	-	dB
OFF Isolation (Figure 4)		25	-	-100	-	dB
Crosstalk (Channel-to-Channel) (Figure 3)	f = 1MHz, V _{ANALOG} = 0 (Figure 5)	25	-	4	-	pF
Source OFF Capacitance, C _{S(OFF)}		25	-	4	-	pF
Drain OFF Capacitance, C _{D(OFF)}		25	-	16	-	pF
Channel ON Capacitance, C _{D(ON)} + C _{S(ON)}						
DIGITAL INPUT CHARACTERISTICS						
Input Current V _{IN} Low, I _{IL}	V _{IN} Under Test = 0.8V, All Others = 2.4V	Full	-0.5	-0.00001	0.5	μA
Input Current V _{IN} High, I _{IH}	V _{IN} Under Test = 2.4V, All Others = 0.8V	Full	-0.5	0.00001	0.5	μA
ANALOG SWITCH CHARACTERISTICS						
Analog Signal Range, V _{ANALOG}		Full	-15	-	15	V
Drain-Source ON Resistance, r _{DS(ON)}	I _S = $\mp 10mA$, V _D = $\pm 8.5V$, V ₊ = 13.5V, V ₋ = -13.5V	25	-	50	85	Ω
		Full	-	-	100	Ω
Source OFF Leakage Current, I _{S(OFF)}	V ₊ = 16.5V, V ₋ = -16.5V, V _D = $\pm 15.5V$, V _S = $\mp 15.5V$	25	-0.5	0.01	0.5	nA
		85	-5	-	5	nA

DG444, DG445

Electrical Specifications Test Conditions: $V_+ = +15V$, $V_- = -15V$, $V_L = 5V$, $V_{IN} = 2.4V$, $0.8V$ (Note 3),
Unless Otherwise Specified **(Continued)**

PARAMETER	TEST CONDITIONS	TEMP (°C)	(NOTE 4) MIN	(NOTE 5) TYP	(NOTE 4) MAX	UNITS
Drain OFF Leakage Current, I _{D(OFF)}	V ₊ = 16.5V, V ₋ = -16.5V, V _D = ±15.5V, V _S = ∓15.5V	25	-0.5	0.01	0.5	nA
		85	-5	-	5	nA
Channel ON Leakage Current, I _{D(ON)} + I _{S(ON)}	V ₊ = 16.5V, V ₋ = -16.5V, V _S = V _D , = ±15.5V	25	-0.5	0.08	0.5	nA
		85	-10	-	10	nA
POWER SUPPLY CHARACTERISTICS						
Positive Supply Current, I ₊	V ₊ = 16.5V, V ₋ = -16.5V, V _{IN} = 0V or 5V	25	-	0.001	1	μA
		85	-	-	5	μA
Negative Supply Current, I ₋		25	-1	-0.0001	-	μA
		85	-5	-	-	μA
Logic Supply Current, I _L		25	-	0.001	1	μA
		85	-	-	5	μA
Ground Current, I _{GND}		25	-1	-0.001	-	μA
		85	-5	-	-	μA

Electrical Specifications (Single Supply) Test Conditions: $V_+ = 12V$, $V_- = 0V$, $V_L = 5V$, $V_{IN} = 2.4V$, $0.8V$ (Note 3),
Unless Otherwise Specified


PARAMETER	TEST CONDITIONS	TEMP (°C)	(NOTE 4) MIN	(NOTE 5) TYP	(NOTE 4) MAX	UNITS
DYNAMIC CHARACTERISTICS						
Turn-ON Time, t _{ON}	R _L = 1kΩ, C _L = 35pF, V _S = 8V (Figure 1)	25	-	300	450	ns
Turn-OFF Time, t _{OFF}		25	-	60	200	ns
Charge Injection, Q (Figure 2)	C _L = 1nF, V _G = 6V, R _G = 0Ω	25	-	2	-	pC
ANALOG SWITCH CHARACTERISTICS						
Analog Signal Range, V _{ANALOG}		Full	0	-	12	V
Drain-Source ON Resistance, r _{DS(ON)}	I _S = -10mA, V _D = 3V, 8V V ₊ = 10.8V, V _L = 5.25V	25	-	100	160	Ω
		Full	-	-	200	Ω
POWER SUPPLY CHARACTERISTICS						
Positive Supply Current, I ₊	V ₊ = 13.2V, V _{IN} = 0V or 5V, V _L = 5.25V	25	-	0.001	1	μA
		Full	-	-	5	μA
Negative Supply Current, I ₋		25	-1	-0.0001	-	μA
		Full	-5	-	-	μA
Logic Supply Current, I _L		25	-	0.001	1	μA
		Full	-	-	5	μA
Ground Current, I _{GND}		25	-1	-0.001	-	μA
		Full	-5	-	-	μA

NOTES:

- V_{IN} = input voltage to perform proper function.
- The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this data sheet.
- Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.


Test Circuits and Waveforms

V_O is the steady state output with the switch on. Feedthrough via switch capacitance may result in spikes at the leading and trailing edge of the output waveform.



NOTE: Logic input waveform is inverted for switches that have the opposite logic sense.

FIGURE 1A. MEASUREMENT POINTS



Repeat test for Channels 2, 3 and 4.

For load conditions, see Specifications. C_L includes fixture and stray capacitance.

$$V_O = V_S \frac{R_L}{R_L + r_{DS(ON)}}$$

FIGURE 1B. TEST CIRCUIT




FIGURE 2A. MEASUREMENT POINTS




FIGURE 2B. TEST CIRCUIT




FIGURE 3. CROSSTALK TEST CIRCUIT




FIGURE 4. OFF ISOLATION TEST CIRCUIT

Test Circuits and Waveforms (Continued)





FIGURE 5. SOURCE/DRAIN CAPACITANCES TEST CIRCUIT

Application Information



GAIN ERROR IS DETERMINED ONLY BY THE RESISTOR TOLERANCE, OP AMP OFFSET AND CMRR WILL LIMIT ACCURACY OF CIRCUIT

$$\frac{V_{OUT}}{V_{IN}} = \frac{R_1 + R_2 + R_3 + R_4}{R_4} = 100$$

WITH SW₄ CLOSED

FIGURE 6. PRECISION WEIGHTED RESISTOR PROGRAMMABLE GAIN AMPLIFIER




FIGURE 7. LEVEL SHIFTER

Typical Performance Curves




FIGURE 8. SWITCHING THRESHOLD vs SUPPLY VOLTAGE




FIGURE 9. SUPPLY CURRENT vs TEMPERATURE




FIGURE 10. INPUT CURRENT vs TEMPERATURE




FIGURE 11. $r_{DS(ON)}$ vs V_D AND TEMPERATURE




FIGURE 12. CROSSTALK REJECTION AND OFF ISOLATION vs FREQUENCY




FIGURE 13. CHARGE INJECTION vs SOURCE VOLTAGE

Typical Performance Curves (Continued)




FIGURE 14. SOURCE/DRAIN CAPACITANCE vs ANALOG VOLTAGE




FIGURE 15. LEAKAGE CURRENTS vs ANALOG VOLTAGE




FIGURE 16. SWITCHING TIME vs INPUT VOLTAGE (DG444)




FIGURE 17. SWITCHING TIME vs INPUT VOLTAGE (DG445)




FIGURE 18. SWITCHING TIME vs POWER SUPPLY VOLTAGE (DG444)




FIGURE 19. SWITCHING TIME vs POWER SUPPLY VOLTAGE (DG445)

Typical Performance Curves (Continued)




FIGURE 20. SWITCHING TIME vs INPUT VOLTAGE (DG444)
(SINGLE 12V SUPPLY)




FIGURE 21. SWITCHING TIMES vs SINGLE SUPPLY VOLTAGE




FIGURE 22. CHARGE INJECTION vs SOURCE VOLTAGE
(SINGLE 12V SUPPLY)




FIGURE 23. SOURCE/DRAIN LEAKAGE CURRENTS (SINGLE
12V SUPPLY)




FIGURE 24. SOURCE/DRAIN CAPACITANCE vs ANALOG VOLTAGE (SINGLE 12V SUPPLY)

Die Characteristics

DIE DIMENSIONS:

2160 μ m x 1760 μ m x 485

METALLIZATION:

Type: SiAl

Thickness: 12k $\text{\AA}$ $\pm$ 1k $\text{\AA}$

PASSIVATION:


Type: Nitride

Thickness: 8k $\text{\AA}$ $\pm$ 1k $\text{\AA}$

WORST CASE CURRENT DENSITY:

9.1×10^4 A/cm²

Metallization Mask Layout



All Harris semiconductor products are manufactured, assembled and tested under **ISO9000** quality systems certification.

Harris semiconductor products are sold by description only. Harris Corporation, Semiconductor Communications Division, reserves the right to make changes in circuit design and/or specifications at any time without notice. Accordingly, the reader is cautioned to verify that data sheets are current before placing orders. Information furnished by Harris is believed to be accurate and reliable. However, no responsibility is assumed by Harris or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Harris or its subsidiaries.

For information regarding Harris Corporation's Semiconductor Communications Division and its products, call **1-800-4-HARRIS** or see web site <http://www.semi.harris.com>

Sales Office Headquarters

NORTH AMERICA

Harris Corporation,
Semiconductor Communications Division
P. O. Box 883, Mail Stop 53-210
Melbourne, FL 32902
TEL: 1-800-442-7747
(407) 727-9207
FAX: (407) 724-3973

EUROPE

Harris Corporation,
Semiconductor Communications Division
Mercure Center
100, Rue de la Fusee
1130 Brussels, Belgium
TEL: (32) 2.724.2111
FAX: (32) 2.724.22.05

ASIA

Harris Corporation,
Semiconductor Communications Division,
Taiwan Limited
7F-6, No. 101 Fu Hsing North Road
Taipei, Taiwan
Republic of China
TEL: (886) 2 2716 9310
FAX: (886) 2 2715 3029